



Installation guide

Thermostat

Types CAS 178, CAS 180, CAS 181





060R9305




Type	T ₂ max.	T ₁ min.	T ₁ max.
	[°C]		
CAS 178	130	-25	70
CAS 180	220		
CAS 181	250		



060R9305



Імпортёр:ТОВ з іі "Данфосс ТОВ" 04080, Київ 80, п/с 168, Україна



L [mm]	Code no.	
	Brass	Steel 18/8
75	060L326266	060L326766
110	060L327166	060L326866
160	060L326366	060L326966



Danfoss 60L1049.11

Info for UK customers only: Danfoss Ltd., 22 Wycombe End, HP9 1NB, GB

