


Ordering from the entire SVL 65 bar (943 psi) Series

Size (DN)	Parts Program														
	Housing								Top complete						
	ANG				STR				SVA-S (cap)	SVA-L (cap)	SCA-X	CHV-X	REG-SA	REG-SB	FIA
	DIN	ANSI	SD	SA	DIN	ANSI	SD	SA							
6	148B6689	148B6687	148B6722	148B6711	148B6693	148B6691	148B6743	148B6732	148B6695						
10	148B6690	148B6688	148B6723	148B6712	148B6694	148B6692	148B6744	148B6733					148B5761	148B5764	
15	148B6622	148B6612	148B6724	148B6713	148B6642	148B6632	148B6745	148B6734	148B6652	148B6659	148B5769	148B5776	148B5762	148B5765	148B5783
20	148B6623	148B6613	148B6725	148B6714	148B6643	148B6633	148B6746	148B6735	148B6652	148B6659	148B5769	148B5776	148B5762	148B5765	148B5783
25	148B6624	148B6614	148B6726	148B6715	148B6644	148B6634	148B6747	148B6736	148B6653	148B6660	148B5770	148B5777	148B5763	148B5766	148B5784
32	148B6625	148B6615	148B6727	148B6716	148B6645	148B6635	148B6748	148B6737	148B6653	148B6660	148B5770	148B5777	148B5763	148B5766	148B5784
40	148B6626	148B6616	148B6728	148B6717	148B6646	148B6636	148B6749	148B6738	148B6653	148B6660	148B5770	148B5777	148B5763	148B5766	148B5784
50	148B6627	148B6617	148B6718		148B6647	148B6637	148B6739		148B6654		148B5771	148B5778		148B5767	148B5785
65	148B6628	148B6618	148B6729	148B6719	148B6648	148B6638	148B6750	148B6740	148B6655		148B5772	148B5779		148B5768	148B5786
80	148B6629	148B6619	148B6730	148B6720	148B6649	148B6639	148B6751	148B6741	148B6656		148B5773	148B5780			148B5787
100	148B6630	148B6620	148B6731	148B6721	148B6650	148B6640	148B6752	148B6742	148B6657		148B5774	148B5781			148B5788
125	148B6631	148B6621			148B6651	148B6641			148B6658		148B5775	148B5782			148B5789
150															
200															

Size (DN)	Service kit*		Complete valve							
	O-ring kit for		SVA (cap)				FIA			
	R717 Heat pump	R1270 Propylene	ANG		STR		ANG		STR	
			DIN	ANSI	DIN	ANSI	DIN	ANSI	DIN	ANSI
6				148B5033		148B5053				
10	148B6084	148B6085		148B5034		148B5054				
15				148B5035		148B5055				
20	148B6070	148B6077		148B5036		148B5056				
25				148B5037		148B5057				
32	148B6071**	148B6078**		148B5038		148B5058				
40	148B6096***	148B6097***		148B5039		148B5059				
50	148B6072	148B6079		148B5040		148B5060				
65	148B6073	148B6080		148B5041		148B5061				
80	148B6074	148B6081		148B5042		148B5062				
100	148B6075	148B6082		148B5043		148B5063				
125	148B6076	148B6083		148B5044		148B5064				
150			148B6665	148B6667	148B6666	148B6668	148B6669	148B6671	148B6670	148B6672
200			148B6673	148B6675	148B6674	148B6676	148B6677	148B6679	148B6678	148B6680



* to be used for SCA-X, CHV-X and REG SA/SB (all sizes) | ** to be used for SCA-X, CHV-X, 25-40 | *** to be used for REG SA/SB, 25-40

Danfoss A/S
Climate Solutions - danfoss.com • +45 7488 2222

Any information, including, but not limited to information on selection of product, its application or use, product design, weight, dimensions, capacity or any other technical data in product manuals, catalogues, descriptions, advertisements, etc. and whether made available in writing, orally, electronically, online or via download, shall be considered informative, and is only binding if and to the extent, explicit reference is made in a quotation or order confirmation. Danfoss cannot accept any responsibility for possible errors in catalogues, brochures, videos and other material. Danfoss reserves the right to alter its products without notice. This also applies to products ordered but not delivered provided that such alterations can be made without changes to form, fit or function of the product. All trademarks in this material are property of Danfoss A/S or Danfoss group companies. Danfoss and the Danfoss logo are trademarks of Danfoss A/S. All rights reserved.

AF359543218157en-000201

© Danfoss | Climate Solutions | 2022.12

See how tomorrow's solutions are ready today
visit www.danfoss.com/IR

ENGINEERING
TOMORROW

Danfoss