





Installation Guide

AB-QM (ANSI), 2½"-4", 2nd gen.




Installation




Installation Guide AB-QM (ANSI), 2½"-4"

Shut off




Setting

Note: best before applying pressure





Resetting





Installation Guide AB-QM (ANSI), 2½"-4", 2nd gen.

Locking




Measuring



15...250°F
(-10...120°C)



CLASS 150



$\Delta p_{max.} = 58 \text{ psi (400 kPa)}$

2½"	l/h	GPM
40%	7938	35
50%	10206	45
60%	11340	50
70%	13608	60
80%	15876	70
90%	18144	80
100%	19278	85

Note: 1 turn = 10%

3"	l/h	GPM
40%	11340	50
50%	13608	60
60%	17010	75
70%	19278	85
80%	22680	100
90%	24948	110
100%	27216	120

Note: 1 turn = 10%

4"	l/h	GPM
40%	14742	65
50%	19278	85
60%	22680	100
70%	26082	115
80%	29484	130
90%	34020	150
100%	37422	165

Note: 1 turn = 10%

Installation Guide AB-QM (ANSI), 2½"-4", 2nd gen.
