



min 150 mm  
[5.91 in]


278 mm  
[10.94 in]

100 mm  
[3.94 in]



27

G 1/2A




Pg 16

Ø14 mm  
[0.55 in]



88 mm  
[3.46 in]



70 mm  
[2.76 in]