






A (mm/inch)	B (mm/inch)	C (mm/inch)
Sensor insertion length	Distance from sensor to wall	Total length
50/1.97	100/3.94	109/4.29
60/2.36	110/4.33	119/4.69
80/3.15	130/5.12	139/5.47
100/3.94	150/5.91	159/6.26
120/4.72	170/6.69	179/7.05
150/5.91	200/7.87	209/8.23
200/7.87	250/9.84	259/10.20
250/9.84	300/11.81	309/12.17
300/11.81	350/13.78	359/14.13
310/12.20	360/14.17	369/14.53

Danfoss
DIM084Z6017-00