

Data Sheet

Danfoss *Icon*™ Master Controller 230V

Description



Danfoss *Icon*™ 230V Master controller is a connection box for use in hydronic floor heating using 230V thermostats and actuators.

The *Icon*™ 230V Master controller can connect up to 14 thermal actuators from up to 8 room thermostats. It is provided with 230V Live circulation pump output and a potential-free relays for controlling a boiler. The relays are activated when one or more thermostats require heat.

The featured version also supports away and cooling mode which can be controlled by a 230 V signal as well as LED's to indicate when outputs are active.

Mounting is made easy due to a simple layout of the terminals and clear marking on the screw terminals.

Ordering

Product	Type of plug	Code number
Danfoss <i>Icon</i> ™ Master, 230 V, 8 ch., Basic	F	088U1030
Danfoss <i>Icon</i> ™ Master, 230 V, 8 ch., Featured	F	088U1031
Danfoss <i>Icon</i> ™ Master, 230 V, 8 ch., Basic, CH	J	088U1032
Danfoss <i>Icon</i> ™ Master, 230 V, 8 ch., Featured, CH	J	088U1033


Technical data

	Basic	Featured
Max. number of thermostats	8	
Max number of actuators	14	
Supported actuator types	Normally closed (NC)	
Internal fuse	3A	
Conforms with directives	LVD, EMC, RoHs, WEEE	
Supply voltage	220 - 240 V AC	
Supply frequency	50/60 Hz	
Output voltage, actuators	230 VAC	
Ambient temp. range, operation	0 °C to +50 °C	
Storage temp. range,	-20 °C to +60 °C	
Output relay, pump	230V Max. 100 W	
Output relay, boiler	Potential free Max. 2A	
Output cooling	NA	230 V when active
Output Setback	NA	230 V when active
Input Cooling	NA	External switch input (230 V rating)
Input setback	NA	External switch input (230 V rating)
Rated impulse voltage	4 kV	
Temperature for ball pressure test	75 °C	
Control pollution degree	Pollution degree 2	
Disposal instructions	As electronic waste	

code no.: 088U1030, 088U1032



Icon™ Master Controller 230V Featured
code no.: 088U1031, 088U1033



Danfoss can accept no responsibility for possible errors in catalogues, brochures and other printed material. Danfoss reserves the right to alter its products without notice. This also applies to products already on order provided that such alterations can be made without consequential changes being necessary in specifications already agreed.

All trademarks in this material are property of the respective companies. Danfoss and All Danfoss logos are trademarks of Danfoss A/S. All rights reserved.