

Sales Memo

Danfoss Comfort Controls

CORRECTED

2006-10-02

Press-fit radiator valves

Danfoss is launching a new range of radiator valves.

The new Danfoss press-fit radiator valves are similar to standard RA-N and RLV valves, but with press-fit connection on the system side of the valve (see picture).

The press part of the valves has been designed and developed in such a way that the most commonly used press jaws and pressing tools already available on the market can be used. Plumbers and contractors are therefore not forced into making additional investments in special pressing tools.

Please see the data sheet for suitable press tools and jaws.



Danfoss press valves are approved according to EN215-1 (CEN). Pipes used together with Danfoss press valves must as a minimum comply with EN10312 / EN1057 (minimum wall thickness ≥ 1 mm). O-ring used in press part of Danfoss press valves complies with EN681

Sales Information

| Type | Text | DN | Code | PCL | Stat.no. | EAN |
|------------|--|----|----------|-----|----------|---------------|
| RA-N Press | RA-N 15 Press, Angle | 15 | 013G4207 | 015 | 03446 | 5702420074436 |
| RA-N Press | RA-N 15 Press, Straight | 15 | 013G4208 | 015 | 03446 | 5702420074429 |
| RA-N Press | RA-N 15 Press, Reversed angle | 15 | 013G4209 | 015 | 03446 | 5702420074443 |
| RLV Press | RLV 15 Press, Straight | 15 | 003L0224 | 223 | 03447 | 5702420074450 |
| RLV Press | RLV 15 Press, Angle | 15 | 003L0225 | 223 | 03447 | 5702420074467 |

Pricing

In order to determine the price setting in your market, please contact Henrik Enevold Jensen, Direct phone +45 74 88 80 31, <mailto:heje@danfoss.com>



Sales Memo

Danfoss Comfort Controls

Packaging

Valves are packed in singlepacks, put into multipacks similar to standard RA-N valve types

| | Code | Single pack pcs | Multipack pcs. |
|--|----------|-----------------|----------------|
| RA-N 15 Press, Angle | 013G4207 | 1 | 60 |
| RA-N 15 Press, Straight | 013G4208 | 1 | 60 |
| RA-N 15 Press, Reversed angle | 013G4209 | 1 | 75 |
| RLV 15 Press, Straight | 003L0224 | 1 | 60 |
| RLV 15 Press, Angle | 003L0225 | 1 | 60 |

Brief instructions for installing the valves are printed on the box, but for detailed information please see complete instruction and datasheet.

Literature

Master Datasheets in English and German for both RA-N and RLV are available in PCM from October 1st. Instruction including list of suitable press tools and jaws are available in PCM from October 1st. Local language version will be prepared on request.

Ordering and delivery:

Orders can be placed to Danfoss Silkeborg from now. Stock has been build up during August and September, and approx 2.000 pcs. of each type will be available at the start of October 2006.

Sales promotion materials

Following materials will be available from October 1st 2006:

- Combined Brochure and Leaflet, containing colour pictures, design and ordering data etc.
- Installation video, showing how to install press fit valves.
- PowerPoint presentation, including all above mentioned points.
- Demo panel, with real samples of pressed and unpressed valves (feel and touch)
- Demo suitcases, containing 5 valve types, pipe samples, press-fitting samples and adaptor from 15mm pipe to Rp $\frac{1}{2}$ " pipe tread.

Intranet

Product pictures are available in Heating Image Bank: [>> Link to Heating Image bank <<](#)

Products including data are available in PCM, and present on Danfoss intranet.

Technical support

Michael Nielsen
CD-E, Customer Support
Comfort Controls