




General Information



The LX Series Power Module makes it easy to connect more heating mats or cables to the same thermostat without the need for contactor panels.

- An easy control solution for large areas
- Receives on/off command from the main thermostat
- Each Power Module adds 15A switching capability
- Up to 5 Power Modules can be added to the thermostat
- Includes Class-A GFCI for safety (approved for wet locations)
- For use with Programmable LX thermostat only


|  |                                    |
|--|------------------------------------|
| <b>c-UL-us according to the following standards:</b> |                                    |
| Thermostat:  | UL 873<br>CSA C22.2 No. 24         |
| <b>UL-E file:</b>                                    | E157297                            |
| GFCI:  | UL 943<br>CSA C22.2, No. 144. 1-06 |

Technical Data

|                      |  |
|----------------------|--|
| Supply:              | 120/240 VAC, 50/60 Hz                    |
| Max. Load:           | 15A maximum (resistive load)             |
| Power:               | 1800W at 120 VAC / 3600 at 240 VAC       |
| GFCI:                | Class A (5 mA trip level)                |
| Temperature Range:   | Controlled by thermostat                 |
| Ambient Temp. Range: | Controlled by thermostat                 |
| Housing:             | NEMA 2 (IP21)                            |
| Dimensions (HxWxD):  | 4.8" x 3.0" x 1.0" (123mm x 75mm x 25mm) |



## Typical Application



## Ordering Information

| Part No. | Description            |
|----------|------------------------|
| 088L5135 | Power Module with GFCI |

## Applications

Products in this data sheet are for use with these Danfoss LX Thermostats:

| Part No. | Description  |
|----------|--|
| 088L5130 | LX Thermostat with Floor & Air Sensor (Programmable) |
| 088L5136 | LX205T Touch Thermostat (Programmable)               |
| 088L5137 | LX205 Thermostat (Non-Programmable)                  |

## Warranty

Danfoss offers a two year limited warranty covering defects in workmanship and materials.

## Technical Services

For technical questions, please contact Danfoss Heating Division North America at **1-888-DANFOSS (326-3677)**. More information on Danfoss Electric Heating products is available at [www.LX.Danfoss.com](http://www.LX.Danfoss.com).

Danfoss can accept no responsibility for possible errors in catalogs, brochures, other printed materials, and website information. Danfoss reserves the right to alter its products without notice. This also applies to products already on order provided that such alteration can be made without subsequent changes being necessary in specifications already agreed upon. All trademarks in this material are property of the respective companies. Danfoss and Danfoss logotype are trademarks of Danfoss A/S. All rights reserved.



**Danfoss**  
**Toronto**  
 Tel: 1-888-DANFOSS (326-3677)  
 Tel.: 905-285-2050  
 Fax: 416-352-5981  
[www.LX.Danfoss.com](http://www.LX.Danfoss.com)

**Danfoss LX**  
 BRINGING WARMTH TO LIFE