


## Instructions

AV PN16 / 73695380

## Service kits




A	PN	DN	Δp (bar)								Code No.
			0.05 ÷ 0.5 0.1 ÷ 0.5	0.2 ÷ 1.0	0.3 ÷ 2.0	0.8 ÷ 1.6	0.2	0.3	0.5		
16	15 ÷ 32	-	-	-	-	-	-	×	-	003H1326	
		-	-	-	-	-	-	-	×	003H1331	
		-	-	-	-	×	-	-	-	003H1332	
	25	15 ÷ 50	-	-	-	×	-	-	-	88835920	
25	15 ÷ 25	-	-	-	-	-	-	×	-	88835930	
	32 ÷ 50	-	-	-	-	-	-	×	-	88835940	

M1	CuSn5ZnPb (Rg5)
M2	EN-GJS-400-18-LT (GGG 40.3)

B	PN	DN	Δp <sub>b</sub> (bar)								Code No.
			0.1 ÷ 0.5	0.2 ÷ 1.0	0.3 ÷ 2.0	0.8 ÷ 1.6	0.2	0.3	0.5		
16	15 ÷ 32	-	-	-	-	-	×	-	-	-	003H1330
25	15 ÷ 25	-	-	-	-	-	×	-	-	-	88835920
	32 ÷ 50	-	-	-	-	-	-	-	-	-	-



2	PN 16	AVP, AVP-F, AVPB, AVPB-F, AVD, AVQ, AVQM	M1
2	PN 16	AVPQ, AVPQ-F	M1
3	PN 16	AVPQ 4, AVPQ 4-F	M1
3	PN 16	AVPA	M1

**Service kits**


## Service kits

## Service kits

---

### Danfoss A/S

Climate Solutions • [danfoss.com](http://danfoss.com) • +45 7488 2222

---

Any information, including, but not limited to information on selection of product, its application or use, product design, weight, dimensions, capacity or any other technical data in product manuals, catalogues descriptions, advertisements, etc, and whether made available in writing, orally, electronically, online or via download, shall be considered informative, and is only binding if and to the extent, explicit reference is made in a quotation or order confirmation. Danfoss cannot accept any responsibility for possible errors in catalogues, brochures, videos and other material. Danfoss reserves the right to alter its products without notice. This also applies to products ordered but not delivered provided that such alterations can be made without changes to form, fit or function of the product.

All trademarks in this material are property of Danfoss A/S or Danfoss group companies. Danfoss and the Danfoss logo are trademarks of Danfoss A/S. All rights reserved.