



General Information



The Danfoss RX-C Roof Clip Glue is a versatile, high-strength, one-part, hard-setting, pick-proof adhesive sealant. It offers superb tensile strength with excellent resistance to nature, by being both water- and weather-proof.

The glue is designed for use with Danfoss RX-C Roof Clips - a clip used to secure Danfoss RX cables to asphalt shingles/metal roofs & gutters. Not recommended for membrane and rubber roofs.

Benefits:

- High-strength
- Flexible
- Hard-setting
- Weather-resistant
- Fast-skinning
- Durable bond to material
- Does not crack or become brittle
- Easy application
- Long service life

Ordering Information

Part No.	Description	Packaging
Roof Clip Glue	RX-C Roof Clip Adhesive	10.3 fl. oz. cartridge

For Use With RX-C Roof Clips:

Part No.	Description	Qty
088L3001	RX-C Roof Clips	50 per bag

Application

Interface and surfaces must be clean, dry and free of dust, dirt, oil and water-proofing and release agents. Cut cartridge nozzle at desired size and puncture inner seal. Apply bead size as desired. Apply uniform bead with steady pressure. Tool immediately after application to ensure full contact with both sides of the joint area. Sealant starts to skin over in 20-25 minutes. **Minimum application temperature is 50° F (10° C). Not recommended for soft expansion joints, polystyrene or styrene containing plastic.**

Curing Process

With an 1/8" bead, RX-C Roof Clip Glue is 80% cured after 3 days in 50°F temperatures or higher and 90% cured within 2 weeks. Colder temperatures will stall curing process.

Shelf Life & Storage

12 months from the time of shipment from Danfoss. Please note that RX-C Roof Clip Glue may last many years in an unopened container if stored properly. Unopened containers should be stored in a cool, dry area. Keep above 50°F (10° C) before use.



Caution

For industrial use only. Skin and eye irritant. Harmful if swallowed. Avoid contact with or breathing in of vapor. Material on skin should be wiped and washed off with soap and water. For eyes, flush with water and seek medical attention.

Technical Services

For technical questions, please contact Danfoss Heating Division North America at **1-866-676-8062**. More information on Danfoss Electric Heating products is available at **www.LX.Danfoss.com**.

Danfoss can accept no responsibility for possible errors in catalogs, brochures, other printed materials, and website information. Danfoss reserves the right to alter its products without notice. This also applies to products already on order provided that such alteration can be made without subsequent changes being necessary in specifications already agreed upon. All trademarks in this material are property of the respective companies. Danfoss and Danfoss logotype are trademarks of Danfoss A/S. All rights reserved.



**Danfoss
Toronto**
Toll Free: 1-866-676-8062
Tel.: 905-285-2050
Fax: 416-352-5981
www.LX.Danfoss.com

Danfoss *RX-C*
BRINGING WARMTH TO LIFE