


# Easy Product Selection

## Product Selector for a Basic Roof

1. Total length (ft) of roof line (A) X 5 = RL
2. Total length (ft) of all down spouts (E) x 2 = DS
3. Add RL + DS = estimated length (ft) of cable required

\*\*Discuss more complicated roof lines with your distributor.



## RX Kits, 120V

Part No.	Length (feet)	Watts	Amps	Shingle Clips Inc.	Spacer Clips Inc.
088L3500	30	170	1.4	25	10
088L3502	65	310	2.6	25	10
088L3503	80	395	3.3	50	10
088L3504	100	455	3.8	50	10
088L3505	120	540	4.5	75	10
088L3508	170	755	6.3	100	10
088L3510	230	1080	9.0	100	10
088L3511	265	1225	10.2	125	10

## RX-C Cables

Part No.	Length (feet)	Volts
088L1422	250 ft. spool	120
088L1472	1000 ft. spool	120
088L1432	250 ft. spool	240
088L1473	1000 ft. spool	240
088L1462	Cut to order/by ft."	120
088L1463	Cut to order/by ft."	240

ENGINEERING  
TOMORROW

*Danfoss*

## Electric Heating Solutions

Danfoss heating systems deliver a safe and healthy way of heating homes. We offer a one stop solution to floor heating, snow melting, pipe tracing, and roof and gutter needs.



Danfoss PX trace cable



Danfoss GX Snow Melting Mat



Danfoss LX Cables



## Danfoss

Toll Free: 888 DANFOSS (326 3677) • Fax: 416 352 5981  
www.Heating.Danfoss.us

VBAPH322\_Aug\_2017

ENGINEERING  
TOMORROW

*Danfoss*

## RX Roof & Gutter Deicing

Solutions for Commercial & Residential Applications




www.Heating.Danfoss.us

# Exclusive Features


## Benefits

- Reduce damage to roofs by efficient and free draining of melt water
- Protects from the danger of falling ice from your roof
- Compatible with virtually any type of roof construction (RX-C)
- Typically installed in gutters, downspouts and on roof in problem areas
- Commercial grade cable (RX-C)
- AC plug-residential light commercial (RX Kit)

## Danfoss Cable



## Typical Competitive Grade Cable



# Residential Solutions

## New & Improved RX Kits

Danfoss RX Kits come with everything you need to install the RX cable. Comes complete with heating cable, shingle clips and spacer clips all conveniently in one box. Typically installed on asphalt shingle roofs. 100% Aluminum Foil Screen. (ESP) Electrical Shock Proof. Non-prorated 2 year warranty.



## Kit includes:

- 120V Heating Cable with grounded plug
- Spacer clips
- Shingle clips
- Instruction manual
- 6 Ft. Power Lead

## RX1200 Roof & Gutter De-icing Controller


- Easy, no maintenance operation
- Save up to 75% on energy consumption costs
- Prevent roof damage & leaks
- Extends life of roof de-icing system
- Fully automatic
- Plug & play installation
- Pre-assembled & ready-to-install



# Commercial Solutions

## RX-C Roof & Gutter De-Icing Cables

Danfoss RX-C self regulating cables provide the protection needed to prevent ice dams and build-up from damaging commercial buildings, roof, and gutters. UV-rated.



## DS-8C Remote Sensor Controller for Snow Melting Applications

- Housed in weatherproof enclosure (NEMA 3R)
- Senses both moisture and temperature
- Adjustable temperature trigger point
- Expanded 30-90 min. & 2-6 hr. delay off drying time
- Super bright front panel power/activation LED indicator
- Remote control & monitor capabilities
- Easy to install



## RX-C Clips

- Designed to secure RX-C cables to asphalt shingles, metal seam roofs & gutters.

