





AB-QM Tailpieces for Sizes 1/2" to 1 1/4"					
DATE:	SPECIFICATION SECTION:	PAGE:	of		
<b>PROJECT</b>	<b>ARCHITECT/ENGINEER</b>	<b>AGENCY</b>	<b>REPRESENTATIVE</b>	<b>DATE</b>	<b>NOTES</b>
		<b>ARCHITECT</b>			
<b>SUPPLIER</b>	<b>CONTRACTOR</b>	<b>ENGINEER</b>			
		<b>CONTRACTOR 1</b>			
		<b>CONTRACTOR 2</b>			
		<b>OTHER</b>			
<b>ORDER NO.</b>	<i>NOTE</i>		<i>COMMENT</i>		

For the AB-QM valve bodies in sizes 1/2" to 1 1/4" the valve body will require two (2) tailpiece kits on each end of the valve. Each tailpiece kit contains the tailpiece, union nut and gasket.

**Tailpiece Kit**

Valve Size	Male NPT	Qty	Female Solder	Qty	Special Union Nut *	Qty
1/2" Low Flow	003Z0282		003Z0292		013U0496	
1/2"	003Z0282		003Z0292			
3/4"	003Z0283		003Z0293			
1"	003Z0284		003Z0294			
1 1/4"	003Z0285		003Z0295			

\* For 1/2" Low Flow AB-QM valve body each tailpiece kit will require a special union nut, prt# 013U0496.



Fitting Size	A	Gasket Thickness	Assembled Valve
1/2"	1" (25.5mm)	0.063" (1.6mm)	4.69" (119.2mm)
3/4"	1.12" (28.5mm)		5.60" (142.2mm)
1"	1.30" (33.0mm)		6.82" (173.2mm)
1 1/4"	1.44" (36.5mm)		8.12" (206.2mm)

**Material and Design**

*Tailpieces*

Material	Brass
Available Options	Male NPT / Female Solder
Installation	Radiator spud wrench

*Union Nut*

Material	Brass
Internal Threads	Unplated brass union nut- NPSM Nickel plated (013U0496) - Metric G 3/4

*Gasket*

Material	Fiber gasket material
----------	-----------------------

Danfoss can accept no responsibility for possible errors in printed materials and reserves the right to alter its products without notice. All trademarks in this material are property of the respective companies. Danfoss and Danfoss logotype are trademarks of Danfoss A/S. All rights reserved.



**Danfoss Inc.**  
Toronto, ON,  
Tel.: 866-375-4822, Fax: 905-285-2055  
www.na.heating.danfoss.com

**Danfoss Inc.**  
Baltimore, MD  
Tel.: 866-375-4822, Fax: 443-512-0270  
www.na.heating.danfoss.com