

## Operating Guide

# How to set up a Gmail connection in an AK-SM 8xxA?

**Description**

First action is to organize an email account.


In the below example we have the following data (**Note:** the password needs to be replaced with a real one):

Server name : smtp.gmail.com  
User : danfoss.ecs@gmail.com  
Password : aliasadmin12345  
Port : 587


**Attention!**

On your email account it is important that 3<sup>rd</sup> party devices, like the AK-SM 8xxA, are allowed to send messages.

1. When you have logged into your Google Account, go to "Manage your Google Account".



2. On the left side menu go to "Security".



3. In the "Signing in to Google" enable "2-Step Verification" and follow the guide on screen.

4. When this is done you need to create a new "App password" to be used with the AK-SM 8xxA.


5. The Google system will now create a password that has to be used in your AK-SM 8xxA (remember to take a copy of the password, because it cannot be retrieved afterwards)

If it is still not working use following [link](#) and follow the steps.

### How to configure the SM 8xxA?

If you are accessing through StoreviewBrowser5 go to "Configuration" → "Alarms" and then "Connections":

Fig. 1:



**Location:** Configuration → Alarms **Address:** 0

**Connections** Service Alarm Routing Relays System Offline


**Connections** Updated 10:57:41

Number of network connections	1
Network Connection 1	
Type	E-Mail
E-Mail Configuration	
Use Encryption	Yes
Server	
Type	Name
Name	smtp.gmail.com
Use authentication	Yes
User name	danfoss.ecs@gmail.com
Password	*****
Send To	
1	reciever1@mail.com
2	reciever2@mail.com
3	
Reply To	danfoss.ecs@gmail.com
Send abbreviated alarm message	No
Date	DD/MM/YYYY
Language	English
Time	24 Hour
Port	587
Schedule 1	Standard
From	00:00
To	00:00
Days	SMTWRFSA
Holidays	12345678
Schedule 2	Not Used
Schedule 3	Not Used

Type in all data as shown above incl. the receiver mail addresses.


If you are logging in via Storeview WEB click on the app menu and select “Configuration”:

Fig. 2:



Then you need to go to “Connections” and type in all data (as was shown in Fig. 1 also).

Fig. 3:



The screenshot shows the 'Configuration' page in the Danfoss Smart Store. The 'Connections' tab is selected, displaying a table for configuring network connections. The table includes fields for 'Number of network connections', 'Network Connection 1', 'Type', 'E-Mail Configuration', 'Use Encryption', 'Server', 'Name', 'smtp.gmail.com', 'Use authentication', 'User name', 'danfoss.ecs@gmail.com', 'Password', 'Send To', '1', 'reciever1@mail.com', '2', 'reciever2@mail.com', '3', 'Reply To', 'danfoss.ecs@gmail.com', 'Send abbreviated alarm message', 'No', 'Date', 'DD/MM/YYYY', 'Language', 'English', 'Time', '24 Hour', 'Port', '587', 'Schedule 1', 'Standard', 'From', '00:00', 'To', '00:00', 'Days', 'SMTWRFSA', 'Holidays', '12345678', 'Schedule 2', 'Not Used', and 'Schedule 3', 'Not Used'.

Connections	
Number of network connections	1
Network Connection 1	
Type	E-Mail
E-Mail Configuration	
Use Encryption	Yes
Server	
Type	Name
Name	smtp.gmail.com
Use authentication	Yes
User name	danfoss.ecs@gmail.com
Password	*****
Send To	
1	reciever1@mail.com
2	reciever2@mail.com
3	
Reply To	danfoss.ecs@gmail.com
Send abbreviated alarm message	No
Date	DD/MM/YYYY
Language	English
Time	24 Hour
Port	587
Schedule 1	Standard
From	00:00
To	00:00
Days	SMTWRFSA
Holidays	12345678
Schedule 2	Not Used
Schedule 3	Not Used

## Danfoss A/S

Climate Solutions • danfoss.com • +45 7488 2222

Any information, including, but not limited to information on selection of product, its application or use, product design, weight, dimensions, capacity or any other technical data in product manuals, catalogues descriptions, advertisements, etc. and whether made available in writing, orally, electronically, online or via download, shall be considered informative, and is only binding if and to the extent, explicit reference is made in a quotation or order confirmation. Danfoss cannot accept any responsibility for possible errors in catalogues, brochures, videos and other material. Danfoss reserves the right to alter its products without notice. This also applies to products ordered but not delivered provided that such alterations can be made without changes to form, fit or function of the product.

All trademarks in this material are property of Danfoss A/S or Danfoss group companies. Danfoss and the Danfoss logo are trademarks of Danfoss A/S. All rights reserved.