

# DEVI EasyConnect



DEVI EasyConnect is a system that enables you to connect your self-limiting heating cables - DEVliceguard™ (T), DEVpipeguard™ (T), DEVpipeguard™ LSZH and modify your heat tracing circuit in 1 click. You can use the EasyConnect indoors as well as outdoors. The connectors are IP 68 rated by VDE and CE marked.

The modular design allows a variety of combinations of the connections. The system is compatible with DEVpipeguard™(T),DEVpipeguard™LSZH and DEVliceguard™ (T).

## Benefits:

- Easy to install
- Cut to length on site
- High temperature cable

## Standard compliance:

- DIN VDE 0606 T200
- DIN EN 61984 (VDE 0627)
- VDE 0110 IEC 60999
- LR Type Approval System

## Compliance symbols:



Type	Value
Nominal voltage, max.	250 V~
Max. current	16 A
Max. permissible use temperature	100 °C
Min. permissible use temperature	-40 °C
Power cable	3 x 2,5 mm <sup>2</sup>
Outer sheath	thermoplastic, PA66
Protection class	IP68 (2 hours in water 3 meters deep)
Seal	NBR (Nitrile Butadiene Rubber)



[Click to download - BIM model](#)




## Types

Item no.	Type	Resistance	EAN no.
98300870	DEVI EasyConnect EC-1	Power supply connection set	5703466214503
98300871	DEVI EasyConnect EC-T1	Connection set for 2 heating cables	5703466214510
98300872	DEVI EasyConnect EC-ETK	End plug set	5703466214527
98300873	DEVI EasyConnect EC-1+ETK	Power supply connection set with an end plug	5703466214534
98300874	DEVI EasyConnect EC-T2	Set for heating cable branching – 1 to 2	5703466214541
98300875	DEVI EasyConnect EC-2	Power supply connection set for 2 cables	5703466214558
98300876	DEVI EasyConnect EC-3	Power supply connection set for 3 cables	5703466214565


Make it easy,  
make it DEVI

**DEVI EasyConnect**


**EC-1 (98300870).**  
Power supply connection set




**EC-2 (98300875).**  
Power supply connection set for 2 cables




**EC-3 (98300876).**  
Power supply connection set for 3 cables




**EC-ETK (98300872).**  
End plug set




**EC-1 + ETK (98300873).**  
Power supply connection set with an end plug




**EC-T1 (98300871).**  
Connection set for heating to heating cable.



**EC-T2 (98300874).**  
Set for heating cable branching – 1 to 2



**Example of DEVI EasyConnect appliance**



ECF - socket outlet (Female), ECM - socket plug (Male),  
ECEM - socket plug cover(Male), ECS - distribution block.