

QUYX.E494625 - Process Control Equipment, Electrical

Process Control Equipment, Electrical

See General Information for Process Control Equipment, Electrical

DANFOSS A/S E494625

BLDG E14-S1A NORDBORGVEJ 81 6430 NORDBORG, DENMARK

Pressure transmitters, Model(s) DST P5XZ YYYYYYYY where: "X" and "Z" can be any number from 0-9 "Y" can be letters and numbers And is used to distinguish pressure connection types and also for market purpose

Last Updated on 2019-05-22

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL's Follow-Up Service. Always look for the Mark on the product.



QUYX2.E494625 - Process Control Equipment, Electrical - Component

Process Control Equipment, Electrical - Component

DANFOSS A/S E494625

BLDG E14-S1A NORDBORGVEJ 81 NORDBORG, 6430 Denmark

Process Control Equipment, Model(s) MBT 3270 MBT 3270 followed by 084Z2347

Type MBS, followed by 3000, 3050, 32, 32R, 2050, 33, 3200, 3250, 3300, 3350, 33M, 4003, 4010, 4000, 4050, 1700 or 1750 followed by 060 followed by G, followed by a 4 digit number. Type MBS, followed by 5100, 5150 or 5153, followed by 060 followed by N, followed by a 4 digit number. Type EMP2, followed by 084 followed by G, followed by a 4 digit number.

Pressure Sensor, Type AKS, followed by 32R, 2050, 3000, 3050, 33, 32 followed by 060 followed by G, followed by a 4 digit number.

Type DST, followed by P300, P310, P340, P30M or P35M, followed by 076G, followed by a 4 digit number.

Pressure Transmitter, Model DST followed by P100, P110, P120, P130 or P140, be followed by 075, followed by G followed by any 4 digit number, followed by xx %, zz Vdc or yy mA, where 'xxx' can be a numerical value 0-100, 'zz' can be a numerical value 0-11, and 'yy' can be a numerical value 0-20.

Pressure Transmitter, Model DST followed by P6XX, may be followed by 4 alphanumeric characters, may be followed by 7 alphanumeric characters.

Marking: Company name and model designation.

Last Updated on 2021-09-29

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL's Follow-Up Service. Always look for the Mark on the product.



QUYX7.E494625 - Process Control Equipment, Electrical Certified for Canada

Process Control Equipment, Electrical Certified for Canada

See General Information for Process Control Equipment, Electrical Certified for Canada

DANFOSS A/S E494625

BLDG E14-S1A NORDBORGVEJ 81 6430 NORDBORG, DENMARK

Pressure transmitters, Model(s) DST P5XZ YYYYYYYY where: "X" and "Z" can be any number from 0-9 "Y" can be letters and numbers And is used to distinguish pressure connection types and also for market purpose

Last Updated on 2019-05-22

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL's Follow-Up Service. Always look for the Mark on the product.



QUYX8.E494625 - Process Control Equipment, Electrical Certified for Canada - Component

Process Control Equipment, Electrical Certified for Canada - Component

DANFOSS A/S E494625

BLDG E14-S1A NORDBORGVEJ 81 NORDBORG, 6430 Denmark

Process Control Equipment, Model(s) MBT 3270 MBT 3270 followed by 084Z2347

Type MBS, followed by 3000, 3050, 32, 32R, 2050, 33, 3200, 3250, 3300, 3350, 33M, 4003, 4010, 4000, 4050, 1700 or 1750, followed by 060 followed by G, followed by a 4 digit number. Type MBS, followed by 5100, 5150 or 5153 followed by 060, followed by N, followed by a 4 digit number. Type EMP2, followed by 084, followed by G, followed by a 4 digit number.

Pressure Sensor, Type AKS, followed by 32R, 2050, 3000, 3050, 33, 32, followed by 060 followed by G, followed by a 4 digit number.

Type DST, followed by P300, P310, P340, P30M or P35M, followed by 076G, followed by a 4 digit number.

Pressure Transmitter, Model DST followed by P100, P110, P120, P130 or P140, be followed by 075, followed by G followed by any 4 digit number, followed by xx %, zz Vdc or yy mA, where 'xxx' can be a numerical value 0-100, 'zz' can be a numerical value 0-11, and 'yy' can be a numerical value 0-20.

Pressure Transmitter, Model DST followed by P6XX, may be followed by 4 alphanumeric characters, may be followed by 7 alphanumeric characters

Marking: Company name, model designation and the Recognized Component Mark for Canada,



Last Updated on 2021-09-29

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL's Follow-Up Service. Always look for the Mark on the product.