

Infographic

## How AB-QM 4.0 redefines the value of PICVs

An interactive comparison between Danfoss AB-QM and new AB-QM 4.0

Almost 20 years ago Danfoss created a new way of hydronic balancing and control in HVAC heating and cooling systems by introducing AB-QM Pressure Independent balancing and Control Valves (PICVs).

Now we redefine PICV value with AB-QM 4.0. The successor of AB-QM is designed to be the indisputable best PICV on the market. Find out what we did and how that helps your PICV designs.

Continue by clicking the buttons below:

Specification and installation >

Reliability and robustness >



Specification and installation


## For those who want to win tenders

AB-QM is designed to comply with modern specifications. It has multiple features and functionalities that simplify installation and commissioning.

For example, the control accuracy, especially at low flow settings, has been improved for optimized energy efficiency and comfort.

Also, the flow range per DN size has been increased, allowing smaller valves to perfectly control larger flows. This results in competitive project prices with best-in-class products.

Back to front page >



Setting >

Measuring >

Connections >


Pressure and Flow >



< Go to datasheet

## Setting

Specification and installation



### NEW AB-QM 4.0


Visible setting with mounted actuator

Nominal flow in l/h and US GPM

1-10 scale for 10-100% flow setting

Stroke limitation principle

Back to overview >



### AB-QM

Invisible setting with mounted actuator

Nominal flow in l/h


20-100 scale for 20-100% flow setting

Stroke limitation principle

Measuring >

## Measuring

Specification and installation



### NEW AB-QM 4.0


Accurate flow measuring

Test plugs optional (DN 15LF - DN 20HF)

Test plugs **standard** (DN 25 - DN 32HF)

**Standard** test plugs c.t.c. distance

Back to overview >



### AB-QM

Flow indication

Test plugs optional

Non-standard test plugs c.t.c. distance

Connections >

## Connections

Specification and installation




### NEW AB-QM 4.0

**Standard** external thread acc. ISO 228/1

**Standard** internal thread acc. ISO 7/1

Available in DN 15LF - DN 32HF

Back to overview >



### AB-QM

Short external thread acc. ISO 228/1


No internal thread version

Available in DN 10LF - DN32HF

Pressure and Flow >

## Pressure and Flow

Specification and installation



### NEW AB-QM 4.0

PN 25 / 360 PSI

$\Delta P$  min. = 16 kPa (DN 15-20 LF and NF)  
= 25 kPa (DN 15/20 HF)  
= 20 kPa (DN 25/32 NF)  
= 30 kPa (DN 25/32 HF)


$\Delta P$  max. =600 kPa

Qmin. = **10%** of Qnom.

**Increased** design flow settings:

- DN 10: **not available**  
- DN 15: **20 – 1200 l/h**  
- DN 20: **110 – 1900 l/h**  
- DN 25: **230 – 3800 l/h**  
- DN 32: **360 – 5000 l/h**

Back to overview >



### AB-QM

PN 16 / 300 PSI


$\Delta P$  min. = 16 kPa (DN 15-20 LF and NF)  
= 32 kPa (DN 15/20 HF)  
= 20/25 kPa (DN 25/32 NF)  
= 35 kPa (DN 25/32 HF)

$\Delta P$  max. = 600 kPa

Qmin. = 20% of Qnom.

Design flow settings:

- DN 10: 15 – 275 l/h  
- DN 15: 55 – 1135 l/h  
- DN 20: 180 – 1700 l/h  
- DN 25: 340 – 2700 l/h  
- DN 32: 640 – 4000 l/h



Reliability and robustness


## For those who want superior quality

AB-QM 4.0 is designed for a long lifetime value to reduce the buildings' total costs of ownership. For example the presence of scaling and clogging in heating and cooling systems can't be avoided.

By using innovative PPSU polymer for the inner components most sensitive to scaling, we reduce the effect and maintain the high control performance over a longer lifetime.

Flushing and filling of the system can now be performed in both directions, saving precious time before commissioning and hand-over of the system.

Back to front page >



Control valve >

Valve body >


Pressure controller >



< Go to datasheet

## Control valve

Reliability and robustness




### NEW AB-QM 4.0

PPSU polymer and DZR brass materials

**Superior protection** against scaling and clogging through extensive testing and intensive use of new materials

Stroke **4 mm** for all valve sizes

Back to overview >



### AB-QM

DZR brass materials


Better protection against scaling and clogging compared to other PICVs on the market

Stroke 2.25 – 4.5 mm depending on valve size

Valve body >

## Valve body

Reliability and robustness




### NEW AB-QM 4.0

DZR brass

**Bi-directional** flushing and filling

Made as **1 part**

Back to overview >



### AB-QM

DZR Brass

Flow-direction flushing and filling

Made from 2 parts

Pressure controller >

## Pressure controller

Reliability and robustness



### NEW AB-QM 4.0


**Re-designed, low friction**, differential pressure controller that reduces the hysteresis

PPSU polymer and DZR brass materials

**Superior protection** against scaling and clogging through extensive testing and intensive use of new materials

Functions over control valve only for 100% valve authority to ensure high accuracy pressure independent control performance

Back to overview >



### AB-QM

Membrane-driven differential pressure controller that reduces the hysteresis

DZR Brass materials

Better protection against scaling and clogging compared to other PICVs on the market

Functions over control valve only for 100% valve authority to ensure high accuracy pressure independent control performance

AD31198421227728en-010301 | 2022.09