

 **CERTIFICATE**  
FOR EUROPEAN PRODUCT SAFETY

Reference No. SE-S-2400126

## Heating cable, serie-resistive

**Type designation:** DEVIflex\*\*T, ECflex\*\*T, DEVIsafe\*\*T, ECsafe\*\*T

**Certificate holder:**  
Danfoss Poland Sp. z.o.o.  
Chrzanowska 5  
05-825 Grodzisk Mazowiecki  
POLAND

**The product complies with the standard(s):** IEC 60800:2009

**Date of expiry:** 22 February, 2029

Additional information in Appendix

**Certification Body:** Intertek Semko AB, Product Certification

**Place:** Kista - Stockholm

**Signed:**



**Date:** 22 February, 2024

Anneli Averland Johansson

This Certificate is for the exclusive use of Intertek's client and is provided pursuant to the agreement between Intertek and its Client. Intertek's responsibility and liability are limited to the terms and conditions of the agreement. Intertek assumes no liability to any party, other than to the Client in accordance with the agreement, for any loss, expense or damage occasioned by the use of this Certificate. Only the Client is authorized to permit copying or distribution of this Certificate and then only in its entirety. Any use of the Intertek name or one of its marks for the sale or advertisement of the tested material, product or service must first be approved in writing by Intertek.

## APPENDIX:

Reference No. SE-S-2400126

### Technical Data:

Type designation	DEVIflex **T, ECflex **T
Rated voltage (V)	300/500 V
Number of conductors	2 + screen
Trademark	DEVI, Danfoss
Test Report	2306595ST0-001
Product information	"" denotes power rating (6 / 10 / 18 / 20 W/m). Multi conductor series resistive. With cold lead, splice and end seal. Mechanical class M2. Minimum installation temperature: -5°C. Minimum bending diameter: 6 times cable diameter.
Others	DEVI type reference: DEVIflex **T Danfoss type reference: ECflex **T

Type designation	DEVIsafe **T, ECsafe **T
Rated voltage (V)	300/500 V
Number of conductors	2 + screen
Trademark	DEVI, Danfoss
Test Report	2306595ST0-001
Product information	"" denotes power rating (20 W/m), Multi conductor series resistive. With cold lead splice and end seal. Mechanical class M2. Also for outdoor installation (UV-resistant). Minimum installation temperature: -5°C. Minimum bending diameter: 6 times cable diameter.
Others	DEVI type reference: DEVIsafe **T Danfoss type reference: ECsafe-**T.

### Manufacturing Sites:

Danfoss Poland Sp. z.o.o.  
Ul. Chrzanowska 5  
05-825 Grodzisk Mazowiecki  
POLAND

**Certification Body:**

Intertek Semko AB, Product Certification

**Signed:**

**Place:** Kista - Stockholm

**Date:** 22 February, 2024

  
Anneli Averland Johansson

This Certificate is for the exclusive use of Intertek's client and is provided pursuant to the agreement between Intertek and its Client. Intertek's responsibility and liability are limited to the terms and conditions of the agreement. Intertek assumes no liability to any party, other than to the Client in accordance with the agreement, for any loss, expense or damage occasioned by the use of this Certificate. Only the Client is authorized to permit copying or distribution of this Certificate and then only in its entirety. Any use of the Intertek name or one of its marks for the sale or advertisement of the tested material, product or service must first be approved in writing by Intertek.