

PRODUCT CERTIFICATE

Certificate Number:
7714-2016-PC-DEN-DANAK rev. 11
ID no.: 54

Initial Certification Date:
23 February 2012

Validity:
01 May 2024 to 30 April 2027

It is hereby certified that:

Danfoss A/S

Nordborgvej 81, 6430 Nordborg, Denmark

with the following production site

Danfoss EOOD

5, Rezbarska Street, 1510 Sofia, Bulgaria

fulfils the requirements in:

DS/EN 215:2019

This certificate is valid for following scope:

CEN Keymark Scheme Rules for Thermostatic Radiator valves


For more details see appendix to certificate

This certificate is valid under the condition that the certificate holder comply with the current CEN Keymark scheme rules for Thermostatic Radiator Valves and the specific rules for certification as specified in SBC 215. The certificate is not transferable.

Place and date:
Hellerup, 01 May 2024



For the issuing office:
DNV Business Assurance Denmark A/S


Jesper Schultz
Management Director

Appendix to Certificate

Name	Parameters	Additional Parameters	Technical Report
Valves / Series			
Siemens			
D	VEN 110	DN 10 A	B 20. DAN.1291
D	VDN 110	DN 10 S	B 20. DAN.1291
D	VUN 210	DN 10 A	B 20. DAN.1291
D	VEN 115	DN 15 A	B 20. DAN.1291
D	VDN 115	DN 15 S	B 20. DAN.1291
D	VUN 215	DN 15 A	B 20. DAN.1291
D	VEN 120	DN 20 A	B 20. DAN.1291
D	VDN 120	DN 20 S	B 20. DAN.1291
F	VEN 210	DN 10 A	B 20. DAN.1290
F	VDN 210	DN 10 S	B 20. DAN.1290
F	VEN 215	DN 15 A	B 20. DAN.1290
F	VDN 215	DN 15 S	B 20. DAN.1290
F	VEN 220	DN 20 A	B 20. DAN.1290
F	VDN 220	DN 20 S	B 20. DAN.1290
RA-G			
D	013G1675	DN 15 S	B 22. DAN.1402
D	013G1676	DN 15 A	B 22. DAN.1402
D	013G1677	DN 20 S	B 22. DAN.1402
D	013G1678	DN 20 A	B 22. DAN.1402
*	013G1679	DN 25 S	B 22. DAN.1402
*	013G1680	DN 25 A	B 22. DAN.1402
RTR-G			
D	013G7023	DN 15 A	B 20.DAN.1310
D	013G7025	DN 20 A	B 20.DAN.1310
*	013G7027	DN 25 S	B 20.DAN.1310
*	013G7028	DN 25 A	B 20.DAN.1310
RA-N			
*	013G4202	DN 15 S	B 22. DAN.1403
*	013G4203	DN 15 A	B 21. DAN.1342
*	013G4204	DN 15 A	B 21. DAN.1342
*	013G4205	DN 15 A	B 21. DAN.1342
*	013G6804**	DN 15 A	B 21. DAN.1355
*	013G6805**	DN 15 S	B 21. DAN.1355
*	013G6806**	DN 15 A	B 22. DAN.1417
*	013G6807**	DN 15 A	B 22. DAN.1417
*	013G6814**	DN15A	B 22.DAN.1394
*	013G6815**	DN 15 S	B 22. DAN.1418
*	013G3011**	DN 10 A	B 21. DAN.1343
*	013G3013**	DN 15 A	B 22. DAN.1405
*	013G3015**	DN 20 A	B 22. DAN.1405
*	013G3031	DN 10 A	B 22. DAN.1406
*	013G3033	DN 15 A	B 21. DAN.1343
*	013G3237	DN 15 A	B 22. DAN.1407
*	013G3239	DN 15 A	B 22. DAN.1407
S	013G4022	DN 10 S	B 22. DAN.1408
*	013G0231	DN 10 A	B 21. DAN.1344
*	013G0232	DN 10 A	B 21. DAN.1344
D	013G0035	DN 20 A	B 22. DAN.1409
RA-N			
D	013G0036	DN 20 S	B 22. DAN.1409
*	013G0037	DN 25 A	B 22. DAN.1409

Certificate no.: 7714-2016-PC-DEN-DANAK rev. 11
ID no.: 54
Place and date: Hellerup, 01 May 2024

Name	Parameters	Additional Parameters	Technical Report
*	013G0038	DN 25 S	B 22. DAN.1409
D	013G0155	DN 20 A	B 22. DAN.1410
S	013G0051	DN 10 A	B 22. DAN.1411
S	013G0053	DN 15 A	B 22. DAN.1411
S	013G0055	DN 20 A	B 20.DAN.1284/A1
S	013G0056	DN 20 S	B 22. DAN.1411
S	013G0071**	DN 10 A	B 22. DAN.1411
S	013G0073**	DN 15 A	B 22. DAN.1411
S	013G0075 **	DN 20 A	B 20. DAN.1311
S	013G0076**	DN 20 S	B 22. DAN.1411
RTR-N			
	013G7017	DN 25 A	B 20.DAN.1309
	013G7018	DN 25 S	B 20.DAN.1309
	013G7049	DN 20 A	B 20.DAN.1309
RA-NCX			
D	013G4237	DN 15 A	B 21.DAN.1345
D	013G4238	DN 15 S	B 19.DAN.1262
*	013G4239	DN 15 A	B 22. DAN.1412
*	013G4240	DN 15 A	B 22. DAN.1412
F	013G4247	DN 15 A	B 22. DAN.1412
F	013G4248	DN 15 S	B 22. DAN.1412
RA-U			
S	013G3022	DN 10 S	B 22. DAN.1413
S	013G3292	DN 10 S	B 21. DAN.1356
RA-FN			
F	013G0002	DN 10 S	B 22. DAN.1414
F	013G0005	DN 20 A	B 23. DAN.1477
D	013G0025	DN 20 A	B 22. DAN.1415
D	013G0026	DN 20 S	B 22. DAN.1415
*	013G0027	DN 20 A	B 23. DAN.1477
*	013G0028	DN 20 S	B 23. DAN.1477
*	013G0149	DN 15 A	B 22. DAN.1416
D	013G0145	DN 20 A	B 19. DAN.1264
D	013G0141	DN 10 A	B 20. DAN.1285/A1
*	013G4218	DN 15 A	B 19. DAN.1263
RTR-FN			
F	013G7005	DN 20 A	B 20.DAN.1308
D	013G7009	DN 20 A	B 20.DAN.1308
RVM-FN			
	013L3133	DN 15 A	A 20.DAN.1292
RA-DV			
*	013G7699	DN15 A	B 20.DAN.1269-A2
F	013G7715	DN 20 A	B 20.DAN.1287
F	013G7716	DN 20 S	B 20.DAN.1287
D	013G7725	DN 20 A	B 20.DAN.1289
D	013G7726	DN 20 S	B 20.DAN.1289
*	013G7717	DN 10 A	B 20.DAN.1288
*	013G7718	DN 10 A	B 20.DAN.1288
*	013G7719	DN 15 A	B 20.DAN.1288
*	013G7720	DN 15 A	B 20.DAN.1288
D	013G7709	DN 10 A	B 20.DAN.1286
D	013G7710	DN 15 A	B 20.DAN.1286
RA-IN			
*	013G6571	DN 10 A	B 23.DAN.1480
*	013G6572	DN 10 A	B 23.DAN.1480
*	013G6587	DN 25 A	B 23.DAN.1481

Lack of fulfilment of conditions as set out in the Certification Agreement may render this Certificate invalid.

Name	Parameters	Additional Parameters	Technical Report
*	013G6588	DN 25 S	B 23.DAN.1481
D	013G6593	DN 15 A	B 23.DAN.1476
D	013G6595	DN 20 A	B 23.DAN.1482
Siemens			
D	VPE110A-135	DN10A	B 22. DAN.1367
D	VPD110A-135	DN10S	B 22. DAN.1367
D	VPE115A-135	DN15A	B 22. DAN.1367
D	VPD115A-135	DN15S	B 22. DAN.1367
D	VPE120A-135	DN20A	B 22. DAN.1367
D	VPD120A-135	DN20S	B 22. DAN.1367
D	VPU110A-135	DN10A	B 22. DAN.1364
D	VPU115A-135	DN15A	B 22. DAN.1364
F	VPE210A-135	DN10A	B 22. DAN.1366
F	VPD210A-135	DN10S	B 22. DAN.1366
F	VPE215A-135	DN15A	B 22. DAN.1363
F	VPD215A-135	DN15S	B 22. DAN.1363
F	VPE220A-135	DN20A	B 22. DAN.1366
F	VPD220A-135	DN20S	B 22. DAN.1366
RA-N PURE			
S	015G0071	DN10A	B 22. DAN.1404
S	015G0072	DN10S	B 22. DAN.1404
S	015G0073	DN15A	B 22. DAN.1404
S	015G0074	DN15S	B 22. DAN.1404
S	015G0076	DN20S	B 22. DAN.1404
S	015G3022	DN10S	B 22. DAN.1404
S	015G4022	DN10S	B 22. DAN.1404
RA-DV PURE			
S	015G0251	DN10A	B 23.DAN.1469
S	015G0252	DN10S	B 23.DAN.1469
S	015G0253	DN15A	B 23.DAN.1469
S	015G0254	DN15S	B 23.DAN.1469
S	015G0255	DN20A	B 23.DAN.1469
S	015G0256	DN20S	B 23.DAN.1469
S	015G0271	DN10A	B 23.DAN.1469
S	015G0272	DN10S	B 23.DAN.1469
S	015G0273	DN15A	B 23.DAN.1469
S	015G0274	DN15S	B 23.DAN.1469
S	015G0275	DN20A	B 23.DAN.1469
S	015G0276	DN20S	B 23.DAN.1469