



TYPE APPROVAL CERTIFICATE
No. **ELE173322XG/006**

This is to certify that the product below is found to be in compliance with the applicable requirement of the RINA type approval system.

| | |
|-----------------------------|--|
| <i>Description</i> | FREQUENCY CONVERTERS |
| <i>Type</i> | Series FC-300 |
| <i>Applicant</i> | DANFOSS POWER ELECTRONICS A/S ULSNAES 1 DK-6300 GRAASTEN DENMARK |
| <i>Manufacturer</i> | DANFOSS, LLC |
| <i>Place of manufacture</i> | 4401 N. BELL SCHOOL RD., 61111 LOVES PARK (IL), U.S.A ULSNAES 1, DK-6300 GRAASTEN, DENMARK |
| <i>Reference standards</i> | Rules for the classification of ships.- Part C - Machinery, systems and fire protection. - Ch.3, Sect. 6, Table 1 |

Issued in **HAMBURG** on **November 16, 2022**. This Certificate is valid until **September 1, 2027**

RINA Services S.p.A.
Giuseppe Russo

This certificate consists of this page and 1 enclosure

TYPE APPROVAL CERTIFICATE

No. ELE173322XG/006

Enclosure - Page 1 of 4

Series FC-300

Product description:

The VLT® Automation Drive Series FC-300 series (FC-301/302) are frequency converter for asynchronous motors for use in various marine applications.

FC-300: 200-240V

| Power rating [kW] | Enclosure type | | | |
|----------------------|----------------|-----------|-----------|-----------|
| | IP20 (*1) | IP21 (*2) | IP55 (*3) | IP66 (*4) |
| FC-300 | | | | |
| 0,25 | A2 | A2 (*5) | A4+A5 | A4+A5 |
| 0,37 | | | | |
| 0,55 | | | | |
| 0,75 | | | | |
| 1,1 | | | | |
| 1,5 | | | | |
| 2,2 | A3 | A3 (*5) | A5 | A5 |
| 3,0 | | | | |
| 3,7 | B3 | B1 | B1 | B1 |
| 5,5 | | | | |
| 7,5 | | | | |
| 11 | B4 | B2 | B2 | B2 |
| 15 | | C1 | C1 | C1 |
| 18,5 | C3 | | | |
| 22 | | | | |
| 30 | C4 | C2 | C2 | C2 |
| 37 | | | | |

FC-300: 380-480/500V

| Power rating [kW] | Enclosure type | | | |
|----------------------|----------------|-----------|-----------|-----------|
| | IP20 (*1) | IP21 (*2) | IP55 (*3) | IP66 (*4) |
| FC-300 | | | | |
| 0,37 | A2 | A2 (*5) | A4+A5 | A4+A5 |
| 0,55 | | | | |
| 0,75 | | | | |
| 1,1 | | | | |
| 1,5 | | | | |
| 2,2 | | | | |
| 3,0 | A3 | A3 (*5) | A5 | A5 |
| 4,0 | | | | |
| 5,5 | B3 | B1 | B1 | B1 |
| 7,5 | | | | |
| 11 | | | | |
| 15 | B4 | B2 | B2 | B2 |
| 18,5 | | | | |
| 22 | C3 | C1 | C1 | C1 |
| 30 | | | | |
| 37 | C4 | C2 | C2 | C2 |
| 45 | | | | |
| 55 | | | | |
| 75 | | | | |

DR

TYPE APPROVAL CERTIFICATE
No. ELE173322XG/006
Enclosure - Page 2 of 4
Series FC-300

FC-300: 525-690V

| Power rating [kW] | Enclosure type | | | |
|----------------------|----------------|-----------|-----------|-----------|
| | IP20 (*1) | IP21 (*2) | IP55 (*3) | IP66 (*4) |
| FC-300 | | | | |
| 1,1 | A3 | NA | NA | NA |
| 1,5 | | | | |
| 2,2 | | | | |
| 3,0 | | | | |
| 3,7 | | | | |
| 5,5 | | | | |
| 7,5 | B4 | B2 | B2 | B2 |
| 11 | | | | |
| 15 | | | | |
| 18 | | | | |
| 22 | | | | |
| 30 | | | | |
| 37 | C3 | C2 | C2 | C2 |
| 45 | | | | |
| 55 | | | | |
| 75 | D3h | | | |

- (*1) IP20/Panel mount. All IP20 versions can be upgraded to IP21 with optional kit
- (*2) IP21/NEMA Type 1
- (*3) IP55/NEMA Type 12
- (*4) IP66/NEMA Type 4X
- (*5) IP20/Panel with IP21 upgrade kit

FC-302: 380-480/500V

| Power rating [kW] | Enclosure type | | | | |
|----------------------|----------------|-----------|------------------|----------|--------------------------|
| | 6-pulse | | | 12-pulse | Low Harmonic Drive (LHD) |
| FC-302 | IP00 (*1) | IP20 (*1) | IP21 / IP54 (*2) | | |
| 90 | NA | D3H | D1h/D5h/D6h | NA | NA |
| 110 | | | | | D1n |
| 132 | | D4h | D2h/D7h/D8h | | D2n |
| 160 | | | | | |
| 200 | E2, E3h | E3h | E1/E1h | F8/F9 | E9 |
| 250 | | | | | |
| 315 | | | | | |
| 355 | | | | | |
| 400 | E4h | E4h | F1/F3/E2h | F10/F11 | F18 |
| 450 | | | | | |
| 500 | | | | | |
| 560 | NA | NA | F1/F3 | F12/F13 | NA |
| 630 | | | | | |
| 710 | | | F2/F4 | | |
| 800 | | | | | |

SR

TYPE APPROVAL CERTIFICATE

No. **ELE173322XG/006**

Enclosure - Page 3 of 4

Series FC-300

FC-302: 525-690V

| Power rating [kW] | Enclosure type | | | |
|----------------------|----------------|-------------|------------------|----------|
| | 6-pulse | | | 12-pulse |
| | IP00 (*1) | IP20 (*1) | IP21 / IP54 (*2) | |
| FC-302 | | | | |
| 55 | NA | D3h | D1h/D5h/D6h | NA |
| 75 | | | | |
| 90 | | | | |
| 110 | | | | |
| 132 | | | | |
| 160 | | | | |
| 200 | | | | |
| 250 | D4h | D2h/D7h/D8h | | |
| 315 | | | | |
| 355 | E2, E3h | E3h | E1/E1h | F8/F9 |
| 400 | | | | |
| 450 | | | | |
| 500 | | | | |
| 560 | | | | |
| 630 | E4h | E4h | F1/F3/E2h | F10/F11 |
| 710 | | | | |
| 800 | NA | NA | F1/F3 | F12/F13 |
| 900 | | | F2/F4 | |
| 1000 | | | | |
| 1200 | | | | |

(*1) IP00/IP20/Panel mount.

(*2) IP21/NEMA Type 1; IP54/NEMA Type 12

Technical data: (In accordance with Danfoss design guide)

Power supply: 200-240V / 380-480V / 525-690V, 50/60Hz

Voltage variation: +-10 %, -15% reduced power rating

Frequency variation: A, B and C frames: +-10%; D, E and F frames: +-5%

Output frequency: A, B and C frames: 0 - 590 Hz; D, E and F frames: 0 - 590 Hz

Temperature range in operation: 0 - 45°C, 46-55°C derating according to relevant design guide.

Protection class: IP00 / 20 / 21 / 54 / 55 / 66

Documents and drawings:

User manuals: - MG16O102 dated 01/2017; MG22A102 dated 01/2017; MG38A102 dated 01/2017;

Drawings: - 177r0659 dated 9/15/16; 177r0704 dated 06/24/2020; 177r0705 dated 06/24/2020; 177r0706 dated 06/24/2020; - 177r0707 dated 06/25/2020;

Test reports:

Checklist for visual inspection 4001PRT2 00734665 Rev. 2.10 dated 2017-01-18;

Danfoss A/S: - 00715502 Rev. A dated 2013-07-30; 00734306 Rev. A dated 2017-01-12; 00734307 Rev. A dated 2017-01-13;

- 00734308 Rev. A dated 2017-01-13; 00734309 Rev. A dated 2017-01-13; 00734724 dated 2017-01-26;

- 00735629 Rev. A dated 2017-03-16; 00735840 dated 2017-03-27; P4001 dated 3/15/2017;

- P4001 Rev. A dated 2017-01-10; P7020 dated 2015-07-10; tr4001 dated 12-09-16; PEC-4639 dated 19-10-2021; PEC-4640 dated

24-09-2021; PEC-4679 dated 28-09-2021; PEC-4680 dated 05-10-2021; PEC-4681 dated 13-10-2021; PEC-4682 dated 15-10-2021;

Datasyst Engineering & Testing Services Inc.: - D15-15766 Rev. A dated July 29,2013; D15-17445 dated August 17,2016;

Elite Electronic Engineering Inc.: - 1604970-01 Rev.B dated January 17, 2017;

TÜV Rheinland: - 19645766001 dated 11 Jan 2017; 19645767001 dated 11 Jan 2017;

UL: - 00733941; 11494250A dated December 16,2016; 11494250B dated December 16,2016;

- 4786962025-S1-1 dated 9 July 2015; Break Down of Component_Test DataSheet;

DR

TYPE APPROVAL CERTIFICATE

No. **ELE173322XG/006**

Enclosure - Page 4 of 4

Series FC-300

Manufacturing sites:

DANFOSS, LLC
4401 N. BELL SCHOOL RD.
61111 LOVES PARK (IL)
U.S.A.

DANFOSS DRIVES A/S
ULSNAES 1
6300 GRAASTEN
DANMARK

Remarks:

- The products fulfill EC-Code: EC21.
- All changes in software are to be recorded as long as the system is in use on board. Major changes in the software are to be approved before being installed in the converter.
- Converters EMC classed C3 according to IEC 61800-3 can be installed in "special distribution zone" and "general power distribution zone" in accordance with IEC 60533 provided precautions are taken to attenuate these effects on the distribution system, so the safe operation is assured.

This certificate replaces and annuls the previous certificate ELE173322XG/003.

HAMBURG November 16, 2022

