



CERTIFICATE

必维认证集团认证控股有限公司英国分公司确证下述组织的管理体系

丹佛斯（天津）有限公司

总部运营地址：中国天津武清开发区泉汇路 9 号

总部注册地址：中国天津武清开发区福源道 5 号

统一社会信用代码：911202226008919279

此份为多场所证书，各分场所见证书附页

已经评审并确认符合下列管理体系标准全部适用条款的要求

ISO 45001:2018

体系覆盖范围：

总范围：热力膨胀阀，电子膨胀阀，管路元件，电磁阀，工业制冷阀门，组件，压力传感器和温度传感器的设计、开发、制造、以及解决方案和相关服务。商用压缩机及其涡旋和壳体的设计，开发，制造，以及解决方案和相关服务。

证书编号：

CN057946

最初认证周期起始日期：

25-12-2020

本次认证周期起始日期：

20-11-2025

到期日：

25-11-2028

（在证书持有者之管理体系持续符合要求的运行条件下）

版本号：No.1

发证日期：

20-11-2025

必维认证集团认证控股有限公司英国分公司
授权代表



0008



认证机构地址：5th Floor, 100 Lower Thames Street, London, EC3R 6DL, United Kingdom

当地办公室地址：必维认证（北京）有限公司，中国北京市东城区东长安街1号东方广场西一办公楼9层902室，邮编：100738

*OHSAS 18001: 2007 最初认证周期起始日期：26-11-2019

需进一步澄清本证书范围和有效状态，以及此管理体系要求的适用性，请电：+86 10 59683663

获证组织必须定期接受监督审核并经审核合格此证书方继续有效。本证书信息可在国家认证认可监督管理委员会官方网站(www.cnca.gov.cn)上查询。

CER CERTIF ALL TPL 002 Rev 4.4

CERTIFICATE

丹佛斯（天津）有限公司

ISO 45001:2018

体系覆盖范围：

场所名称	场所地址	场所认证范围
丹佛斯（天津）有限公司	运营地址：中国天津武清开发区泉汇路9号 注册地址：中国天津武清开发区福源道5号	热力膨胀阀，电子膨胀阀，管路元件，电磁阀，工业制冷阀门，组件，压力传感器和温度传感器的设计、开发、制造、以及解决方案和相关服务。
丹佛斯（天津）有限公司	中国天津武清开发区福源道5号	商用压缩机及其涡旋和壳体的设计，开发，制造，以及解决方案和相关服务。

证书编号：

CN057946

版本号：No.1

发证日期：

20-11-2025



必维认证集团认证控股有限公司英国分公司
授权代表



0008

认证机构地址：5th Floor, 100 Lower Thames Street, London, EC3R 6DL, United Kingdom

当地办公室地址：必维认证（北京）有限公司，中国北京市东城区东长安街1号东方广场西一办公楼9层902室，邮编：100738

*OHSAS 18001: 2007 最初认证周期起始日期：26-11-2019

需进一步澄清本证书范围和有效状态，以及此管理体系要求的适用性，请电：+86 10 59683663

获证组织必须定期接受监督审核并经审核合格此证书方继续有效。本证书信息可在国家认证认可监督管理委员会官方网站(www.cnca.gov.cn)上查询。

CER CERTIF ALL TPL 002 Rev 4.4



CERTIFICATE

Bureau Veritas Certification Holding SAS - UK Branch certifies that the Management System of

Danfoss (Tianjin) Ltd.

Head Office Operation Address: No.9 Quanhui Road, Wuqing Development Area, Tianjin, P.R.C

Head Office Registration Address: No.5 Fuyuan Road, Wuqing Development Area, Tianjin, P.R.C

Unified social credit code: 911202226008919279

This is a multi-site certificate, additional site(s) are listed on the next page(s).

has been audited and found to be in accordance with the requirements of the management system standards detailed below

ISO 45001:2018

Scope of certification:

Overall: Design, development, manufacturing, solution and related service of Thermostatic Expansion Valves (TXV), Electronic Expansion Valves (EEV), Line Components (LC), Solenoid Valves (SV), Industrial Refrigeration Valves (IR), Modules, Pressure Sensor and Temperature Sensor (IA). Design, development, manufacturing, solution and related service of commercial compressors (CC), scroll and shell of Commercial Compressors (CC).

Certificate number:

CN057946

Original certification date:

25-12-2020

Current cycle start date:

20-11-2025

Expiry date:


25-11-2028

(Subject to the continued satisfactory operation of the organisation's Management System)

Version N: No.1

Issue date:

20-11-2025



Signed on behalf of BVCH SAS UK Branch



0008

Certification body address: 5th Floor, 100 Lower Thames Street, London, EC3R 6DL, United Kingdom

Local office address: Bureau Veritas Certification (Beijing) Co., Ltd, Room 02, 9 / F, West Office Building 1, Oriental Economic and Trade City, Oriental Plaza, No.1 East Chang'an Street, Dongcheng District, Beijing, China. 100738

*OHSAS 18001: 2007 Original Cycle Start Date: 26-11-2019

Further clarifications regarding the scope and validity of this certificate, and the applicability of the management system requirements, please call: +86 10 59683663

Certified organisation has to accept and pass regular surveillance audits, then this certificate can be continuously valid. Information of this certificate may be obtained by visiting CNCA website (www.cnca.gov.cn).

CER CERTIF ALL TPL 002 Rev 4.4





BUREAU
VERITAS

CERTIFICATE

Danfoss (Tianjin) Ltd.

ISO 45001:2018

Scope of Certification:

Site Name	Site Address	Site Scope
Danfoss (Tianjin) Ltd.	Operation Address: No.9 Quanhui Road, Wuqing Development Area, Tianjin, P.R.C Registration Address: No.5 Fuyuan Road, Wuqing Development Area, Tianjin, P.R.C	Design, development, manufacturing, solution and related service of Thermostatic Expansion Valves (TXV), Electronic Expansion Valves (EEV), Line Components (LC), Solenoid Valves (SV), Industrial Refrigeration Valves (IR), Modules, Pressure Sensor and Temperature Sensor (IA).
Danfoss (Tianjin) Ltd.	No.5 Fuyuan Road, Wuqing Development Area, Tianjin, P.R.C	Design, development, manufacturing, solution and related service of commercial compressors (CC), scroll and shell of Commercial Compressors (CC).

Certificate number:
CN057946

Version N: No.1

Issue date:
20-11-2025

Signed on behalf of BVCH SAS UK Branch



0008

Certification body address: 5th Floor, 100 Lower Thames Street, London, EC3R 6DL, United Kingdom
Local office address: Bureau Veritas Certification (Beijing) Co., Ltd, Room 02, 9 / F, West Office Building 1, Oriental Economic and Trade City, Oriental Plaza, No.1 East Chang'an Street, Dongcheng District, Beijing, China. 100738

***OHSAS 18001: 2007 Original Cycle Start Date:** 26-11-2019

Further clarifications regarding the scope and validity of this certificate, and the applicability of the management system requirements, please call: +86 10 59683663

Certified organisation has to accept and pass regular surveillance audits, then this certificate can be continuously valid. Information of this certificate may be obtained by visiting CNCA website (www.cnca.gov.cn).

