



**TYPE APPROVAL CERTIFICATE**  
No. ELE012726XP/001

**This is to certify** that the product below is found to be in compliance with the applicable requirement of the RINA type approval system.

<i>Description</i>	<b>FREQUENCY CONVERTERS</b>
<i>Type</i>	<b>Series FC-102</b>
<i>Applicant</i>	<b>DANFOSS POWER ELECTRONICS A/S ULSNAES 1 DK-6300 GRAASTEN DENMARK</b>
<i>Manufacturer</i>	<b>DANFOSS, LLC</b>
<i>Place of manufacture</i>	<b>4401 N. BELL SCHOOL RD., 61111 LOVES PARK (IL), U.S.A ULSNAES 1, DK-6300 GRAASTEN, DENMARK</b>
<i>Reference standards</i>	<b>Rules for the classification of ships.- Part C - Machinery, systems and fire protection. - Ch.3, Sect. 6, Table 1</b>

Issued in **RINA Poland Marine** on **February 18, 2026**. This Certificate is valid until **February 17, 2031**

*B. Mejer*

ON BEHALF OF  
**RINA Services S.p.A.**  
*Adam Mejer*



This certificate consists of this page and 1 enclosure



**TYPE APPROVAL CERTIFICATE**

**No. ELE012726XP/001**

**Enclosure - Page 1 of 1**

**Series FC-102**

**Product description:**

The VLT<sup>®</sup> HVAC Drive Series FC-102 series are frequency converter for asynchronous motors for use in various marine applications.

FC-102: 200-240V

Power Rating [kW]	Enclosure type			
	IP20 (*1)	IP21 (*2)	IP55 (*3)	IP66 (*4)
FC-102				
1,1	A2	A2 (*5)	A4+A5	A4+A5
1,5				
2,2				
3,0	A3	A3 (*5)	A5	A5
3,7				
5,5	B3	B1	B1	B1
7,5				
11				
15	B4	B2	B2	B2
18,5		C1	C1	C1
22	C3			
30				
37	C4	C2	C2	C2
45				

FC-102: 380-480/500V

Power rating [kW]	Enclosure type			
	IP20 (*1)	IP21 (*2)	IP55 (*3)	IP66 (*4)
FC-102				
1,1	A2	A2 (*5)	A4+A5	A4+A5
1,5				
2,2				
3,0	A3	A3 (*5)	A5	A5
4,0				
5,5	B3	B1	B1	B1
7,5				
11				
15	B4	B2	B2	B2
18,5				
22	C3	C1	C1	C1
30				
37	C4	C2	C2	C2
45				
55	C4	C2	C2	C2
75				
90				

**TYPE APPROVAL CERTIFICATE**

**No. ELE012726XP/001**

**Enclosure - Page 2 of 4**

**Series FC-102**

FC-102: 525-690V

Power rating [kW]	Enclosure type			
	IP20 (*1)	IP21 (*2)	IP55 (*3)	IP66 (*4)
FC-102	IP20 (*1)	IP21 (*2)	IP55 (*3)	IP66 (*4)
1,1	A3	NA	NA	NA
1,5				
2,2				
3,0				
3,7				
5,5				
7,5				
11	B4	B2	B2	B2
15				
18				
22				
30				
37				
45	C3	C2	C2	C2
55				
75	D3h	C2	C2	C2
90				

(\*1) IP20/Panel mount. All IP20 versions can be upgraded to IP21 with optional kit

(\*2) IP21/NEMA Type 1

(\*3) IP55/NEMA Type 12

(\*4) IP66/NEMA Type 4X

(\*5) IP20/Panel with IP21 upgrade kit

FC-102: 380-480/500V

Power rating [kW]	Enclosure type				
	6-pulse			12-pulse	Low Harmonic Drive (LHD)
FC-102	IP00 (*1)	IP20 (*1)	IP21 / IP54 (*2)		
110	NA	D3H	D1h/D5h/D6h	NA	NA
132					
160		D4h	D2h/D7h/D8h		
200				E2, E3h	E3h
250		E4h	E4h		
315					
355	NA			NA	F1/F3
400					
450	NA	NA	F2/F4	F12/F13	NA
500					
560	NA	NA	F1/F3	F12/F13	NA
630					
710					
800	NA	NA	F2/F4	F12/F13	NA
1000					



**TYPE APPROVAL CERTIFICATE**

**No. ELE012726XP/001**

**Enclosure - Page 3 of 4**

**Series FC-102**

FC-102: 525-690V

Power rating [kW]	Enclosure type				
	6-pulse			12-pulse	
FC-102	IP00 (*1)	IP20 (*1)	IP21 / IP54 (*2)		
75	NA	D3h	D1h/D5h/D6h		
90					
110					
132					
160					
200		D4h	D2h/D7h/D8h		
250					
315	E2, E3h	E3h	E1/E1h		
400					
450					
500					
560	E4h	E4h	F1/F3/E2h		
630					
710	NA	NA	F1/F3		
800					
900			F2/F4		F10/F11
1000					
1200			F12/F13		
1400					

(\*1) IP00/IP20/Panel mount.

(\*2) IP21/NEMA Type 1; IP54/NEMA Type 12

**Technical data:** (In accordance with Danfoss design guide)

Power supply: 200-240V / 380-480V / 525-690V, 50/60Hz

Voltage variation: +10 %, -15% reduced power rating

Frequency variation: A, B and C frames: +-10%; D, E and F frames: +-5%

Output frequency: A, B and C frames: 0 - 590 Hz; D, E and F frames: 0 - 590 Hz

Temperature range in operation: 0 - 45°C, 46-55°C derating according to relevant design guide.

Protection class: IP00 / 20 / 21 / 54 / 55 / 66

**Documents and drawings:**

User manuals: - MG16O102 dated 01/2017; MG22A102 dated 01/2017; MG38A102 dated 01/2017;

Drawings: - 177r0659 dated 9/15/16; 177r0704 dated 06/24/2020; 177r0705 dated 06/24/2020; 177r0706 dated 06/24/2020;

- 177r0707 dated 06/25/2020;

**Test reports:**

Checklist for visual inspection 4001PRT2 00734665 Rev. 2.10 dated 2017-01-18;

Danfoss A/S: - 00715502 Rev. A dated 2013-07-30; 00734306 Rev. A dated 2017-01-12; 00734307 Rev. A dated 2017-01-13;

- 00734308 Rev. A dated 2017-01-13; 00734309 Rev. A dated 2017-01-13; 00734724 dated 2017-01-26;

- 00735629 Rev. A dated 2017-03-16; 00735840 dated 2017-03-27; P4001 dated 3/15/2017;

- P4001 Rev. A dated 2017-01-10; P7020 dated 2015-07-10; tr4001 dated 12-09-16; PEC-4639 dated 19-10-2021; PEC-4640

dated 24-09-2021; PEC-4679 dated 28-09-2021; PEC-4680 dated 05-10-2021; PEC-4681 dated 13-10-2021; PEC-4682 dated 15-10-2021;

Datasyst Engineering & Testing Services Inc.: - D15-15766 Rev. A dated July 29,2013; D15-17445 dated August 17,2016;

Elite Electronic Engineering Inc.: - 1604970-01 Rev.B dated January 17, 2017;

TÜV Rheinland: - 19645766001 dated 11 Jan 2017; 19645767001 dated 11 Jan 2017;

UL: - 00733941; 11494250A dated December 16,2016; 11494250B dated December 16,2016;

- 4786962025-S1-1 dated 9 July 2015; Break Down of Component\_Test DataSheet;

RINA Services S.p.A.  
Via Corsica, 12 - 16128 Genova  
Tel +39 010 53851  
Fax +39 010 5351000



**TYPE APPROVAL CERTIFICATE**

No. **ELE012726XP/001**

Enclosure - Page 4 of 4

Series FC-102

**Manufacturing sites:**

DANFOSS, LLC  
4401 N. BELL SCHOOL RD  
61111 LOVES PARK (IL)  
U.S.A.

DANFOSS DRIVES OY  
RUNSORINTIE 7  
65380 VAASA  
FINLAND

DANFOSS DRIVES A/S  
ULSNAES 1  
6300 GRAASTEN  
DANMARK

ZHEJIANG HOLIP ELECTRONIC TECHNOLOGY Co., Ltd  
#339 NORTH XINQIAO ROAD, WUYUAN  
STREET HAIYAN COUNTY, JIAXING CITY,  
ZHEJIANG PROVINCE, 314300 HAIYAN,  
CHINA

**Remarks:**

- The products fulfill EC-Code: EC21.
- All changes in software are to be recorded as long as the system is in use on board. Major changes in the software are to be approved before being installed in the converter.
- Converters EMC classed C3 according to IEC 61800-3 can be installed in "special distribution zone" and "general power distribution zone" in accordance with IEC 60533 provided precautions are taken to attenuate these effects on the distribution system, so the safe operation is assured.

*This certificate replaces and annuls the previous certificate ELE173322XG/001.*

**RINA Poland Marine February 18,  
2026**

RINA Services S.p.A.  
Via Corsica, 12 - 16128 Genova  
Tel +39 010 53851  
Fax +39 010 5351000

