

## Data Sheet

# RA-C Valves for Cooling and Heating Circuits

### Products



RA-C 15 cooling valve



RA-C 20 cooling valve

Together with Danfoss selfacting and electronic controls, RA-C valves make up a perfect combination for control of cooling and heating circuits.

The RA-C valve is a normally open valve. In an application with self-acting sensors type FEK or FED it is ensured that the cooling valve opens when the room temperature is rising above the set temperature.

The RA-C valve has 4 presettings, thus the correct quantity of water is ensured for each cooling circuit and it is PN16 approved.

The valve has two external threads thus fittings for various pipe types may be mounted.

Moreover, Danfoss can also offer a comprehensive range of fittings (see back page).

### Ordering and Specifications

Valve	Con- nec- tions	Presettings: $k_v$ -value <sup>1)</sup> , m <sup>3</sup> /h				$k_{vs}$	Max. work. press. <sup>3)</sup>	Max. diff. press. <sup>2)</sup>	Test press.	Water temp.	Code no.
		1	2	3	N						
RA-C 15	2 x G ¾ A	0.30	0.55	0.75	0.90	1.20	16 bar	0.6 bar	24 bar	-10 - 120 °C	013G3094
RA-C 20	2 x G 1 A	0.80	1.10	1.70	2.60	3.30					013G3096

<sup>1)</sup> The  $k_v$ -values show the flow (Q) in m<sup>3</sup>/h at a differential pressure ( $\Delta p$ ) of 1 bar through the valve. At presetting N the  $k_v$ -value is shown at  $X_p = 3$  K. The  $X_p$ -value decreases at lower presettings thus the  $k_v$ -value at presetting 1 is shown at  $X_p = 1$  K.


<sup>2)</sup> The max. differential pressure specified is the maximum pressure at which the valves give satisfactory regulation. As with any device which imposes a pressure drop on the system, noise may occur under certain flow/pressure conditions. A differential pressure between 0.1 and 0.3 bar across the valves is recommended. The differential pressure can be reduced using Danfoss differential pressure regulators.

<sup>3)</sup> Shut-off PN10 approved.

**Presetting**


With the valve body type RA-C the calculated setting can be set easily and exactly without using special tools:

- remove the protective cap or sensor element,
- raise the setting ring,
- turn the scale on the setting ring until the required scale value faces the reference mark,
- release the setting ring.



The presetting can be set at the values: 1- 2 - 3 and N. At setting N, the valve is completely open.

A setting in the shaded areas should be avoided. When the sensor element is mounted, the presetting is hidden, and is thus protected against alteration.



1. Presetting range

**Pressure and Noise Conditions**


Special demands are made on the various components of the system. This is due to water temperature conditions, the chosen pipe types and pipe dimensions of both chilled ceilings and fancoils/induction units and the structure of the cooling circuits.

The RA-C valve has especially been designed to correspond to these demands, no matter whether selfacting or electronic controls are used.


In chilled ceilings and fancoils/induction-units relatively large differential pressure and water flow are often used compared to normal heating systems. This may lead to noise nuisance.

**Design**

**RA-C 15**




**RA-C 20**




1. Gland seal
2. O-ring
3. Pressure pin
4. Seal
5. Regulation spring
6. Presetting bush
7. Valve body
8.  $k_v$ -nozzle

Dimensions

RA-C 15



RA-C 20




Materials in contact with water


Valve body and other metal parts	Corrosion resistant brass
Spindle	Corrosion resistant brass
Throttle nozzle	PPS
O-ring	EPDM
Valve cone	NBR
Gland seal pressure pin	Chrome steel
k <sub>v</sub> -nozzle	PP

Capacities

RA-C 15



RA-C 20



**Sizing example, chilled ceiling**

Cooling demand:	Φ = 0.55 kW
System temperature rise:	Δt = 2 °C
Differential pressure:	Δp = 0.1 bar
Calculated water quantity:	$Q = \frac{550}{2 \times 1.16} = 237 \text{ l/h}$

The setting is found in the capacity diagramme:

RA-C 15: Presetting value 3


RA-C 20: Presetting value 1

Capacities with P-band between 1 and 3 K.

**Accessories: Compression Fittings**

**Compression fittings for PEX plastic tubing**

Compression fittings are for connecting Danfoss valves to circuits in heating systems only. Compression fittings are used for connecting PEX plastic tubings in accordance with DIN 16892/16893. Maximum operating pressure and temperature are given by the tubing manufacturer. However, 10 bar and 95° C must not be exceeded. One set consists of one olive, one supporting bush and one union nut.



For PEX plastic tubing Connection	Tube dimension	Max. working pressure	Test pressure	Max. flow temperature	Code no.
G 3/4", internal thread	12 x 2 mm	6 bar	10 bar	95 °C	013G4152
	13 x 2 mm	6 bar	10 bar	95 °C	013G4153
	14 x 2 mm	6 bar	10 bar	95 °C	013G4154
	15 x 2.5 mm	6 bar	10 bar	95 °C	013G4155
	16 x 1.5 mm	6 bar	10 bar	95 °C	013G4157
	16 x 2 mm	6 bar	10 bar	95 °C	013G4156
	16 x 2.2 mm	6 bar	10 bar	95 °C	013G4163
	17 x 2 mm	6 bar	10 bar	95 °C	013G4162
	18 x 2 mm	6 bar	10 bar	95 °C	013G4158
	18 x 2.5 mm	6 bar	10 bar	95 °C	013G4159
	20 x 2 mm	6 bar	10 bar	95 °C	013G4160
	20 x 2.5 mm	6 bar	10 bar	95 °C	013G4161

**Compression fittings for Alupex tubing**

Compression fittings are for connecting Danfoss valves to circuits in heating systems only. When connecting circuits with compression fittings for Alupex tubing, always observe the maximum operating pressure and temperature which are given by the tubing manufacturer. However, 10 bar and 95° C must not be exceeded.

One set consists of one olive, one supporting bush, one insulation washer and one union nut.



External thread


Internal thread

For Alupex tubing Connection	Tube dimension	Max. working pressure	Test pressure	Max. flow temperature	Code no.
G 3/4", internal thread	12 x 2 mm	6 bar	10 bar	95 °C	013G4182
	14 x 2 mm	6 bar	10 bar	95 °C	013G4184
	15 x 2.5 mm	6 bar	10 bar	95 °C	013G4185
	16 x 2 mm	6 bar	10 bar	95 °C	013G4186
	16 x 2.25 mm	6 bar	10 bar	95 °C	013G4187
	18 x 2 mm	6 bar	10 bar	95 °C	013G4188
	20 x 2 mm	6 bar	10 bar	95 °C	013G4190
	20 x 2.5 mm	6 bar	10 bar	95 °C	013G4191

**Compression fittings for steel and copper tubing**

Compression fittings are for connecting Danfoss valves to circuits in heating systems only. Compression fittings are used for connecting steel and copper pipes in accordance with DIN 1786/2391.

One set consists of one olive and one union nut. It is recommended to use supporting bushes with soft pipes.



For steel and copper tubing Connection	Tube dimension	Max. working pressure	Test pressure	Max. flow temperature	Code no.
G 3/4", internal thread	10 mm	16 bar	24 bar	120 °C	013G4120
	12 mm	16 bar	24 bar	120 °C	013G4122
	14 mm	16 bar	24 bar	120 °C	013G4124
	15 mm	16 bar	24 bar	120 °C	013G4125
	16 mm	16 bar	24 bar	120 °C	013G4126
	18 mm	16 bar	24 bar	120 °C	013G4128
G 1"	18 mm	16 bar	24 bar	120 °C	013U0134
	22 mm	16 bar	24 bar	120 °C	013U0135



Danfoss A/S  
Heating Solutions  
Haarupvaenget 11  
8600 Silkeborg  
Denmark  
Phone: +45 7488 8000  
Fax: +45 7488 8100  
Email: [heating.solutions@danfoss.com](mailto:heating.solutions@danfoss.com)  
[www.heating.danfoss.com](http://www.heating.danfoss.com)

---

Danfoss can accept no responsibility for possible errors in catalogues, brochures and other printed material. Danfoss reserves the right to alter its products without notice. This also applies to products already on order provided that such alterations can be made without subsequential changes being necessary in specifications already agreed. All trademarks in this material are property of the respective companies. Danfoss and the Danfoss logotype are trademarks of Danfoss A/S. All rights reserved.

---