

Data sheet

Pressure transmitter for general industrial purposes

MBS 3000 and MBS 3050



The compact pressure transmitter, type MBS 3000, is designed for use in industrial and hydraulic applications, and offers a reliable pressure measurement, even under harsh environmental conditions.


The compact heavy duty pressure transmitter MBS 3050 with integrated pulse-snubber is designed for use in hydraulic applications with severe medium influences like cavitation, liquid hammer or pressure peaks and offers a reliable pressure measurement, even under harsh environmental conditions.

The flexible pressure transmitter programme covers different output signals, absolute or gauge (relative) versions, measuring ranges from 0–1 to 0–600 bar. A wide range of pressure and electrical connections are available.

Excellent vibration stability, robust construction, and a high degree of EMC/EMI protection equip the pressure transmitter to meet the most stringent industrial requirements.

Features

- Designed for use in severe industrial and hydraulic environments
- Resistant to cavitation, liquid hammer and pressure peaks (MBS 3050)
- Enclosure and wetted parts of acid-resistant stainless steel (AISI 316L)
- Pressure ranges in relative (gauge) or absolute from 0 up to 600 bar
- All standard output signals: 4 – 20 mA, 0 – 5 V, 1 – 5 V, 1 – 6 V, 0 – 10 V, 1 – 10 V, Ratiometric output signal: 10-90% of supply voltage
- A wide range of pressure and electrical connections
- Fully digitally compensated
- For use in ATEX zone 2 explosive atmospheres
- UL approved

Application and media conditions for MBS 3050

Application

Cavitation, liquid hammer and pressure peaks may occur in hydraulic systems with changes in flow velocity, e.g. fast closing of a valve or when a pump starts and stops.

The problem may occur on the inlet and outlet side of the application, even at rather low operating pressures.

Media condition

Clogging of the nozzle may occur in liquids containing particles. Mounting the transmitter in an upright position minimizes the risk of clogging, because the flow in the nozzle is limited to the start-up period until the dead volume behind the nozzle orifice is filled. The media viscosity has only little effect on the response time. Even at a viscosities up to 100 cSt, the response time will not exceed 4 ms.

Technical data
Performance (EN 60770)

Accuracy (incl. non-linearity, hysteresis and repeatability)	$\leq \pm 0.5\%$ FS (typ.)	
	$\leq \pm 1\%$ FS (max.)	
Non-linearity BFSL (conformity)	$\leq \pm 0.2\%$ FS	
Hysteresis and repeatability	$\leq \pm 0.1\%$ FS	
Thermal zero point shift	$\leq \pm 0.1\%$ FS / 10K (typ.)	
	$\leq \pm 0.2\%$ FS / 10K (max.)	
Thermal sensitivity (span) shift	$\leq \pm 0.1\%$ FS / 10K (typ.)	
	$\leq \pm 0.2\%$ FS / 10K (max.)	
Response time	Liquids with viscosity < 100 cSt	< 4 ms
	Air and gases (MBS 3050)	< 35 ms
Overload pressure (static)	6 × FS (max. 1500 bar)	
Burst pressure	6 × FS (max. 2000 bar)	
Power-up time	< 50 ms	
Durability, P: 10 – 90% FS	> 10 × 10 ⁶ cycles	

Electrical specifications

Nom. output signal (short-circuit protected)	4 – 20 mA	0–5, 1–5, 1–6 V	0–10 V, 1–10 V	Ratiometric 10 – 90% of [U _B]
Supply voltage [U _B], polarity protected	9–32 V DC	9–32 V DC	15–32 V DC	4.5 – 5.5 V DC
Supply – current consumption	–	≤ 5 mA	≤ 8 mA	≤ 5 mA at 5 V DC
Supply voltage dependency	< 0.1% FS / 10 V	< 0.05% FS / 10 V		--
Ratiometricity	-	-		< 0.05% FS / 4.5 - 5.5 V
Output limitation	22.4 mA	0-5V: 5.75 V 1-5V: 5.6 V 1-6V: 6.75 V	0-10V: 11.5 V	≈ supply voltage
Sink / Source	–	< 1 mA		
Load [R _L] (load connected to 0 V)	R _L \leq (U _B - 9V) / 0.02 A	R _L \geq 10 kΩ	R _L \geq 15 kΩ	R _L \geq 10 kΩ at 5 V DC

Technical data
(continued)
Environmental conditions

Sensor operating temperature	Normal	-40 – 85 °C	
	ATEX Zone 2	-10 – 85 °C	
Media temperature range		-40 – 85 °C	
Ambient temperature range (depending on electrical connection)		See page 6	
Compensated temperature range		0 – 80 °C	
Transport/storage temperature range		-50 – 85 °C	
EMC – Emission		EN 61000-6-3	
EMC – Immunity		EN 61000-6-2	
Insulation resistance		> 100 MΩ at 500 V DC	
Mains frequency test		Based on SEN 361503	
Vibration stability	Sinusoidal	15.9 mm-pp, 5 Hz – 25 Hz	IEC 60068-2-6
		20 g, 25 Hz – 2 kHz	
	Random	7.5 g _{rms} , 5 Hz – 1 kHz	IEC 60068-2-64
Shock resistance	Shock	500 g / 1 ms	IEC 60068-2-27
	Free fall	1 m	IEC 60068-2-32
Enclosure (depending on electrical connection)		See page 6 & 7	

Explosive atmospheres


Zone 2 applications	II 3G Ex nA IIA T3 Gc -10 °C < Ta < +85 °C	EN60079-0; EN60079-15
---------------------	-----------------------------------------------------------------------------	-----------------------

When used in ATEX Zone 2 areas at low temperatures the cable and plug must be protected against impact.

Mechanical characteristics

Materials	Wetted parts	EN 10088-1; 1.4404 (AISI 316 L)
	Enclosure	EN 10088-1; 1.4404 (AISI 316 L)
	Electrical connections	See page 6 & 7
Net weight (depending on pressure connection and electrical connection)		0.2 – 0.3 kg


Ordering standard



Non-standard build-up combinations may be selected. However, minimum order quantities may apply. Please contact your local Danfoss office for further information.

Dimensions/Combinations








Type code	A1	A3	E3	A8	A6	C8	D9	G1
	ENI 175301-803-A, Pg 9	2 m screened cable	EN 60947-5-2, M12 x 1; 4-pin	AMP Superseal	EN 175301-803-A, Pg 11	ISO 15170-A1-3.2-SN	AMP 173065, male, Flying leads	AMP Econoseal



Type code	AB04	AB06	AB08	AC04	AC08	GB04	FA09	FA12	FD10
	G 1/4 A (EN 837)	G 3/8 A (EN 837)	G 1/2 A (EN 837)	1/4 – 18 NPT	1/2 – 14 NPT	DIN 3852-E-G 1/4 R	DIN 3852-E-M14 x 1.5	DIN 3852/3, M 18 x 1.5 – 6 g	5/8–18 UNF-2A (SAE J514)
	30 – 35 Nm	30 – 35 Nm	30 – 35 Nm	2 – 3 turns after finger tightened	2 – 3 turns after finger tightened	30 – 35 Nm	30 – 35 Nm	30 – 35 Nm	30 – 35 Nm

1) Depends on different parameters such as gasket material, mating material, thread lubrication and pressure level

Electrical connections




Type code	A1 & A6	A3	E3	A8
	 <p>EN 175301-803-A, Pg 9 & Pg 11</p>	 <p>2 m screened cable</p>	 <p>EN 60947-5-2 M12 x 1; 4-pin</p>	 <p>AMP Superseal 1.5 series (male)</p>
Ambient temperature	-40 – 85 °C	-30 – 85 °C	-25 – 90 °C	-30 – 85 °C
Enclosure (IP protection fulfilled together with mating connector)	IP65	IP67	IP67	IP67
Material	Glass filled polyamid, PA 6.6 ¹⁾	Poliolyfin cable with PE shrinkage tubing	Nickel plated brass, CuZn/Ni	Glass filled polyamid, PA 6.6 ²⁾
Electrical connection, 4 – 20 mA output (2 wire)	Pin 1: + supply Pin 2: ÷ supply Pin 3: not used  Earth: Connected to MBS enclosure	Brown wire: + supply Black wire: ÷ supply Red wire: not used Orange: not used Screen: not connected to MBS enclosure	Pin 1: + supply Pin 2: not used Pin 3: not used Pin 4: ÷ supply	Pin 1: + supply Pin 2: ÷ supply Pin 3: not used
Electrical connection, 0 – 5 V, 1 – 5 V, 1 – 6 V, 0 – 10 V, 1 – 10 V output	Pin 1: + supply Pin 2: ÷ supply/common Pin 3: + output  Earth: Connected to MBS enclosure	Brown wire: + output Black wire: ÷ supply Red wire: + supply Orange: not used Screen: not connected to MBS enclosure	Pin 1: + supply Pin 2: not used Pin 3: + output Pin 4: ÷ supply/common	Pin 1: + supply Pin 2: ÷ supply/common Pin 3: + output
Electrical connection Ratiometric output, 10-90% of supply voltage	Pin 1: + supply Pin 2: ÷ supply Pin 3: output/common  Earth: Connected to MBS enclosure	Brown wire: output Black wire: ÷ supply Red wire: Common ³⁾ Orange: Not used Screen: Not connected to MBS enclosure	Pin 1: + supply Pin 2: Not used Pin 3: output Pin 4: ÷ supply/Common	Pin 1: + supply Pin 2: ÷ supply Pin 3: output/Common

¹⁾ Female plug: Glass filled polyester, PBT

²⁾ Wire: PTFE (teflon) Protection sleeve: PBT mesh (polyester)

³⁾ Common

**Electrical connections
continued**

Type code	C8	D9	G1
	 <p>ISO 15170-A1-3.2-Sn Bayonet</p>	 <p>AMP 173065, male Flying leads 125 mm</p>	 <p>AMP Econoseal J series (male)</p>
Ambient temperature	-40 – 85 °C	-40 – 85 °C	-30 – 85 °C
Enclosure (IP protection fulfilled together with mating connector)	IP67/IP69	IP67	IP67
Material	Glass filled polyester PBT ¹⁾	Glass filled polyester, PBT ²⁾	Glass filled polyamide, PA 6.6 ¹⁾
Electrical connection, 4 – 20 mA output (2 wire)	-	Pin 1: + supply Pin 2: - supply Pin 3: not used	Pin 1: + supply Pin 2: ÷ supply/common Pin 3: not used
Electrical connection, 0 – 5 V, 1 – 5 V, 1 – 6 V, 0 – 10 V, 1 – 10 V output	-	Pin 1: + supply Pin 2: - supply Pin 3: + output	Pin 1: + supply Pin 2: ÷ supply/Common Pin 3: + output
Electrical connection Ratiometric output, 10-90% of supply voltage	Pin 1: + supply Pin 2: ÷ supply/common Pin 3: + output Pin 4: Not used	-	Pin 1: + supply Pin 2: ÷ supply/common Pin 3: + output

¹⁾ Female plug: Glass filled polyester, PBT

²⁾ Wire: PTFE (teflon) Protection sleeve: PBT mesh (polyester)