

Infographic

Actuator selection for PICVs

An interactive selection for all Danfoss AB-QM PICV valves

Pressure Independent Control Valves (PICVs) are commonly used for hydronic balancing and precise temperature control in HVAC heating and cooling systems. The control accuracy, controllers to be used, project price and many more aspects are mostly determined by the selection of the PICV actuator.

There are many actuators that fit the Danfoss AB-QM series of PICV valves. This interactive infographic helps you find the best suited actuator for your projects.

Continue by clicking the buttons below:

Small combinations
DN 15 - DN 32




Large combinations
DN 125 - DN 150



Medium combinations
DN 40 - DN 100



X-large combinations
DN 200 - DN 250



Small combinations for terminal units

AB-QM valves size S

AB-QM

DN	Qmin.	Qnom.
25	340 l/h	1700 l/h
25 HF	540 l/h	2700 l/h
32	640 l/h	3200 l/h
32 HF	800 l/h	4000 l/h

[Go to datasheet](#)



Why choose?

- pressure independent control performance
- high accuracy control at full- and partial load conditions
- for heating and cooling systems
- increase HVAC system efficiency



[Back to front page](#)



[Actuators size S](#)



Actuators size S - specifications

The overview shows the most common used actuators for AB-QM PICVs.
For special needs or applications contact our local Sales representative.

Control principle	Digital	Modulating / Floating			On-off	
Actuator principle	Step motor	Gear		Thermal	Gear	Thermal
Why choose?	- connectivity & data - HVAC 4.0 - BMS integration - high accuracy - remote possibilities	- high accuracy - high quality	high quality	low noise operation	- high quality - speed	- low-price - PWM - complete series
Actuator	NovoCon® S	AME 110/120 NL(X)	AMV 110/120 NL	ABNM A5	AMI 140	TWA-Q
						
Specification summary						
Control signals	BACnet; Modbus; 0-10V; 4-20mA	0-10V; 4-20mA	3-point	0-10V	on-off 24/230V AC	on-off (PWM) 24/230V AC/DC
Power supply	24V AC/DC	24V AC	24V AC	24V AC/DC	24/230V AC	24/230V AC/DC
Feedback signal	BACnet; Modbus	x-signal	--	--	--	--
Speed	24/12/6/3 sec./mm	24/12 sec./mm	24/12 sec./mm	30 sec./mm	12 sec./mm	30 sec./mm
Characteristic	Logarithmic / Linear	Logarithmic / Linear	--	Logarithmic / Linear	--	--
Valve open/close detection	yes	yes	yes	yes	no	no
Cable	plug-in	standard	standard	plug-in	standard	standard
Mounting adapter	--	--	--	VA41 (incl.)	--	--
IP class	IP54	IP42	IP42	IP54	IP42	IP54
Options & accessories						
Power cable lengths	1.5/5/10 m	1.5/5/10 m	1.5/5/10 m	1/5/10 m	1.5/5 m	1.2/2/5 m
Daisy-chain cable length	0.5/1.5/5/10 m	--	--	--	--	--
Halogen free cables	standard	standard	standard	standard	standard	optional
DC power supply	standard	--	--	optional	--	standard
Expand features	energy cable; remote I/O cable; ChangeOver [®] actuator					
	Go to datasheet >	Go to datasheet >	Go to datasheet >	Go to datasheet >	Go to datasheet >	Go to datasheet >

[Back to front page](#) >



[AB-QM size M](#) >

Medium combinations for air handling units

AB-QM valves size M

AB-QM NovoCon® for NovoCon M actuator

DN	Qmin.	Qnom.
40 (G 2A)	3 m³/h	7,5 m³/h
50 (G 2 ½A)	5 m³/h	12,5 m³/h
50	5 m³/h	12,5 m³/h
65	8 m³/h	20 m³/h
65 HF	10 m³/h	25 m³/h
80	11,2 m³/h	28 m³/h
80 HF	16 m³/h	40 m³/h
100	15,2 m³/h	38 m³/h
100 HF	23,6 m³/h	59 m³/h

[Go to datasheet](#)



[Back to front page](#)



Why choose?

- pressure independent control performance
- high accuracy control of low flows at partial load conditions
- for heating and cooling systems
- increase HVAC system efficiency

AB-QM for AME and AMV actuators

DN	Qmin.	Qnom.
40 (G 2A)	3 m³/h	7,5 m³/h
50 (G 2 ½A)	5 m³/h	12,5 m³/h
50	5 m³/h	12,5 m³/h
65	8 m³/h	20 m³/h
65 HF	10 m³/h	25 m³/h
80	11,2 m³/h	28 m³/h
80 HF	16 m³/h	40 m³/h
100	15,2 m³/h	38 m³/h
100 HF	23,6 m³/h	59 m³/h

[Go to datasheet](#)



[Actuators size M](#)



Actuators size M - specifications

The overview shows the most common used actuators for AB-QM PICVs.
For special needs or applications contact our local Sales representative.

	Digital	Modulating / Floating	
	Step motor	Gear	
Control principle			
Actuator principle			
Why choose?	- connectivity & data - high accuracy - HVAC 4.0	- BMS integration - remote possibilities	- high accuracy - speed
Actuator	NovoCon® M 	AME 435 QM 	AMV 435 
Specification summary			
For valves	AB-QM NovoCon®	AB-QM	AB-QM
Control signals	BACnet; Modbus; 0-10V; 4-20mA	0-10V; 4-20mA	3-point
Power supply	24V AC/DC	24V AC/DC	24V AC / 230V AC
Feedback signal	BACnet; Modbus	x-signal	--
Speed	24/12/6/3 sec./mm	15/7.5 sec./mm	15/7.5 sec./mm
Characteristic	Logarithmic / Linear	Logarithmic / Linear	--
Valve open/close detection	yes	yes	no
Cable	--	--	--
Mounting adapter	--	--	--
Actuator connection	push/pull	push/pull	push/pull
IP class	IP54	IP54	IP54
Options & accessories			
Expand features	3x Temperature sensors; 1x Analog Input; 1x Analog Output		
Stem heater	--	for AB-QM generation 2 = 065Z0315	for AB-QM generation 2 = 065Z0315
	Go to datasheet	Go to datasheet	Go to datasheet

[Back to front page](#)



[AB-QM size L](#)

Large combinations for chillers

AB-QM valves size L

AB-QM


DN	Qmin.	Qnom.
125	36 m ³ /h	90 m ³ /h
125 HF	44 m ³ /h	110 m ³ /h
150	58 m ³ /h	145 m ³ /h
150 HF	76 m ³ /h	190 m ³ /h

[Go to datasheet](#)



Why choose?

- pressure independent control performance
- high accuracy control of low flows at partial load conditions
- for heating and cooling systems
- increase HVAC system efficiency



[Back to front page](#)



[Actuators size L](#)



Actuators size L - specifications

The overview shows the most common used actuators for AB-QM PICVs.
For special needs or applications contact our local Sales representative.

Control principle	Digital	Modulating / Floating		
Actuator principle	Step motor	Gear		
Why choose?	- connectivity & data - BMS integration - remote possibilities - high accuracy - HVAC 4.0	- high accuracy - low-price	- speed - high accuracy - DC power supply - UL certification	- high accuracy - DC power supply - SU/SD - UL certification
Actuator	NovoCon® L	AME 55 QM	AME 655-1	AME 658-1
Specification summary Control signals Power supply Feedback signal Speed Characteristic Valve open/close detection Cable Mounting adapter Actuator connection IP class Options & accessories Expand features Stem heater Spring return UL certification				
	BACnet; Modbus; 0-10V; 4-20mA	0-10V; 4-20mA; 3-point	0-10V; 4-20mA; 3-point	0-10V; 4-20mA; 3-point
	24V AC/DC	24V AC	24V AC/DC	24V AC/DC
	BACnet; Modbus	x-signal	x-signal	x-signal
	24/12/6/3 sec./mm	8 sec./mm	6/2 sec./mm	6/4 sec./mm
	Logarithmic / Linear	Logarithmic / Linear	Logarithmic / Linear	Logarithmic / Linear
	yes	yes	yes	yes
	--	--	--	--
	--	--	--	--
	push/pull	push/pull	push/pull	push/pull
	IP54	IP54	IP54	IP54
	3x Temperature sensors; 1x Analog Input; 1x Analog Output			
	065Z7022	065Z7022	065Z7022	065Z7022
	Spring up / Spring down	--	--	Spring up / Spring down
	--	--	yes	yes
Go to datasheet >		Go to datasheet >		Go to datasheet >

Back to front page >



AB-QM size XL >

X-large combinations for district cooling

AB-QM valves size XL

AB-QM


DN	Qmin.	Qnom.
200	80 m ³ /h	200 m ³ /h
200 HF	108 m ³ /h	270 m ³ /h
250	120 m ³ /h	300 m ³ /h
250 HF	148 m ³ /h	370 m ³ /h

[Go to datasheet](#)



Why choose?

- pressure independent control performance
- high accuracy control of low flows at partial load conditions
- for district energy systems
- increase system efficiency



[Back to front page](#)




[Actuators size XL](#)



Actuators size XL - specifications

The overview shows the most common used actuators for AB-QM PICVs.
For special needs or applications contact our local Sales representative.

Control principle	Digital	
Actuator principle	Step motor	
Why choose?	- connectivity & data - BMS integration - remote possibilities - high accuracy - HVAC 4.0	
Actuator	Gear	
	- speed - high accuracy - power supply - UL certification	
Actuator	NovoCon® XL	
		
Specification summary	AME 685-1	
Control signals		
Power supply	BACnet; Modbus; 0-10V; 4-20mA	0-10V; 4-20mA; 3-point
Feedback signal	24V AC/DC	24V AC/DC
Speed	BACnet; Modbus	x-signal
Characteristic	24/12/6/3 sec./mm	6/3 sec./mm
Valve open/close detection	Logarithmic / Linear	Logarithmic / Linear
Cable	yes	yes
Mounting adapter	--	--
Actuator connection	--	--
IP class	Push/pull	Push/pull
Options & accessories	IP54	IP54
Expand features		
Stem heater	3x Temperature sensors; 1x Analog Input; 1x Analog Output	
Spring return	--	--
UL certification	--	yes
	Go to datasheet >	Go to datasheet >