


Data Sheet

Micro Plate Heat Exchanger Type **C62 & H62**

For more efficient Chillers & Heat Pumps



20% reduction in refrigerant charge compared with a traditional BPHE, the ideal solution to help you meet the world's climate and energy aspirations.

The C62 & H62 are families of Condensers and Evaporators optimized for high-efficiency chillers and heat pumps.

The heat exchanger features innovative Micro Plate technology that improves heat transfer and reduces the amount of material used.

To meet demands for higher COPs in heat pumps, the evaporator H62(L)-C is designed to work efficiently with close temperature approaches, while a low pressure drop on the brine side reduces the pump power and keeps the overall COP high. H62 can cover a capacity range from 4 to 40kW.

The C62(L)-E and the C62(L)-C are respectively evaporator and condenser designed to work efficiently and increase comfort in modern buildings without increasing the carbon footprint. Helping chillers perform more efficiently achieving higher seasonal efficiency levels, it reduces both energy costs and environmental impact. C62 can cover a capacity range from 20 to 90kW.

The low hold-up volume reduces the system refrigerant charge and offers valuable savings.

Features

- Minimal hold-up volume: Less refrigerant charge
- Reduced pressure drop: For a more efficient system
- Smaller footprint: Enabling more compact system
- Reduced CO₂ footprint: Environmentally friendly with high heat transfer and minimal refrigerant charge

Portfolio overview

C62L-E: Evaporator optimized for R410A in chiller application, from 20 to 90kW.
 C62-E: Evaporator for medium density refrigerants in chiller application, from 20 to 90kW.
 C62L-C: Condenser optimized for high density refrigerants in chiller application, from 20 to 90kW.
 C62-C: Condenser optimized for medium density refrigerants in chiller application, from 20 to 90kW.
 H62L-C: Condenser optimized for high density refrigerants in heat pump application, from 4 to 40kW.
 H62-C: Condenser optimized for medium density refrigerants in heat pump application, from 4 to 40kW.

Table 1: Designation

a Applications C: chiller H: heat pump HDW: heat pump double wall	d Specific duty E= evaporator C= condenser Plate design Omit L: L-type M: M-type H: H-type W: W-type X: Asymmetric Z: Z flow Configuration Omit: single D: Dual circuit U: Mixing chamber	e Distributor version Omit B F Plate stacking sequence Omit: a-b-a... R: b-a-b...
b Platform⁽¹⁾ 22,30,55,62,118...		f Number of plates⁽²⁾
c Pressure Service Omit: 30bar L: 45/49bar		

⁽¹⁾ Heat exchanging surface per plate 1/1000 m².

⁽²⁾ Rule:

- Single: even number
- Dual: even number not multiple of 4

Application

The C62 & H62 are families of Condensers and Evaporators specifically optimized for high-efficiency chillers and heat pumps, dedicated to comfort applications, cooling-industrial process, data centers. The evaporators are design to operate also in reversable systems in condenser mode, in co or counter current flow configuration; as well as the condensers are verified with regards to the defrost operation cycle.

Media

Refrigerants


R410A, R407C, R452B, R454B, R290

For other refrigerants please contact your Danfoss Sales representative.

Product specification

Dimensions

Figure 1: Dimensions



A:

C62-C / C62-E: $11.5 + 1.72 \times N$ [0.45 + 0.068xN]

C62L-C / C62L-E: $13.5 + 1.72 \times N$ [0.53 + 0.068xN]

H62-C: $11.5 + 1.44 \times N$ [0.45 + 0.057xN]

H62L-C: $13.5 + 1.44 \times N$ [0.53 + 0.057xN]

N: Number of Plate

Operating conditions

Preconditions:

N = number of plates

Max number of plates: 150

Pressure and temperature data*:

Min. working temperature: -196 °C (-320 °F)

Max. working temperature: 200 °C (390 °F)

Max. working pressure*:

C62-C / C62-E / H62-C: 30 bar (435psi)

C62L-C / C62L-E: 45 bar (653psi)

H62L-C: 48 bar (696psi) [UL: 45 bar (653psi)]

For details, refer to the [Third party approvals](#) chapter.

Weight*

C62-C / C62-E: $2.92 + 0.145 \times N$ [kg] / $6.44 + 0.32 \times N$ [lb]

C62L-C / C62L-E: $3.35 + 0.145 \times N$ [kg] / $7.39 + 0.32 \times N$ [lb]

H62-C: $2.91 + 0.145 \times N$ [kg] / $6.42 + 0.32 \times N$ [lb]

H62L-C: $3.35 + 0.145 \times N$ [kg] / $7.39 + 0.32 \times N$ [lb]

N: Number of Plate

*without connections

Material specification


Table 2: Standard materials

Item	Material	Specification
Cover plates	Stainless steel	AISI 304L
Plates	Stainless steel	AISI 316L
Connections	Stainless steel	AISI 304L
Brazing filler	Pure copper	Cu

Other material combinations are available on request. Please contact your Danfoss sales representative for more information.

Configuration flow

Figure 2: Configuration flow



Parallel flow:

Q1-Q2 [H1-H2]: brine/secondary side

Q3-Q4 [H3-H4]: primary, first circuit

Hold up volume

C/H62(L)-C/E:

Q1-Q2: $0.081 \times N/2$ [l]

Q3-Q4: $0.081 \times (N-2)/2$ [l]

H62(L)-C:

Q1-Q2: $0.066 \times N/2$ [l]

Q3-Q4: $0.066 \times (N-2)/2$ [l]

N: Number of Plate

Ordering

Global or local standard code numbers can be accessed via Store.Danfoss.com on local subsites, with full set of technical data as well as relevant assets such as documentation and drawings. Since the portfolio may contain different types depending on country, this document contains only a summarized list of standard code numbers with a few data relevant for the product selection.

Configuring and calculating products

The C62 & H62 can be easily customized based on the application needs; model size can be evaluated using Hexact software.

For details, product configuration and code creation please contact your Danfoss Sales representative.

Mechanical connections

Circuits	Connection type options	Connection size option
Q1-Q2 (water-brine side)	BSP Gas male	1/2", 3/4", 1", 1 1/4", 1 1/2"
	BSP Gas female	1/2", 3/4", 1"
	DIN R male	1", 1 1/4"
	NPT	1", 1 1/4"
	Victaulic	1", 1 1/4", 1 1/2"
Q3 -Q4 (refrigerant side)	Soldering	3/8", 1/2", 5/8", 3/4", 7/8", 1 1/8", 1 3/8"

Accessories and spare parts

MPHE products are not serviceable, i.e. cannot be taken apart and repaired, and there are no spare parts program. As for accessories, stud bolts, feet on front and/or back cover plates for mounting support and handling are available upon request.

Table 3: Stud bolts:

Stud bolt position	Bolt sizes
327 mm, middle	M8x20mm
140 x 100 mm, middle	M8x25mm
	M8x30mm

Contact your Danfoss sales representative for further information.

Certificates, declarations, and approvals


The list contains all certificates, declarations, and approvals for this product type. Individual code number may have some or all of these approvals, and certain local approvals may not appear on the list.

Some approvals may change over time. You can check the most current status at danfoss.com or contact your local Danfoss representative if you have any questions.

Third party approvals

All MPHE and BPHE are certified to European Pressure Equipment Directive (PED) and are approved by Underwriters Laboratories (UL).

Table 4: Third party approvals



Other certifications are available upon request: Kraia, EAC, UA, AS; for others and more details please contact your local Danfoss representative.

Online support

Danfoss offers a wide range of support along with our products, including digital product information, software, mobile apps, and expert guidance. See the possibilities below.

The Danfoss Product Store



The Danfoss Product Store is your one-stop shop for everything product related—no matter where you are in the world or what area of the cooling industry you work in. Get quick access to essential information like product specs, code numbers, technical documentation, certifications, accessories, and more.

Start browsing at store.danfoss.com.

Find technical documentation



Find the technical documentation you need to get your project up and running. Get direct access to our official collection of data sheets, certificates and declarations, manuals and guides, 3D models and drawings, case stories, brochures, and much more.

Start searching now at www.danfoss.com/en/service-and-support/documentation.

Danfoss Learning



Danfoss Learning is a free online learning platform. It features courses and materials specifically designed to help engineers, installers, service technicians, and wholesalers better understand the products, applications, industry topics, and trends that will help you do your job better.

Create your Danfoss Learning account for free at www.danfoss.com/en/service-and-support/learning.

Get local information and support



Local Danfoss websites are the main sources for help and information about our company and products. Find product availability, get the latest regional news, or connect with a nearby expert—all in your own language.

Find your local Danfoss website here: www.danfoss.com/en/choose-region.

Coolselector^{®2} - find the best components for you HVAC/R system



Coolselector^{®2} makes it easy for engineers, consultants, and designers to find and order the best components for refrigeration and air conditioning systems. Run calculations based on your operating conditions and then choose the best setup for your system design.

Download Coolselector^{®2} for free at coolselector.danfoss.com.

Hexact for heat exchangers



Hexact for heat exchangers helps you identify the best heat exchanger for your chiller, heat pump, or other application based on operating conditions. Works for innovative MPHE and traditional BPHE brazed heat exchangers.

Download Hexact for free at hexact.danfoss.com

Danfoss can accept no responsibility for possible errors in catalogues, brochures and other printed material. Danfoss reserves the right to alter its products without notice. This also applies to products already on order provided that such alterations can be made without subsequential changes being necessary in specifications already agreed. All trademarks in this material are property of the respective companies. Danfoss and the Danfoss logotype are trademarks of Danfoss A/S. All rights reserved.