

Data Sheet

Temperature sensor
Type **MBT 3270**

Compact industrial temperature sensor.



The flexible temperature sensor MBT 3270 can be used in many industrial applications such as: Air Compressors, Mobile Hydraulics and Exhaust gas return systems. In other words applications where robustness, size and performance are essentials.

The sensor can be equipped with different sensing elements (RTD, NTC and PTC) and is available with different electrical connections (Cable, Delphi Metri Pack, AMP junior power Timer, Deutsch DT04).

Features:

- OEM Temperature Sensor program
- Various sensor elements available (RTD, NTC, PTC)
- Robust, high protection against moisture
- Fixed measuring insert
- Brass or stainless steel
- Very low response times
- Temperature range up to 300 °C
- Available with cable or integrated plug (Delphi Metri Pack, AMP junior power Timer, Deutsch DT04)

Product specification

Technical data

Cable version

Figure 1: Cable version




Table 1: General data

Features		Description	
Ambient temperature	Cable	PVC	-40 – 100 °C
		Silicon	-40 – 200 °C
		Teflon	-40 – 200 °C
		Polyolefin (oil resistant)	-40 – 150 °C
	Plug	AMP spade	-40 – 200 °C
		AMP Junior Power Timer	-40 – 125 °C
		Delphi Metri Pack 102	-40 – 125 °C
		Deutsch DT04-3P	-40 – 125 °C
Media temperature		Pt 100	-50 – 300 °C
		NTC	-50 – 150 °C, Special versions up to 300 °C
		PTC	-50 – 150 °C
Max. external pressure		Operating pressure	500 bar
		Burst pressure	> 900 bar
Max. tightening torque		M10	17 Nm
		M14	24 Nm

Table 2: Performance

Features		Description
Sensor Element		Pt 100, Pt 1000, NTC, PTC
Process Connection		Refer to ordering standard, see page Cable version
Sensor insertion length	Brass	80 mm @ d ≥ 8 mm
		60 mm @ 8 > d > 5 mm
		40 mm @ d ≤ 5 mm
	Stainless steel	70 mm @ d ≥ 8 mm
		50 mm @ 8 > d > 5 mm
		35 mm @ d ≤ 5 mm
Electrical Connection		Stripped wire ends Cable with AMP spade (6.35) Cable with AMP Junior Power Timer Cable with Delphi Metri Pack 102 Cable with Deutsch DT04-3P-2P Other on request
Connection		2, 3 or 4 wire (depending on electrical connection)

Table 3: Indicative response times

Material protection tube	Protection tube	Indicative response times	
		Water 0,2 m/s	
		t _{0,5}	t _{0,9}
Stainless steel	ø6 mm	6 s	18 s
	ø4 mm	2 s	6 s
	ø3 mm	0.5 s	1.5 s

NOTE:

Response times can vary very much depending on the design of the sensor and the temperature element chosen.

Temperature sensor, Type MBT 3270

Table 4: Mechanical and environmental specifications

Features	Description	
Sensor tolerances	Pt 1000 / Pt 100	EN 60751 Class B: $\pm (0.3 + 0.005 \times t)$
	NTC	On request
	PTC 2000 (KTY 81 – 210)	$\pm 1\%$ at 25 °C
Vibration stability	Shock	50 g / 6 ms
	Vibrations, x-y-z directions	15.3 g sine, 20 – 2000 Hz, 8 hours
Enclosure	Sensor only	IP67 according to IEC 60529
	Cable with AMP spade	IP00 according to IEC 60529
	Cable with AMP Junior Timer	IP65 according to IEC 60529
	Cable with Delphi Metri Pack 102	IP65 according to IEC 60529
	Cable with Deutsch DT04	IP65 according to IEC 60529

Table 5: Materials

Features	Description
Protection tube in contact with media	AISI 316 Brass
Process connection	AISI 316 Brass
Cable	PVC, Silicon, Teflon (other on request)
Gasket	Viton, NBR (other on request)
Plug	PPS (Ryton 4)

Integrated plug version

Figure 2: Integrated plug version




Table 6: General data

Features	Description	
Ambient temperature	Plug	-40 – 125 °C
Media temperature	Pt 1000, Pt 100	-50 – 300 °C
	NTC	-50 – 150 °C, Special versions up to 300 °C
	PTC	-50 – 150 °C
Max. external pressure	Operating pressure	500 bar
	Burst pressure	> 900 bar
Max. tightening torque	M10	17 Nm
	M14	24 Nm

Table 7: Performance

Features	Description	
Sensor Element	Pt 100, Pt 1000, NTC, PTC	
Process Connection	Refer to ordering standard, see page Integrated plug version	
Sensor insertion length	Brass	80 mm @ $d \geq 8$ mm
		60 mm @ $8 > d > 5$ mm
		40 mm @ $d \leq 5$ mm
	Stainless steel	70 mm @ $d \geq 8$ mm
		50 mm @ $8 > d > 5$ mm
		35 mm @ $d \leq 5$ mm
Electrical Connection	AMP Junior Power Timer Delphi Metri Pack Deutsch DT04 Other on request	
Connection	2 wire	

Temperature sensor, Type MBT 3270

Table 8: Indicative response times

Material protection tube	Protection tube	Indicative response times	
		Water 0,2 m/s	
		$t_{0.5}$	$t_{0.9}$
Stainless Steel	ø6 mm	6 s	18 s
	ø4 mm	2 s	6 s
	ø3 mm	0.5 s	1.5 s

NOTE:

Response times can vary very much depending on the design of the sensor and the temperature element chosen.

Table 9: Mechanical and environmental specifications

Features	Description	
Sensor tolerances	Pt 1000 / Pt 100 NTC PTC 2000 (KTY 81 – 210)	EN 60751 Class B On request ± 1% at 25 °C
Vibration stability	Shock	50 g / 6 ms
	Vibrations, x-y-z directions	15.3 g sine, 20 – 2000 Hz, 8 hours
Enclosure	AMP Junior Power Timer Delphi Metri Pack Deutsch DT04	IP65 according to IEC 60529






Table 10: Materials

Features	Description
Protection tube in contact with media	AISI 316 Brass
Process connection	AISI 316 Brass
Gasket	Viton, NBR (other on request)
Plug	PPS (Ryton 4)

Electrical connection




Cable version

Table 11: Electrical connection of cable version

AMP spade (6.35)	AMP Junior Power Timer	Deutsch DT04 3 pin	Deutsch DT04 2 pin	Delphi Metri Pack 102
				

Integrated plug version



Table 12: Electrical connection of integrated plug version

Deutsch DT04	AMP Junior Power Timer	Delphi Metri Pack 102
		

Dimensions

Cable version

Table 13: Dimensions

-50 – 150 °C	-50 – 150 °C / 300 °C
	

Examples:

Insertion length: $L_i = 21$ to xx (max. 80 mm)

Cable length: $L_c = 0.5$ m to $x.xx$ m

Tube diameter depends on the chosen sensor element and the wanted response time.

Ordering

Cable version

Figure 3: Ordering for MBT 3270 - Cable version

Type MBT 3270

Measuring range

-50 – 150 °C

-50 – 200 °C

-50 – 300 °C

Other

Resistance value

1 × Pt 100

1 × Pt 1000

NTC 2000, B25/85 2880 - 4570

NTC 2700, B25/85 2880 - 4570

NTC 3000, B25/50 3499

NTC 5000, B25/100 3988

Other (e.g. NTC)

Tolerance

EN 60751 Class B

± 1%

± 2%

± 3%

Other

NTC characteristic

No NTC

Other

Protection tube

Brass

Acid-Proof Steel, AISI 316

Other

Insertion length (80 mm max)

24 mm

28 mm

40 mm

Other (21 – 80)

Cable length

050

100

200

xxx

0.5 m

1.0 m

2.0 m

x.x m

Cable

1

2

3

4

5

6

7

8

9

Silicone

Silicone, screened

Teflon

Teflon, screened

PVC

PVC, screened

Polyolefine, screened

Polyolefine, screened 80 °C

Other

Connection

0

1

2

2-wire

3-wire

4-wire

Plug

0

1

3

5

D

E

9

None

AMP (Spade 6.35)

AMP Junior Power Timer

Deutsch Flying DT04– 3 pin

Deutsch Flying DT04 – 2 pin

Delphi Metri Pack flying – 102

Other

Insert

0

Fixed

Process connection

0

1

2

3

B

9

G ¼ A

G 3/8 A

G ½ A

M10 × 1

M14 × 1.5

Other

Integrated plug version

Figure 4: Ordering for MBT 3270 - Integrated plug version

Type MBT 3270																			
Measuring range																			
-50 – 150 °C		0																	
-50 – 200 °C		1																	
-50 – 300 °C		2																	
Other		9																	
Resistance value																			
1 × Pt 100		0																	
1 × Pt 1000		2																	
NTC 2000, B25/85 2880 – 4570		6																	
NTC 2700, B25/85 2880 – 4570		K																	
NTC 3000, B25/50 3499		A																	
NTC 5000, B25/100 3988		L																	
Other (e.g. NTC)		9																	
Tolerance																			
EN 60751 Class B		0																	
± 1%		1																	
± 2%		2																	
± 3%		3																	
Other		9																	
NTC characteristic																			
No NTC		0																	
Other		9																	
Protection tube																			
Brass		0																	
Acid-Proof Steel, AISI 316		1																	
Other		9																	
Insertion length (80 mm max)																			
24 mm		0 2 4																	
28 mm		0 2 8																	
40 mm		0 4 0																	
Other (21 – 80)		x x x																	

Connection

2-wire

Other

Plug

None

AMP Junior Power Timer

Delphi Metri-pack Integrated – 102

Deutsch Integrated DT04 – 2 pin

Other

Insert

Fixed

Process connection

G ¼ A

G 3/8 A

G ½ A

M10 × 1

M14 × 1.5

Other

Certificates, declarations, and approvals

The list contains all certificates, declarations, and approvals for this product type. Individual code number may have some or all of these approvals, and certain local approvals may not appear on the list.

Some approvals may change over time. You can check the most current status at danfoss.com or contact your local Danfoss representative if you have any questions.

Table 14: MBT 3270

File name	Document type	Document topic	Approval authority
E494625	Electrical - Safety Certificate	–	UL
DK.C.32.004.A 41461	Measuring - Performance Certificate	–	GOST
097R0004.01	Manufacturers Declaration	RoHS	Danfoss
084R1022.01	Manufacturers Declaration	China RoHS	Danfoss
087R0017.00	Manufacturers Declaration	Simple apparatus	Danfoss
OC.C.32.004.A 75977	Measuring - Performance Certificate	–	GOST

Online support

Danfoss offers a wide range of support along with our products, including digital product information, software, mobile apps, and expert guidance. See the possibilities below.

The Danfoss Product Store



The Danfoss Product Store is your one-stop shop for everything product related—no matter where you are in the world or what area of the cooling industry you work in. Get quick access to essential information like product specs, code numbers, technical documentation, certifications, accessories, and more.

Start browsing at store.danfoss.com.

Find technical documentation



Find the technical documentation you need to get your project up and running. Get direct access to our official collection of data sheets, certificates and declarations, manuals and guides, 3D models and drawings, case stories, brochures, and much more.

Start searching now at www.danfoss.com/en/service-and-support/documentation.

Danfoss Learning



Danfoss Learning is a free online learning platform. It features courses and materials specifically designed to help engineers, installers, service technicians, and wholesalers better understand the products, applications, industry topics, and trends that will help you do your job better.

Create your Danfoss Learning account for free at www.danfoss.com/en/service-and-support/learning.

Get local information and support



Local Danfoss websites are the main sources for help and information about our company and products. Find product availability, get the latest regional news, or connect with a nearby expert—all in your own language.

Find your local Danfoss website here: www.danfoss.com/en/choose-region.