

Data sheet

Buffer storage tank (6 bar)


Type PSS
300 ... 2000

Heating buffer storage tank, standing model,
Charging-/Discharging connections as flange connection

**Materials and
Maximum operating
parameters**

Material (tank/shell):	Steel EN 10025 S235 JRG2
Maximum permissible operating temperature:	110 °C
Maximum permissible operating pressure:	6 bar

Surface treatment: Raw inside, outside undercoat - black
 Approval: According factory standard
 Accessory: Insulation, polyester nonwoven 100mm thickness + impact-resistance polystyrene surface RAL 9006 and black top layer (from 1500 liter as bypack/not mounted). 100% recyclable, CFC free.



Type PSS I	H mm	H1 mm	H2 mm	H3 mm	H4 mm	H5 mm	H6 mm	H7 mm	H8 mm	H9 mm	H _{max} mm	d mm	D _x mm	D mm	Tilted height mm	connections	codes	Weight kg
300	1450	1270	1070	860	760	660	560	320	215	115	1130	550	790	750	1550	DN 25 / PN 16	641U1180	85
500	1860	1665	1430	1055	950	690	590	350	245	145	1550	600	840	800	2010	DN 40 / PN 16	641U1181	115
750	1870	1635	1400	1055	950	710	610	370	265	165	1500	750	990	950	1945	DN 40 / PN 16	641U1182	175
1000	1910	1655	1370	1075	970	730	630	390	285	185	1500	850	1090	1050	2090	DN 50 / PN 16	641U1183	240
1500	2030	1740	1505	1145	1030	825	725	445	320	220	1550	1000	1240	1200	2160	DN 50 / PN 16	641U1184 + 641U1186	325
2000	2310	1995	1750	1320	1185	870	770	510	375	265	1770	1100	1340	1300	2450	DN 65 / PN 16	641U1185 + 641U1187	375

Danfoss A/S

Climate Solutions • climatesolutions.danfoss.com • +45 7488 2222 • E-Mail: climatesolutions@danfoss.com

Any information, including, but not limited to information on selection of product, its application or use, product design, weight, dimensions, capacity or any other technical data in product manuals, catalogues descriptions, advertisements, etc. and whether made available in writing, orally, electronically, online or via download, shall be considered informative, and is only binding if and to the extent, explicit reference is made in a quotation or order confirmation. Danfoss cannot accept any responsibility for possible errors in catalogues, brochures, videos and other material. Danfoss reserves the right to alter its products without notice. This also applies to products ordered but not delivered provided that such alterations can be made without changes to form, fit or function of the product.

All trademarks in this material are property of Danfoss A/S or Danfoss group companies. Danfoss and the Danfoss logo are trademarks of Danfoss A/S. All rights reserved.