

Data Sheet

EC-LTS1200-410

Liquid cooled heavy duty inductor unit

FEATURES

- Extremely compact design: 410 A unit only 23 kg
- High enclosure class IP67 – sealed from moisture and dust
- Liquid cooled with plain water or water/glycol mixture
- Ambient temperature up to +105 °C and down to -40 °C
- Allowed coolant temperature up to +65 °C
- Robust design withstanding high levels of mechanical vibrations and shocks
- Designed especially for highly cyclical loads typical in heavy mobile work machines
- Three temperature sensors included for temperature surveillance



GENERAL

The device is a heavy duty external inductance unit designed to be combined with EC-C1200 DC/DC-converter. It allows flexible positioning of the DC/DC-converter and inductor unit and is used to transfer energy between two different voltage levels.

Typical applications:

- Boosting battery voltage to higher DC-link voltage
- Charging high voltage batteries from higher DC-link voltage

SPECIFICATIONS

			58...150 Hz: 1 G
			5...24.9 Hz: +-1.6 mm
			24.9...100 Hz: 4G (sinusoidal)
DC connection		Mechanical shock	50 G ISO 16750-3
DC link voltage range	0-850 V _{DC}		4.2.2 Test for devices on rigid points on the body and on the frame
DC link nominal voltage	750 V _{DC}		Notes:
Nominal current	410A total (65 °C coolant, 8 kHz interleaved switching frequency)		-acceleration: 500 m/s ² ;
Inductance per inductor	165 µH (at nominal current)		-duration: 6 ms;
			-number of shocks: 10 per test direction (x, y and z axis, both directions, 6x directions in total).
Mechanical			30 G, CEI EN 61373 category 2
Dimensions (WxHxL, mm)	403x147x262 403x147x287 (with +CG1 option)	Connections	
Weight	23 kg	Coolant connection	2 x G3/4" coolant hose connector
Cooling		HV cable recommended type	HUBER+SUHNER Radox Elastomer S screened automotive cable www.hubersuhner.com
Cooling liquid	Plain water with appropriate corrosive inhibitor (max. 50 % corrosive inhibitor)	HV cable cross section	≤70 mm ² (Cu) (M25 cable gland) ≤120 mm ² (Cu) (M32 cable gland)
Cooling liquid glycol type	Ethylene glycol (Glysantin G48 recommended)	HV cable glands (with +CG1)	3x Pflitsch blueglobe TRI bg 225ms tri 3x Pflitsch blueglobe TRI bg 232ms tri 2x M32 plugs Configurable cable glands, see Table 3
Minimum cooling liquid flow	10 l/min	HV cable lug size	35-8, 50-8, 70-8, 95-8, 120-8
Maximum continuous pressure	2 bar	Recommended cable lug	35 mm ² : Druseidt with narrow flange 03901 50 mm ² : Druseidt with narrow flange 03903 70 mm ² : Druseidt with narrow flange 03906 95 mm ² : Druseidt with narrow flange 03910 (Only compatible with M32 cable gland) 120 mm ² : Druseidt with narrow flange 03914 (Only compatible with M32 cable gland) www.druseidt.de
Pressure loss	40 mbar with 10l/min (+25°C coolant)	Temperature measurement	3x PT100 temperature sensors, one per inductor
Cooling liquid temperature	-40°C ...+65°C	Temperature sensor connector + insert + pins	M16 male, 7.840.200.000 Insert 10-pole, 7.003.910.101 Sensor Connector Pin, 7.010.981.001 www.hummel.com
Ambient Conditions		Temperature sensor mating connector + insert + socket	M16 female, 7.810.400.000 Insert 10-pole, M16, RCPT, 7.003.910.102 Sensor Connector Socket, 7.010.981.002 www.hummel.com
Storage temperature	-40°C...105°C		
Operating temperature	-40°C...105°C (with nominal coolant temp.)		
Altitude	max. 4000 m		
Relative humidity	100 %		
Enclosure class	IP67		
Mechanical vibration	10 G ISO 16750-3 Test VII – Commercial vehicle, sprung masses – Table 12 Notes: test duration 8h axis (three axis tested; x,y and z axis) total spectral acceleration 5,91 G _{rms} 5 G, CEI EN 61373 category 2 IEC 60068-2-6 (2007-12, Test Fc) 10...57 Hz: amplitude 0.075mm		




Figure 1 Temperature measurement connector pinout

PIN	Description
1	Temperature 1, PT100 (P), inductor
2	Temperature 1, PT100 (N), inductor
3	Temperature 2, PT100 (P), inductor
4	Temperature 2, PT100 (N), inductor
5	Temperature 3, PT100 (P), inductor
6	Temperature 3, PT100 (N), inductor
7	Enclosure ground (shield)
8	Reserve

Table 1 Pin configuration of temperature measurements (M16 connector, one sensor per inductor)

PRESSURE LOSS VS COOLANT FLOW




Figure 2 Device pressure loss vs coolant flow

DIMENSIONS




Figure 3 Device dimensions with +CG1 option (example cable gland configuration, 3x M25, 1x M32 cable glands and 2x M32 plugs)

Dimension	Length
A	403 mm
B	147 mm
C	287 mm

Table 2 Device dimensions with +CG1 option

APPLICATION EXAMPLE




Figure 4 EC-C1200 DC/DC converter combined with the EC-LTS unit.

LV+ and LV- can be connected, for example, to battery and DC+ and DC- to DC-link. EC-C1200 would then control the battery discharging and charging.

LTS1200 has internal parallel busbar included for low voltage (LV) side inductors. With internal parallel connection 1 to 3 output (LV+) cables can be used depending on the cable gland configuration. Typical cable gland configurations can be seen in table below.

Connections	Typical cable gland combinations		
Connection to DC/DC-converter (L1, L2, L3)	3x M25 cable glands	3x M25 cable glands	3x M25 cable glands
Low voltage side positive connection (+LV)	1x M32 cable gland, 2x M32 plugs	2x M32 cable glands, 1x M32 plugs	3x M32 cable glands, no plugs

Table 3 Typical cable gland configurations for LTS1200 (cable glands and plugs are included in the delivery with +CG1 option for any of these configurations)

PRODUCT CODE AND OPTIONS

Use the product code including all needed options for ordering. Standard options do not need to be listed in the code as they are selected by default if a non-standard option is not selected. Standard options are indicated by a star (*).

EC-LTS is designed to be used in combination with the EC-C inverters.

Product code	Description
EC-LTS1200-410	Standard unit without cable glands or plugs
EC-LTS1200-410+CG1	Unit with all necessary cable glands included for free configuration of power connections

Table 4 Product code examples

Variant	Code	Description	Additional information
Cable glands	*	No cable glands	No cable glands or plugs
	+CG1	M25/M32 cable glands	3x M25 cable glands, 3x M32 cable glands and 2x M32 plugs in delivery
Marine classification	*	No marine classification	
	+CL1		ABS American Bureau of Shipping
	+CL2		BV Bureau Veritas
	+CL3		DNV
	+CL4		LR Lloyd's Register
	+CL5		RINA

*Standard option

Table 5 Option list

Danfoss can accept no responsibility for possible errors in catalogues, brochures and other printed material. Danfoss reserves the right to alter its products without notice. This also applies to products already on order provided that such alterations can be made without changes being necessary in specifications already agreed. All trademarks in this material are property of the respective companies. Danfoss and the Danfoss logotype are trademarks of Danfoss A/S. All rights reserved.