


Data sheet

Seated valves (PN 16)

VRB 2 – 2-way valve, internal and external thread

VRB 3 – 3-way valve, internal and external thread

Description



Features:

- Bubble tight design
- Snap mechanical connection together with AMV(E) 335, AMV(E) 435
- Dedicated 2 and 3-port valv
- Suitable for diverting applications (3-port)

Main data:

- DN 15-50
- k_{vs} 0,63-40 m³/h
- PN 16
- Temperature:
 - Circulation water / glycolic water up to 50 %: 2 (-10*) ... 130 °C
- * At temperatures from -10 °C up to +2 °C use stem heater
- Connections:
 - External thread
 - Internal thread

VRB valves provide a quality, cost effective solution for most water and chilled applications.

The valves are designed to be combined with following actuators:

- With AMV(E) 335, AMV(E) 435 or AMV(E) 438 SU actuators.
- With AMV(E) 25, 25 SU/SD, 35 actuators (with adapter **065Z0311**).

Combinations of actuators is evident under section "Dimension".

Ordering

Example:
3-way valve; DN 15; k_{vs} 1,6; PN 16;
 T_{max} 130 °C; ext. thread

- 1x VRB 3 DN 15 valve
Code No.: **065Z0153**

Option:
- 3x Tailpieces
Code No.: **065Z0291**

2&3-way valves VRB (external thread)

DN	k_{vs} (m ³ /h)	Code No.	
		VRB 2	VRB 3
15	0.63	065Z0171	065Z0151
	1.0	065Z0172	065Z0152
	1.6	065Z0173	065Z0153
	2.5	065Z0174	065Z0154
	4.0	065Z0175	065Z0155
20	6.3	065Z0176	065Z0156
25	10	065Z0177	065Z0157
32	16	065Z0178	065Z0158
40	25	065Z0179	065Z0159
50	40	065Z0180	065Z0160

2 & 3-way valves VRB (internal thread)

DN	k_{vs} (m ³ /h)	Code No.	
		VRB 2	VRB 3
15	0.63	065Z0231	065Z0211
	1.0	065Z0232	065Z0212
	1.6	065Z0233	065Z0213
	2.5	065Z0234	065Z0214
	4.0	065Z0235	065Z0215
20	6.3	065Z0236	065Z0216
25	10	065Z0237	065Z0217
32	16	065Z0238	065Z0218
40	25	065Z0239	065Z0219
50	40	065Z0240	065Z0220

Ordering (continued)

Accessories - Tailpieces

Type	DN	Code No.
Tailpiece ¹⁾	Rp ½	15
	Rp ¾	20
	Rp 1	25
	Rp 1¼	32
	Rp 1½	40
	Rp 2	50

¹⁾ 1 tailpiece internal thread for VRB ext. thread (Ms - CuZn39Pb3)

Accessories - Adapter & stem heater

Type	for actuators	Code No.
Adapter	AMV(E) 25/35	065Z0311
Stem heater	AMV(E) 335/435	065Z0315

Service kits


Type	DN	Code No.
Stuffing box	15	065Z0321
	20	065Z0322
	25	065Z0323
	32	065Z0324
	40/50	065Z0325

Technical data

Nominal diameter	DN	15					20	25	32	40	50
k _{vs} value	m³/h	0.63	1.0	1.6	2.5	4.0	6.3	10	16	25	40
Stroke	mm	10							15		
Control range		30:1	50:1				100:1				
Control characteristic		LOG: port A-AB; LIN: port B-AB									
Cavitation factor z		≥ 0,4									
Leakage		A - AB bubble tight design									
		B - AB ≤ 1.0 % of k _{vs}									
Nominal pressure	PN	16									
Max. closing pressure	bar	Mixing: 4									
		Diverting: 1									
Medium		Circulation water / glycolic water up to 50 %									
Medium pH		Min. 7, Max. 10									
Medium temperature	°C	2 (-10 ¹⁾) ... 130									
Connections		Int. and ext. thread									
Materials											
Valve body		Red bronze CuSn5ZN5Pb5 (Rg5)									
Valve stem		Stainless steel									
Valve cone		Brass									
Stuffing box sealing		EPDM									


¹⁾ At temperatures from -10 up to +2 °C use stem heater

Pressure temperature diagram




Valve characteristics

Valve characteristics log (2-way)



Valve characteristics log/lin (3-way)





Installation

Valve mounting


Before valve mounting the pipes have to be cleaned and free from abrasion. Valve must be mounted according to flow direction as indicated on valve body, except by diverting, where valve can be mounted opposite to the flow direction (flow opposite to indication on the valve body). Mechanical loads of the valve caused by the pipes are not allowed. Valve should be free of vibrations as well.

Installation of the valve with the actuator is allowed in horizontal position or upwards. Installation downwards is not allowed.

Always install the valve with the arrow on the body in the same direction as the flow. In order to avoid turbulence, which will affect the measuring accuracy, it is recommended to have a straight length of pipe up and down stream from the valve as shown (D - diameter of pipe).



Note:
Install a strainer upstream of the valve (e.g. Danfoss FVR/FVF)



Mixing or diverting connection


3-way valve can be used either as mixing or diverting valve (fig.1).

If 3-way valve is installed as mixing valve meaning that A and B ports are inlet ports, and AB port is outlet port it can be installed in mixing (fig.2) or diverting application (fig.3).

3-way valve can be also installed as diverting valve in diverting application (fig.4) meaning that AB port is inlet and A and B ports are outlets.

Note:
Maximal closing pressure for mixing and diverting installation are not the same. Please refer to values stated in Technical data section.

Sizing



Example

Design data:

Flow rate: 6 m³/h

System pressure drop: 55 kPa

Locate the horizontal line representing a flow rate of 6 m³/h (line A-A). The valve authority is given by the equation:

$$\text{Valve authority, } a = \frac{\Delta p_1}{\Delta p_1 + \Delta p_2}$$

Where:

Δp_1 = pressure drop across the fully open valve

Δp_2 = pressure drop across the rest of the circuit with a full open valve

The ideal valve would give a pressure drop equal to the system pressure drop (i.e. an authority of 0,5):

$$\text{if: } \Delta p_1 = \Delta p_2 \\ a = \frac{\Delta p_1}{\Delta p_1 - \Delta p_2} = 0.5$$

In this example an authority of 0,5 would be given by a valve having a pressure drop of 55 kPa at that flow rate (point B). The intersection of line A-A with a vertical line drawn from B lies between two diagonal lines; this means that no ideally-sized valve is available.

The intersection of line A-A with the diagonal lines gives the pressure drops stated by real, rather than ideal, valves. In this case, a valve with k_{vs} 6,3 would give a pressure drop of 90,7 kPa (point C):

$$\text{hence valve authority} = \frac{90.7}{90.7 + 55} = 0.62$$

The second largest valve, with k_{vs} 10, would give a pressure drop of 36 kPa (point D):

$$\text{hence value authority} = \frac{36}{36 + 55} = 0.395$$


Generally, for a 3 port application, the smaller valve would be selected (resulting in a valve authority higher than 0,5 and therefore improved control). However, this will increase the total pressure and should be checked by the system designer for compatibility with available pump heads, etc. The ideal authority is 0,5 with a preferred range of between 0,4 and 0,7.

Design

(Design variations are possible)


VRB 2

1. Valve body
2. Valve insert
3. Valve cone
4. Valve stem
5. Moving valve seat (pressure relieved)
6. Stuffing box






VRB 3


1. Valve body
2. Valve insert
3. Valve cone
4. Valve stem
5. Valve seat
6. Pressure relieve chamber
7. Stuffing box




Dimensions




AMV(E) 335, 435 + VRB 2





AMV(E) 335, 435 + VRB 3



AMV(E) 335, 435 + VRB 2



AMV(E) 335, 435 + VRB 3






Type	DN	Connection		L	H	H ₁	L ₁	H ₂	Weight (kg)	
		Rp ¹⁾	G ²⁾						ext. thread	int. thread
VRB 2	15	½	1	80	25	191	128	-	0.61	0.60
	20	¾	1¼	80	29	194	128		0.78	0.77
	25	1	1½	95	29	197	151		1.00	0.98
	32	1¼	2	112	33	202	178		1.57	1.43
	40	1½	2¼	132	43	213	201		2.62	2.54
	50	2	2¾	160	47	217	234		3.76	3.49
VRB 3	15	½	1	80	40	191	128	64	0.70	0.71
	20	¾	1¼	80	45	194	128	69	0.93	0.91
	25	1	1½	95	50	197	151	78	1.21	1.15
	32	1¼	2	112	58	202	178	91	1.95	1.81
	40	1½	2¼	132	75	230	201	110	3.39	3.35
	50	2	2¾	160	83	243	234	120	5.46	5.13

¹⁾ Rp ... internal thread EN 10226-1

²⁾ G ... external thread DIN ISO 228/01

If stem heater is used dimension H₁ is increased for 31 mm.

Dimensions (continued)



Type	DN	Connection		L	H	H1
		Rp ¹⁾	G ²⁾			
VRB 2	15	½	1	80	25	216
	20	¾	1¼	80	29	218
	25	1	1½	95	29	222
	32	1¼	2	112	35	226
	40	1½	2¼	132	43	237
	50	2	2¾	160	47	242
VRB 3	15	½	1	80	40	216
	20	¾	1¼	80	45	218
	25	1	1½	95	50	222
	32	1¼	2	112	58	226
	40	1½	2¼	132	75	255
	50	2	2¾	160	83	268

¹⁾ Rp ... internal thread EN 10226-1

²⁾ G ... external thread DIN ISO 228/01

If stem heater is used dimension H1 is increased for 5 mm.



Danfoss A/S

Climate Solutions • climatesolutions.danfoss.com • +45 7488 2222 • E-Mail: climatesolutions@danfoss.com

Any information, including, but not limited to information on selection of product, its application or use, product design, weight, dimensions, capacity or any other technical data in product manuals, catalogues descriptions, advertisements, etc. and whether made available in writing, orally, electronically, online or via download, shall be considered informative, and is only binding if and to the extent, explicit reference is made in a quotation or order confirmation. Danfoss cannot accept any responsibility for possible errors in catalogues, brochures, videos and other material. Danfoss reserves the right to alter its products without notice. This also applies to products ordered but not delivered provided that such alterations can be made without changes to form, fit or function of the product.

All trademarks in this material are property of Danfoss A/S or Danfoss group companies. Danfoss and the Danfoss logo are trademarks of Danfoss A/S. All rights reserved.