


Fact sheet

Termix Novi

Instantaneous water heater for flats, single-family houses and small apartment buildings with up to 4 flats



Application

The Termix Novi is an instantaneous water heater featuring superb heat extraction and high performance. The Termix Novi is suitable for flats, single-family houses as well as for small apartment buildings. The water heater is available in two sizes, either for 1 apartment, or up to 4 apartments. The Termix Novi is applicable for decentralized heating systems – as well as for district heating networks with summer operation at low temperatures or with changes in differential pressure. The heat exchanger in Termix Novi cools the district heating water very efficiently, thereby creating a very good operation economy.

Domestic hot water (DHW)

The domestic hot water is prepared in the heat exchanger and the temperature is regulated by a flow-compensated temperature controller with a integrated differential pressure controller. The Danfoss IHPT valve ensures a stable hot water temperature by varying differential pressure without the need for readjusting

the valve. This protects the heat exchanger against overheating and lime scale formation. Furthermore the IHPT valve has an integrated idle temperature controller, which keeps the house supply line warm. This shortens the waiting periods during summer when the heating system is in reduced operation, which is ideal where high comfort is requested.

Options

The water heater can be supplied with a built in non-return valve and safety valve mounted in the cold water supply. The water heater can also be supplied with a thermostatic circulation valve and a non-return and pressure equalizer (GTU).


Construction

All pipes are made of stainless steel. The connections are made by nuts and gaskets. The Termix Novi is delivered with an attractive grey full insulation in modern design, emphasising the high level of quality and comfort which characterises this product.

FEATURES AND BENEFITS

- Instantaneous water heater
- DHW regulation with an accelerated thermostatic control
- Capacity: up to 58,5 kW DHW
- DHW in sufficient quantity
- Operates independently of differential pressure and flow temperature
- Minimum space required for installation
- Pipes and plate heat exchanger made of stainless steel
- Minimized risk of lime scale and bacteria formation
- Optimum temperature regulation up to DH supply temperature 100°C

CIRCUIT DIAGRAM - EXAMPLE



Technical parameters:

Nominal pressure: PN 16
 DH supply temperature: $T_{max} = 120^\circ\text{C}$
 DCW static pressure: $p_{min} = 1,0 \text{ bar}$
 Brazing material (HEX): Copper

Weight incl. cover:

7 – 9 kg
 (incl. packing)

Cover:


Grey lacquered steel

Dimensions (mm):

With insulation:
 H 432 x W 300 x D 155
 With cover:
 H 442 x W 315 x D 165

Connections:

- 1 Domestic cold water (DCW)
- 2 Domestic hot water (DHW)
- 3 District heating flow (DH)
- 4 District heating return (DH)



Connections sizes:

DH + DCW + DHW: G 3/4" (ext. thread)

Options:

- Booster pump (increases DH flow)
- Grey-lacquered steel cover
- Safety valve and non-return valve (10 bar)
- Safety valve with thermostatic circulation set
- Thermostatic circulation set
- Non-return and pressure equalizer (GTU)

DHW: CAPACITY EXAMPLES

Substation type	DHW Capacity [kW]	Supply flow primary [°C]	Return flow primary [°C]	DHW [°C]	Pressure loss Primary [kPa]	DHW Tap load [l/min]
Novi Type 1	32,3	60	19	10/45	19	13,3
	41,5	60	21	10/45	29	16,6
	43	70	17	10/45	19	17,7
	53	70	18	10/45	29	21,8
	30	60	23	10/50	19	10,5
	35	60	24	10/50	29	12,6
	41	70	19	10/50	19	14,8
	50	70	21	10/50	29	18,0

DHW: CAPACITY EXAMPLES

Substation type	DHW Capacity [kW]	Supply flow primary [°C]	Return flow primary [°C]	DHW [°C]	Pressure loss Primary [kPa]	DHW Tap load [l/min]
Novi Type 2	32,3	55	19	10/45	18	13,3
	38	55	20	10/45	26	15,7
	39	60	17	10/45	19	15,7
	48,7	60	19	10/45	28	20,1
	50	70	16	10/45	19	20,6
	57	70	16	10/45	24	23,3
	36	60	21	10/50	19	12,3
	43	60	22	10/50	28	15,9
	48	70	17	10/50	19	17,3

Gemina Termix A/S • Member of the Danfoss Group
 danfoss.com • +45 9714 1444 • mail@termix.dk

Any information, including, but not limited to information on selection of product, its application or use, product design, weight, dimensions, capacity or any other technical data in product manuals, catalogues descriptions, advertisements, etc. and whether made available in writing, orally, electronically, online or via download, shall be considered informative, and is only binding if and to the extent, explicit reference is made in a quotation or order confirmation. Danfoss cannot accept any responsibility for possible errors in catalogues, brochures, videos and other material. Danfoss reserves the right to alter its products without notice. This also applies to products ordered but not delivered provided that such alterations can be made without changes to form, fit or function of the product.

All trademarks in this material are property of Danfoss A/S or Danfoss group companies. Danfoss and the Danfoss logo are trademarks of Danfoss A/S. All rights reserved.