

Installation guide

ELIMINATOR® Hermetic filter drier Type DML / DCL

023R9514

023R9514

| | |
|--|--|
| Refrigerants: R134a, R404A, R407C, R507, R22, R410A and other refrigerants (HCFC, HFC, HFO, HC) | Temperature range: T _{min} : -40 °C / -40 °F T _{max} : 70 °C / 160 °F |
|--|--|

| | | | |
|-------------------------------|------------------------------------|---------------------------|---------------------------|
| Solder pure copper | 1.5, 03, 05, 08, 16, 30, 60 cu in. | 1/4 - 7/8 in. ODM / ODF | PS/MWP 46 bar/667 psig |
| | | 1 1/8 in. ODM / ODF | |
| | 38, 41 cu in. | 3/4 - 7/8 in. ODM / ODF | PS/MWP 35 bar/500 psig |
| | 75 cu in. | 1 1/8 in. ODM / ODF | |
| | 75 cu in. | 3/4 - 1 1/8 in. ODM / ODF | |

| | | | |
|-----------------------------|----------------|---------------------|---------------------------|
| Solder cu-plated | 03 - 60 cu in. | 1/4 - 7/8 in. ODF | PS/MWP 46 bar/667 psig |
| | | 1 1/8 in. ODF | |
| | 75 cu in. | 7/8 - 1 1/8 in. ODF | |

| | | | |
|--------------------------------|----------------|---------------|---------------------------|
| Flare and face seal | 03 - 75 cu in. | 1/4 - 3/4 in. | PS/MWP 46 bar/667 psig |
|--------------------------------|----------------|---------------|---------------------------|

