

Data sheet

Flow controller (PN 25) AVQ - return and flow mounting

Description



AVQ is a self-acting flow controller primarily for use in district heating systems. The controller closes when set max. flow is exceeded.

The controller has a control valve with adjustable flow restrictor and an actuator with one control diaphragm.

Main data:

- DN 15-50
- k_{vs} 1.6-25 m³/h
- Flow range 0.03-15 m³/h
- PN 25
- Flow restrictor Δp : 0.2 bar
- Temperature:
 - Circulation water / glycolic water up to 30%: 2 ... 150 °C
- Connections:
 - Ext. thread (weld-on, thread and flange tailpieces)
 - Flange

Ordering


Example:
Flow controller; DN 15; k_{vs} 1.6; PN 25;
flow restrictor Δp 0.2 bar;
 T_{max} 150 °C; ext. thread

- 1× AVQ DN 15 controller
Code No: **003H6722**

Option:
- 1× Weld-on tailpieces
Code No: **003H6908**

The controller will be delivered completely assembled, inclusive impulse tube between valve and actuator.

AVQ Controller

Picture	DN (mm)	k_{vs} (m ³ /h)	Connection		Code No.
	15	1.6	Cylindr. ext. thread acc. to ISO 228/1	G 3/4 A	003H6722
		2.5			003H6723
		4.0			003H6724
	20	6.3		G 1 A	003H6725
	25	8.0		G 1 1/4 A	003H6726
	32	12.5		G 1 3/4 A	003H6727
	40	16		G 2 A	003H6728
	50	20		G 2 1/2 A	003H6729
	32	12.5	Flanges PN 25, acc. to EN 1092-2		003H6730
	40	20			003H6731
	50	25			003H6732

Ordering (continuous)

Accessories

Picture	Type designation	DN	Connection	Code No.
	Weld-on tailpieces	15	-	003H6908
		20		003H6909
		25		003H6910
		32		003H6911
		40		003H6912
		50		003H6913
	External thread tailpieces	15	Conical ext. thread acc. to EN 10226-1	R 1/2 003H6902
		20		R 3/4 003H6903
		25		R 1 003H6904
		32		R 1 1/4 003H6905
		40		R 1 1/2 065B2004
		50		R 2 065B2005
	Flange tailpieces	15	Flanges PN 25, acc. to EN 1092-2	003H6915
		20		003H6916
		25		003H6917

Service kits

Picture	Type designation	DN	k _{vs} (m ³ /h)	Code No.
	Valve insert	15	1.6	003H6863
			2.5	003H6864
			4.0	003H6865
		20	6.3	003H6866
		25	8.0	003H6867
		32 / 40 / 50	12.5 / 16 / 20 / 25	003H6868
	Actuator	Fixed setting (bar)		Code No.
		0.2		003H6841

Technical data

Valve

Nominal diameter			DN	15			20	25	32	40	50
k _{VS} value			m ³ /h	1.6	2.5	4.0	6.3	8.0	12.5	16/20 ⁴⁾	20/25 ⁴⁾
Range of max. flow setting	Δp _b ¹⁾ = 0.2 bar	from		0.03	0.07	0.07	0.16	0.2	0.4	0.8	0.8
		to		0.86	1.4	2.2	3.0	3.5	8.0	10	12
		or to ³⁾		0.9	1.6	2.4	3.5	4.5	10	12	15
Cavitation factor z			≥ 0.6				≥ 0.55		≥ 0.5		
Leakage acc. to standard IEC 534			% of k _{VS}	≤ 0.02					≤ 0.05		
Nominal pressure			PN	25							
Min. differential pressure			bar	see remark ²⁾							
Max. differential pressure				20					16		
Medium			Circulation water / glycolic water up to 30%								
Medium pH			Min. 7, max. 10								
Medium temperature			°C	2 ... 150							
Connections	valve		External thread					External thread and flange			
	tailpieces		Weld-on and external thread								
			Flange					-			
Materials											
Valve body	thread		Red bronze CuSn5ZnPb (Rg5)						Ductile iron EN-GJS-400-18-LT (GGG 40.3)		
	flange		-								
Valve seat			Stainless steel, mat. No. 1.4571								
Valve cone			Dezincing free brass CuZn36Pb2As								
Sealing			EPDM								
Pressure relieve system			Piston								

¹⁾ Δp_b - differential pressure over flow restrictor

²⁾ Depends on the flow rate and valve k_{vs}; For Q_{set} = Q_{max} → Δp_{min} ≥ 0.5 bar; For Q_{set} < Q_{max} → Δp_{min} = $\left(\frac{Q}{k_{vs}}\right)^2 + \Delta p_b$
³⁾ Higher max flow are achieved at higher differential pressures over AVQ controller. In general at Δp > 1-1.5 bar

⁴⁾ Flange valve body


Technical data (continuous)

Actuator


Type		AVQ
Actuator size	cm ²	54
Nominal pressure	PN	25
Flow restrictor diff. pressure	bar	0.2
Materials		
Actuator housing	Upper casing of diaphragm	Stainless steel, mat. No.1.4301
	Lower casing of diaphragm	Dezincing free brass CuZn36Pb2As
Diaphragm		EPDM
Impulse tube		Copper tube Ø 6 × 1 mm

Application principles

- Return mounting



- Flow mounting



Installation positions



Up to medium temperature of 100°C the controllers can be installed in any position.

For higher temperatures the controllers have to be installed in horizontal pipes only, with a pressure actuator oriented downwards.


Electrical actuator

Note!

Installation positions for electrical actuators AMV(E) have to be observed as well. Please see relevant Data Sheet.




Pressure temperature diagram



Flow diagram

Sizing and setting diagram

Relation between actual flow and number of revolutions on flow restrictor. Values given are approximate.



Note:

For max flow setting on the controller diagrams from Instructions should be used.

Sizing

- Directly connected heating system

Example 1

Motorised control valve (MCV) for mixing circuit in direct-connected heating system requires differential pressure of 0.3 bar (30 kPa) and flow less than 600 l/h.

Given data:

$$\begin{aligned} Q_{\max} &= 0.6 \text{ m}^3/\text{h} \text{ (600 l/h)} \\ \Delta p_{\min} &= 0.9 \text{ bar (90 kPa)} \\ \Delta p_{\text{circuit}}^{1)} &= 0.1 \text{ bar (10 kPa)} \\ \Delta p_{\text{MCV}} &= 0.3 \text{ bar (30 kPa) selected} \\ \Delta p_b^{2)} &= 0.2 \text{ bar (20 kPa)} \end{aligned}$$

Remark:

¹⁾ $\Delta p_{\text{circuit}}$ corresponds to the required pump pressure in the heating circuit and is not to be considered when sizing the AVQ.

²⁾ Δp_b is differential pressure over flow restrictor.

The total (available) pressure loss across the controller is:

$$\Delta p_{\text{AVQ,A}} = \Delta p_{\min} - \Delta p_{\text{MCV}} = 0.9 - 0.3$$

$$\Delta p_{\text{AVQ,A}} = 0.6 \text{ bar (60 kPa)}$$

Possible pipe pressure losses in tubes, shut-off fittings, heatmeters, etc. are not included.

Select controller from flow diagram, page 4, with the smallest possible k_{VS} value considering available flow ranges.

$$k_{VS} = 1.6 \text{ m}^3/\text{h}$$

The min. required differential pressure across the selected controller is calculated from the formula:

$$\Delta p_{\text{AVQ,MIN}} = \left(\frac{Q_{\max}}{k_{VS}} \right)^2 + \Delta p_b = \left(\frac{0.6}{1.6} \right)^2 + 0.2$$



$$\Delta p_{\text{AVQ,MIN}} = 0.34 \text{ bar (34 kPa)}$$

$$\Delta p_{\text{AVQ,A}} > \Delta p_{\text{AVQ,MIN}}$$

$$0.6 \text{ bar} > 0.34 \text{ bar}$$

Solution:

The example selects AVQ DN 15; k_{VS} value 1.6; flow setting range 0.03-0.9 m³/h.



Sizing (continuous)

- Indirectly connected heating system

Example 2

Motorised control valve (MCV) for indirectly connected heating system requires differential pressure of 0.3 (30 kPa) bar and flow less than 1900 l/h.

Given data:

$Q_{\max} = 1.9 \text{ m}^3/\text{h}$ (1900 l/h)
 $\Delta p_{\min} = 1.1 \text{ bar}$ (110 kPa)
 $\Delta p_{\text{exchanger}} = 0.1 \text{ bar}$ (10 kPa)
 $\Delta p_{\text{MCV}} = 0.3 \text{ bar}$ (30 kPa) selected
 $\Delta p_b^{1)} = 0.2 \text{ bar}$ (20 kPa)

Remark:

¹⁾ Δp_b is differential pressure over flow restrictor

The total (available) pressure loss across the controller is:

$$\Delta p_{\text{AVQ,A}} = \Delta p_{\min} - \Delta p_{\text{exchanger}} - \Delta p_{\text{MCV}}$$

$$= 1.1 - 0.1 - 0.3$$

$$\Delta p_{\text{AVQ,A}} = 0.7 \text{ bar} \text{ (70 kPa)}$$

Possible pipe pressure losses in tubes, shut-off fittings, heatmeters, etc. are not included.

Select controller from flow diagram, page 4, with the smallest possible k_{VS} value considering available flow ranges.

$$k_{VS} = 4.0 \text{ m}^3/\text{h}$$

The min. required differential pressure across the selected controller is calculated from the formula:

$$\Delta p_{\text{AVQ,MIN}} = \left(\frac{Q_{\max}}{k_{VS}} \right)^2 + \Delta p_b = \left(\frac{1.9}{4.0} \right)^2 + 0.2$$



$$\Delta p_{\text{AVQ,MIN}} = 0.43 \text{ bar} \text{ (43 kPa)}$$

$$\Delta p_{\text{AVQ,A}} > \Delta p_{\text{AVQ,MIN}}$$

$$0.7 \text{ bar} > 0.43 \text{ bar}$$


Solution:

The example selects AVQ; DN 15; k_{VS} value 4.0; flow setting range 0.07-2.4 m³/h.



Design

1. Cover
2. Adjustable flow restrictor
3. Valve body
4. Valve insert
5. Pressure relieved valve cone
6. Valve stem
7. Built-in spring for flow rate control
8. Control drain
9. Control diaphragm
10. Union nut
11. Upper casing of diaphragm
12. Lower casing of diaphragm
13. Impulse tube
14. Compression fitting for impulse tube



Function

Flow volume causes pressure drop across the adjustable flow restrictor. Resulting pressures are being transferred through the impulse tubes and/or control drain in the actuator stem to the actuator chambers and act on control diaphragm for flow control. The flow restrictor diff. pressure is controlled and limited by means of built-in spring for flow control. Control valve closes on rising differential pressure and opens on falling differential pressure to control max flow.

Settings


Flow setting

Flow setting is being done by the adjustment of the flow restrictor position. The adjustment can be performed on the basis of flow adjustment diagram (see relevant instructions) and/or by the means of heat meter.


Data sheet

AVQ (PN 25)

Dimensions



DN	R ¹⁾	SW	d	L ₁ ²⁾	L ₂	L ₃	k	d ₂	n
mm									
15	1/2	32 (G 3/4A)	21	130	120	139	65	14	4
20	3/4	41 (G 1A)	26	150	131	154	75	14	4
25	1	50 (G 1 1/4A)	33	160	145	159	85	14	4
32	1 1/4	63 (G 1 3/4A)	42	-	177	184	100	18	4
40	1 1/2	70 (G 2A)	47	-	200	204	110	18	4
50	2	82 (G 2 1/2A)	60	-	244	234	125	18	4

¹⁾ Conical ext. thread acc. to EN 10226-1²⁾ Flanges PN 25, acc. to EN 1092-2

DN 15-25

DN 32-50

DN 32-50

DN	15	20	25	32	40	50
L	65	70	75	100	110	130
L1	-	-	-	180	200	230
H	109	109	109	150	150	150
H1	-	-	-	150	150	150
H2	73	73	76	103	103	103
H3	-	-	-	103	103	103
Weight (thread)	2.7	2.7	2.9	5.3	5.5	6.1
Weight (flange)	-	-	-	9.8	11.4	13.5

Note: other flange dimensions-see table for tailpieces.

Danfoss A/S

Climate Solutions • danfoss.com • +45 7488 2222

Any information, including, but not limited to information on selection of product, its application or use, product design, weight, dimensions, capacity or any other technical data in product manuals, catalogues descriptions, advertisements, etc. and whether made available in writing, orally, electronically, online or via download, shall be considered informative, and is only binding if and to the extent, explicit reference is made in a quotation or order confirmation. Danfoss cannot accept any responsibility for possible errors in catalogues, brochures, videos and other material. Danfoss reserves the right to alter its products without notice. This also applies to products ordered but not delivered provided that such alterations can be made without changes to form, fit or function of the product.

All trademarks in this material are property of Danfoss A/S or Danfoss group companies. Danfoss and the Danfoss logo are trademarks of Danfoss A/S. All rights reserved.