

Technical Information

Hydrostatics External Remote Charge Pressure Filter



www.danfoss.com



Revision history

Table of revisions

Date	Changed	Rev
November 2021	Changed document number from 'BC00000064' and '11064579' to 'BC152886484487'; added MP1 to compatibility list	0304
August 2019	Corrected long filter number	0202
March 2014	Converted to Danfoss layout - DITA CMS	0201
November 2010	Minor update	AB



Contents

General Information	
	Introduction
	Features4
System Design Parameters	
	Filtration
	Operating pressure
	Differential pressure and ß-ratio
	Bypass valve and bypass sensor
	Bypass sensor clearance
	Dimensions12



General Information

Introduction

For more than 40 years, Danfoss has been developing state-of-the-art components and systems for mobile machinery used in off-highway operations around the world. We have become a preferred supplier by offering the best of what really matters: The hardware inside your vehicle application.

Features

- Common filter head
- 3 different filter sizes
 - Compatible with
 - _ H1P
 - _ S90
 - _ S42
 - _ S40
 - _ MP1
- Integrated functionality
 - Bypass valve
 - Electric contamination indicator
- Servicebility
 - No extra space for element replacement needed, (side way removal possible)



Filtration

Remote charge pressure filtration

The remote pressure filter head is designed with a filter bypass valve and noncontacting bypass sensor. The pressure differential acting on the filter element also acts on a spring biased bypass spool. This spool is designed with a magnetic area. When a certain spool position is reached, the magnet closes a switch in the bypass sensor which allows R2 to be in parallel with R1. This occurs without any mechanical contact between the spool and the bypass sensor.

The position of the bypass spool is indicated by the change in the measured sensor

resistance. The change in resistance occurs when R2 is switched in and out of the circuit. When the filter is not being bypassed, the nominal measured resistance is 510 ohms. When the switch is closed, the nominal measured resistance is 122 ohms.

The bypass spool is designed so the bypass sensor switch will be closed before oil bypasses the filter element. This gives the machine operator an indication that the filter is very close to bypassing and a filter replacement is required.

For cold start conditions, it is typical that the filter may bypass for a short amount of time while the oil is warming up. At normal operating oil temperatures, a system that does not yet need a filter replacement will operate in the non-bypass mode. The addition of an oil temperature sensor and additional control logic, is recommended to properly determine if a filter replacement is required.

Technical data, pressures

Filter bypass sensor switch closure	Δp 3.7 - 5.1 bar [54 - 74 psi]
Bypass valve	$\Delta p 5.6 \pm 0.9 \text{ bar } [80 \pm 13 \text{ psi}]$
T000 159E	

Technical data, electric

Max. voltage	48 V
Max. power	0.6 W
Switch open	510 Ω
Switch closed	122 Ω
Resistor tolerance	1 %
Temperature range	-20 °C ÷ +100 °C [-4 °F ÷ +212 °C]
IP Rating (IEC 60 529) + DIN 40 050, part 9 with mating connector	IP 69K
T000 160E	•

Integral filter head with filter bypass sensors







Pinout

Pin	Description
1	Voltage
2	Ground
T000 162E	

Alternative pinout

Pin	Description
1	Ground
2	Voltage
T000 163E	

Pin location



For device electrical schematic, see Schematic, page 5.

H1 Filter bypass sensor mating connector parts list

Description	Quantity	Ordering number
Mating connector	1	Deutsch DTM06-2S
Secondary wedge lock	1	Deutsch WM-2S
Socket terminal	2	Deutsch 0462-201-20141
Danfoss mating connector kit	1	11031205
T000 164E		



Operating pressure

	Unit	
Maximum working pressure	bar [psi]	45 [653]
Maximum pressure (cold start)		55 [798]

Differential pressure and ß-ratio

Nominal fl ow at 30 mm ² /s and Δp 0.5 bar [7.3 psi] (clean fi lter element only)		Min β ratio
Short	60 l/min	$\beta_{7.5 (c)} = 75 \ (\beta_{5 (c)} \ge 10)$
Medium	80 l/min	
Long	105 l/min	

Bypass valve and bypass sensor

A common spool is used to activate both the bypass sensor and bypass function leading to the assurance that the bypass sensor will be closed before the bypass is engaged. The bypass sensor occurs at a filter pressure drop of 4.4 +/-0.7 bar. The minimum pressure drop between bypass sensor and open bypass is 1.0 bar.

Bypass sensor

	Diffential pressure [bar]
Bypass sensor engages at	4.4 +/- 0.7
T301 041E	

Bypass valve function

The bypass valve opens at 1.2 bar +- 0.2 bar above bypass sensor engagement pressure.





Filter Bypass Valve Characteristic (completely blocked Filter element)

Below diagramm shows the differental pressure between filter "in" and "out" with a filter element completely blocked, so that all flow runs across the filter bypass valve.





Remote filter 11001484, short, 60 l/min, and 11001485, medium 80 l/min





Remote filter 11048860, long, 105 l/min

Bypass sensor clearance

in

The bypass sensor is activated by the magnetic bypass valve. For proper function it is required to have no steel parts around the sensor within in below radius. No steel parts are allowed within a radius of 150 mm [5.91 in]. Moving steel devices or parts are not allowed within a radius of 250 mm [9.84 in].

Filter element completly blocked

P301 285

out







Dimensions



Filter assembly		In and out port size	L max. mm [inch]	Replacement element
Short	11001484	7/8 -14	205 [8.07]	11004917
Medium	11001485	7/8 -14	233 [9.17]	11004918
Long	11048860	1 1/16 -12	292 [11.49]	11004919



Danfoss

Products we offer:

- Cartridge valves
- DCV directional control valves
- Electric converters
- Electric machines
- Electric motors
- Gear motors
- Gear pumps
- Hydraulic integrated circuits (HICs)
- Hydrostatic motors
- Hydrostatic pumps
- Orbital motors
- PLUS+1[®] controllers
- PLUS+1[®] displays
- PLUS+1[®] joysticks and pedals
- PLUS+1[®] operator interfaces
- PLUS+1[®] sensors
- PLUS+1[®] software
- PLUS+1[®] software services, support and training
- Position controls and sensors
- PVG proportional valves
- Steering components and systems
- Telematics

Hydro-Gear

www.hydro-gear.com

Daikin-Sauer-Danfoss

www.daikin-sauer-danfoss.com

Danfoss Power Solutions is a global manufacturer and supplier of high-quality hydraulic and electric components. We specialize in providing state-of-the-art technology and solutions that excel in the harsh operating conditions of the mobile off-highway market as well as the marine sector. Building on our extensive applications expertise, we work closely with you to ensure exceptional performance for a broad range of applications. We help you and other customers around the world speed up system development, reduce costs and bring vehicles and vessels to market faster.

Danfoss Power Solutions – your strongest partner in mobile hydraulics and mobile electrification.

Go to www.danfoss.com for further product information.

We offer you expert worldwide support for ensuring the best possible solutions for outstanding performance. And with an extensive network of Global Service Partners, we also provide you with comprehensive global service for all of our components.

Local address:

Danfoss Power Solutions (US) Company 2800 East 13th Street Ames, IA 50010, USA Phone: +1 515 239 6000 Danfoss Power Solutions GmbH & Co. OHG Krokamp 35 D-24539 Neumünster, Germany Phone: +49 4321 871 0 Danfoss Power Solutions ApS Nordborgvej 81 DK-6430 Nordborg, Denmark Phone: +45 7488 2222 Danfoss Power Solutions Trading (Shanghai) Co., Ltd. Building #22, No. 1000 Jin Hai Rd Jin Qiao, Pudong New District Shanghai, China 201206 Phone: +86 21 2080 6201

Danfoss can accept no responsibility for possible errors in catalogues, brochures and other printed material. Danfoss reserves the right to alter its products without notice. This also applies to products already on order provided that such alterations can be made without subsequent changes being necessary in specifications already agreed. All trademarks in this material are property of the respective companies. Danfoss and the Danfoss logotype are trademarks of Danfoss A/S. All rights reserved.