

Data Sheet

Mini bearing temperature sensor Type **MBT 2310**

Compact bearing temperature sensor



The MBT 2310 temperature sensor series is specially designed for measuring the bearing temperature at applications with confined space and the purpose is to enable early warning in situations where an overheated bearing could lead to a machine havoc.

To obtain a fast reaction time the measuring element is placed at the very tip of the sensor tube ensuring a response time of down to $\tau_{0.5} = 4$ sec. in water.

The sensor is equipped with a spring-loaded sensor tube which enables physical contact between the bearing and sensor tube.

Features:

- Monitoring of bearing temperatures where there is risk of overheating, in applications such as:
 - Engine bearings
 - Gearbox bearings
 - Power transmission bearings
- 1. Based on Pt 100 / Pt 1000 / NTC technology
- 2. Spring loaded sensor tube to ensure optimal contact with the bearing.

Function

Spring function

Figure 1: Spring function




Table 1: Spring function

Material	Thickness
Stainless steel process connection	A = 0 – 6 mm

Product specification

Technical data

Table 2: Technical data

Ambient temperature @ plug	-25 – 85°C
Storage temperature	-25 – 85°C
Process connection	10 x 1 mm
Hex 19	Tightening torque 10 – 15 Nm
Measuring rang NTC elements	-25°C – 125°C
Measuring range Pt elements	Pt: -25°C – 200°C
Protection tube	ø6x 1 mm

Response time

Table 3: Response time

Protection tube	Indicative response times			
	Water 0.2 m/s		Air 1 m/s	
	$t_{0.5}$	$t_{0.9}$	$t_{0.5}$	$t_{0.9}$
6 x 1 mm	4 s	13.2 s	55 s	210 s

Material

Table 4: Material

Protection tube in contact with the media	AISI 316
O-ring	FPM
Process connection	SUS303
Gasket	Silicone
Electrical connections	AMP JPT
	AMP super seal
	Metri-Pack 150
	Deutsch DT04 (2P)
	M12 x 1 (4P)
	Cable with/without plug

Mechanical and environmental specifications


Table 5: Mechanical and environmental specifications

Sensor tolerance		EN 60751 Class B: $\pm (0.3 \text{ }^\circ\text{C} + 0.005 \times t)$ t = temperature of medium, numerical value
Vibration stability		Vibration test 20 - 2000Hz, 15.3g, 1 oct/min. Time: 3 x 2 hours (X-Y-Z-directions), total 6 hour Shock test (50g/6ms)
Enclosure	According to IEC 60529	Pin type
AMP Junior Power Timer	IP 67	2-pin Sn plated CuSn6
AMP super seal	IP 67	2-pin Sn plated
Metri-Pack 150	IP 67	2-pin Sn plated
Deutsch DT04 (2P)	IP 67	2-pin Sn plated
M12 x 1 (4P)	IP 67	4-pin Au, EN 60947-5-2
Cable with/without plug	IP 65	Silicone cable

Ordering

Ordering standards

Figure 2: Specification code for MBT 2310



Certificates, declaration and approvals

The list contains all certificates, declarations, and approvals for this product type. Individual code number may have some or all of these approvals, and certain local approvals may not appear on the list.

Some approvals may change over time. You can check the most current status at danfoss.com or contact your local Danfoss representative if you have any questions.

Online support

Danfoss offers a wide range of support along with our products, including digital product information, software, mobile apps, and expert guidance. See the possibilities below.

The Danfoss Product Store



The Danfoss Product Store is your one-stop shop for everything product related—no matter where you are in the world or what area of the cooling industry you work in. Get quick access to essential information like product specs, code numbers, technical documentation, certifications, accessories, and more.

Start browsing at store.danfoss.com.

Find technical documentation



Find the technical documentation you need to get your project up and running. Get direct access to our official collection of data sheets, certificates and declarations, manuals and guides, 3D models and drawings, case stories, brochures, and much more.

Start searching now at www.danfoss.com/en/service-and-support/documentation.

Danfoss Learning



Danfoss Learning is a free online learning platform. It features courses and materials specifically designed to help engineers, installers, service technicians, and wholesalers better understand the products, applications, industry topics, and trends that will help you do your job better.

Create your Danfoss Learning account for free at www.danfoss.com/en/service-and-support/learning.

Get local information and support



Local Danfoss websites are the main sources for help and information about our company and products. Find product availability, get the latest regional news, or connect with a nearby expert—all in your own language.

Find your local Danfoss website here: www.danfoss.com/en/choose-region.

Spare Parts



Get access to the Danfoss spare parts and service kit catalog right from your smartphone. The app contains a wide range of components for air conditioning and refrigeration applications, such as valves, strainers, pressure switches, and sensors.

Download the Spare Parts app for free at www.danfoss.com/en/service-and-support/downloads.

Any information, including, but not limited to information on selection of product, its application or use, product design, weight, dimensions, capacity or any other technical data in product manuals, catalogues descriptions, advertisements, etc. and whether made available in writing, orally, electronically, online or via download, shall be considered informative, and is only binding if and to the extent, explicit reference is made in a quotation or order confirmation. Danfoss cannot accept any responsibility for possible errors in catalogues, brochures, videos and other material. Danfoss reserves the right to alter its products without notice. This also applies to products ordered but not delivered provided that such alterations can be made without changes to form, fit or function of the product. All trademarks in this material are property of Danfoss A/S or Danfoss group companies. Danfoss and the Danfoss logo are trademarks of Danfoss A/S. All rights reserved.