



Medium Duty Series
Danfoss® Pumps

Kit 70160-903

-02 Design

Shimming

Process


Introduction

This shim kit is to replace the crush ring within the trunnion cover. If the camplate, trunnion cover or housing is replaced during servicing, the old crush ring can no longer be used to assure proper preload.

Shimming procedures:

- 1 Measure the thickness of the existing crush ring.
- 2 To obtain a starting point stack shims to the measurement of existing crush ring. Then insert shims into the trunnion cover in the same location as the removed crush ring.
- 3 Assemble the housing sub-assembly consisting of the housing, camplate, bearings and trunnion covers. Install the trunnion cover bolts and torque to 56,9 N·m [42 lbf·ft].
- 4 With a torque wrench, check the torque required to rotate the control shaft. The specified torque level is $2,26 \pm 0,6$ N·m [205 lbf·in].
 - If torque level is too low, add additional shims and repeat steps 3 and 4 until specified torque levels are achieved.
 - If torque level is too high, remove shims and repeat steps 2 and 3 until specified torque levels are achieved.
- 5 Finish the assembly of the pump.

Copyright Danfoss Corporation, 1999
All Rights Reserved
Printed in USA



Products we offer:

- Cartridge valves
- DCV directional control valves
- Electric converters
- Electric machines
- Electric motors
- Gear motors
- Gear pumps
- Hydraulic integrated circuits (HICs)
- Hydrostatic motors
- Hydrostatic pumps
- Orbital motors
- PLUS+1® controllers
- PLUS+1® displays
- PLUS+1® joysticks and pedals
- PLUS+1® operator interfaces
- PLUS+1® sensors
- PLUS+1® software
- PLUS+1® software services, support and training
- Position controls and sensors
- PVG proportional valves
- Steering components and systems
- Telematics

Hydro-Gear

www.hydro-gear.com

Daikin-Sauer-Danfoss

www.daikin-sauer-danfoss.com

Danfoss Power Solutions is a global manufacturer and supplier of high-quality hydraulic and electric components. We specialize in providing state-of-the-art technology and solutions that excel in the harsh operating conditions of the mobile off-highway market as well as the marine sector. Building on our extensive applications expertise, we work closely with you to ensure exceptional performance for a broad range of applications. We help you and other customers around the world speed up system development, reduce costs and bring vehicles and vessels to market faster.

Danfoss Power Solutions – your strongest partner in mobile hydraulics and mobile electrification.

Go to www.danfoss.com for further product information.

We offer you expert worldwide support for ensuring the best possible solutions for outstanding performance. And with an extensive network of Global Service Partners, we also provide you with comprehensive global service for all of our components.

Local address:

**Danfoss
Power Solutions (US) Company**
2800 East 13th Street
Ames, IA 50010, USA
Phone: +1 515 239 6000

**Danfoss
Power Solutions GmbH & Co. OHG**
Krokamp 35
D-24539 Neumünster, Germany
Phone: +49 4321 871 0

**Danfoss
Power Solutions ApS**
Nordborgvej 81
DK-6430 Nordborg, Denmark
Phone: +45 7488 2222

**Danfoss
Power Solutions Trading
(Shanghai) Co., Ltd.**
Building #22, No. 1000 Jin Hai Rd
Jin Qiao, Pudong New District
Shanghai, China 201206
Phone: +86 21 2080 6201