



Marauder® EHK006



Engineered to pump with confidence

Boston® Marauder EHK006 is designed for concrete, plaster and grout pumping. Marauder is built to withstand the toughest environments and meets a constant pressure of 1,233 psi. across our full size range, bringing you the pressure you need in any application.



Markets/Applications

- Construction
- Cement
- Swimming pool
- Tunnel faces
- Dams
- Ready-mix concrete
- Gypsum spraying
- Transfer of sand



Sells Against

- Continental Allcrete® Textile (plaster, grout & concrete)
- Continental PGC Placement Textile

Features

- High pressure use up to 1233 psi.
- Meets the requirements of ASME B30.27-2014
- For high pressure concrete pumping and spraying plaster, grout, sand, gypsum, and ready mixed concrete
- Light weight for hand held applications


Order Fulfillment

- Made to Stock
- Made to Order



Marauder EHK006

High pressure solution for spraying plaster and grout, sand and ready-mix concrete pumping



| Number | Hose I.D. | | Hose O.D. | | Operating Pressure | | Min. Burst Pressure | | Weight | | Length | |
|---------------|-----------|------|-----------|------|--------------------|------|---------------------|------|--------|--------|--------|-----|
| | mm | in | mm | in | bar | psi | bar | psi | kg/m | lbs/ft | mtr | ft |
| EHK006-20-100 | 32.0 | 1.25 | 48.8 | 1.92 | 85.0 | 1233 | 178 | 2581 | 1.22 | .820 | 30.5 | 100 |
| EHK006-24-100 | 38.0 | 1.50 | 58.7 | 2.31 | 85.0 | 1233 | 178 | 2581 | 1.81 | 1.21 | 30.5 | 100 |
| EHK006-32-100 | 50.8 | 2.00 | 72.0 | 2.83 | 85.0 | 1233 | 178 | 2581 | 2.40 | 1.61 | 30.5 | 100 |
| EHK006-40-100 | 63.5 | 2.50 | 86.3 | 3.40 | 85.0 | 1233 | 178 | 2581 | 3.01 | 2.02 | 30.5 | 100 |
| EHK006-48-100 | 76.2 | 3.00 | 96.6 | 3.92 | 85.0 | 1233 | 178 | 2581 | 3.65 | 2.45 | 30.5 | 100 |
| EHK006-64-100 | 101.6 | 4.00 | 126.0 | 4.92 | 85.0 | 1233 | 178 | 2581 | 4.74 | 3.18 | 30.5 | 100 |
| EHK006-80-100 | 127.0 | 5.00 | 153.5 | 6.04 | 85.0 | 1233 | 178 | 2581 | 6.38 | 4.29 | 30.5 | 100 |

Construction

Tube Abrasion resistant anti-static natural rubber

Reinforcement

High tensile synthetic textile and anti-static copper wire

Cover

Abrasion, ozone and weather resistant pin-pricked synthetic rubber

Color

Black

Operating Temperature

-40°C to +70°C
(-40°F to +158°F)

Certifications

Meets the requirements of ASME B30.27-2014

Packaging

MTS: 100 ft.

MTO: 100 ft.

Coil on pallet

Abrasion loss value acc.
DIN53516 ≤60mm³

Type of couplings

• Victaulic male NPT

Contact coupling manufacturer for attachment procedure and other coupling recommendations