

 **Sabertooth® H0347**



# Engineered for a smooth transfer

Boston® Sabertooth is a superior option for transfer and discharge of dry bulk and abrasive materials. Designed with a static dissipating inner-tube and dual helical wire reinforcement, this hose is built to transfer the toughest of material ranging from dry bulk, cleaning agents, dry cement and more.



## Markets/Applications

- Transfer of dry bulk, bottle caps and cleaning agents
- Discharge of abrasive material
- In-plant transfers
- Tank truck
- Bottling plant
- Coal plant
- Dry cement operations
- Well service



## Sells Against

- Continental Diversipipe® 150

## Features

- Anti-static inner-tube
- Dual helical wire reinforcement
- 4:1 safety factor


## Order Fulfillment

- Made to Stock



# Sabertooth H0347

Transfer and discharge of dry bulk and abrasive materials



Number	Hose I.D.		Hose O.D.		Operating Pressure		Min. Burst Pressure		Minimum Bend Radius		Vacuum		Weight		Length	
	mm	in	mm	in	bar	psi	bar	psi	mm	in	kPa	in/Hg	kg/m	lbs/ft	mtr	ft
H034748-100	76.2	3.00	101.6	4.00	7.0	100	28.0	400	228.6	9.00	94.8	28	4.76	3.20	30.5	100
H034764-100	101.6	4.00	127.0	5.00	7.0	100	28.0	400	279.4	11.00	94.8	28	6.55	4.40	30.5	100

### Construction

**Tube** Static dissipating natural rubber/SBR

### Operating Temperature

-23°C to +71°C  
(-10°F to +160°F)

### Type of couplings

- Cam and groove
- Combination nipple

### Reinforcement

2-ply fiber with dual helical wires

### Packaging

100 ft.

Contact coupling manufacturer for attachment procedure and other coupling recommendations

**Cover** Synthetic rubber/SBR

**Color** Black