



Engineered for a smooth transfer

Boston® Sabertooth is a superior option for transfer and discharge of dry bulk and abrasive materials. Designed with a static dissipating inner-tube and dual helical wire reinforcement, this hose is built to transfer the toughest of material ranging from dry bulk, cleaning agents, dry cement and more.

Features

- Anti-static inner-tube
- Dual helical wire reinforcement
- 4:1 safety factor



Markets/Applications

- Transfer of dry bulk, bottle caps and cleaning agents
- Discharge of abrasive material
- In-plant transfers
- Tank truck
- Bottling plant
- Coal plant
- Dry cement operations
- Well service



Sells Against

- Continental Diversipipe® 150

Order Fulfillment


- Made to Stock

ENGINEERING
TOMORROW

Danfoss



Transfer and discharge of dry bulk and abrasive materials



Number	Hose I.D.		Hose O.D.		Operating Pressure		Min. Burst Pressure		Minimum Bend Radius		Vacuum		Weight		Length	
	mm	in	mm	in	bar	psi	bar	psi	mm	in	kPa	in/Hg	kg/m	lbs/ft	mtr	ft
H034748-100	76.2	3.00	101.6	4.00	7.0	100	28.0	400	228.6	9.00	94.8	28	4.76	3.20	30.5	100
H034764-100	101.6	4.00	127.0	5.00	7.0	100	28.0	400	279.4	11.00	94.8	28	6.55	4.40	30.5	100

Construction

Tube Static dissipating natural rubber/SBR

Operating Temperature

-23°C to +71°C
(-10°F to +160°F)

Type of couplings

- Cam and groove
- Combination nipple

Reinforcement

2-ply fiber with dual helical wires

Packaging

100 ft.

Contact coupling manufacturer for attachment procedure and other coupling recommendations

Cover Synthetic rubber/SBR

Color Black

Danfoss Power Solutions
2800 East 13th Street • Ames, IA 50010, USA • Phone: +1 515 239 6000

Boston is a registered trademark of Danfoss. All other trademarks are property of their respective owners.

Danfoss can accept no responsibility for possible errors in catalogs, brochures and other printed material. Danfoss reserves the right to alter its products without notice. This also applies to products already on order provided that such alterations can be made without subsequent changes being necessary in specifications already agreed. All trademarks in this material are property of the respective companies. Danfoss and the Danfoss logotype are trademarks of Danfoss A/S. All rights reserved.