



## Concord 250 Steam™ H9568



# Engineered to shift the **steam**

Steam transfer can be a very dangerous application, therefore it is crucial to utilize products that are designed and built to provide maximum safety and reliability. Built with an EPDM construction and allowing a safe transfer up to 450°F, Concord® 250 is a premium solution on the market for steam transfer.

Boston® provides a full system solution offering our qualified EJ fittings in either bulk or assembly that seamlessly partner with our Concord 250 hose. This hose is ideal for in-plant processing and cleaning applications.



### Markets/Applications

- Refining and petrochemical
- Paper industry
- Industrial cleaning markets
- Oil and gas exploration
- Steel
- Ship building
- Transfer of steam for processing products and cleaning equipment



### Sells Against

- Continental Flexsteel® 250 ORS Steam Hose
- Continental MIL-DTL-29210E
- Continental DAMPF Trix® 6000 Steam
- Parker STEAM-LANCE® 250
- Gates Plant Master® Steam 250

### Features

- 10:1 safety factor
- EPDM construction
- Extreme temperature range
- Qualified with Danfoss fittings
- Available in bulk & assembly options
- Offered in red & black color options

### Order Fulfillment

- Made to Stock



# Concord 250 Steam H9568

Transfer of steam for processing products and cleaning equipment



Number	Hose I.D.		Hose O.D.		Operating Pressure		Min. Burst Pressure		Weight		Length	
	mm	in	mm	in	bar	psi	bar	psi	kg/m	lbs/ft	mtr	ft
H956808BK	12.7	0.50	26.9	1.06	17.2	250	172	2500	0.68	0.46	15.2	50
H956812BK	19.1	0.75	35.1	1.38	17.2	250	172	2500	1.04	0.70	15.2	50
H956816BK	25.4	1.00	40.1	1.58	17.2	250	172	2500	1.43	0.96	15.2	50

## H9568 Assemblies

Part Number	Description
FK6500HHH6000	H956808, 50 ft
FK6500KKK6000	H956812, 50 ft
FK6500MMK6000	H956816, 50 ft

Assembly includes male pipe solid & wing nut swivel ground joint fitting

### Construction

**Tube** EPDM

### Reinforcement

2-wire braid

**Cover** Pin-pricked EPDM

**Colors** Black (BK), Red (RD)

### Operating Temperature

Maximum Operating  
+232°C (+450°F)

### Packaging

50, 100, 350 ft. bulk  
50 ft. assemblies

### Type of couplings

Danfoss EJ series

Contact coupling manufacturer for attachment procedure and other coupling recommendations

Danfoss Power Solutions  
2800 East 13th Street • Ames, IA 50010, USA • Phone: +1 515 239 6000

Boston is a registered trademark of Danfoss. All other trademarks are property of their respective owners.

Danfoss can accept no responsibility for possible errors in catalogs, brochures and other printed material. Danfoss reserves the right to alter its products without notice. This also applies to products already on order provided that such alterations can be made without subsequent changes being necessary in specifications already agreed. All trademarks in this material are property of the respective companies. Danfoss and the Danfoss logotype are trademarks of Danfoss A/S. All rights reserved.