

Nitrogen H8811

Boston by Danfoss Nitrogen H8811 Specialty Nitrogen



Engineered for safe transfer

Boston® nitrogen hose is a solution built for nitrogen transfer in the toughest of industries including petrochemical and refineries. Designed with a pin-pricked neoprene cover, this hose ensures safe and reliable transfer of media, end to end. Offered in blue and yellow hose color options and qualified with Danfoss fittings, this is the premium solution on the market for nitrogen transfer.



Markets/Applications

- For transfer of nitrogen at ambient temperatures
- Refineries
- Petroleum industry



Sells Against

- Continental Nitrogen Service
- Parker 7123 Insert Gas Hose

Features

- 4 spiral fiber reinforcement
- 4:1 safety factor
- Pin-pricked neoprene cover
- Blue and yellow color options

Order Fulfillment

- Made to Stock

Nitrogen H8811

Nitrogen service for the toughest petrochemical and refinery applications

Boston by Danfoss Nitrogen H881112 Specialty Nitrogen 19.1 MM (0.75 IN) DN19 21 BAR (300 PSI) -40°C to +82°C (-40°F to +180°F) YYYY-MM-DD Made in USA /-/- Lot Code



Number	Hose I.D.		Hose O.D.		Operating Pressure		Min. Burst Pressure		Weight		Length	
	mm	in	mm	in	bar	psi	bar	psi	kg/m	lbs/ft	mtr	ft
H881112BU-250	19.1	0.75	30.2	1.19	21.0	300	84.0	1200	0.57	0.38	76.2	250

Construction

Tube Nitrile

Reinforcement

4-textile

Cover Pin-pricked neoprene

Colors Blue (BU), Yellow (YW)

Operating Temperature

-40°C to 82°C
(-40°F to 180°F)

Packaging

250 ft.

Type of couplings

- Danfoss 4T series
- Danfoss TTC/Z series
- Barbed inserts
- Boss male
- Ground joint female

Contact coupling manufacturer for attachment procedure and other coupling recommendations

Danfoss Power Solutions
2800 East 13th Street • Ames, IA 50010, USA • Phone: +1 515 239 6000

Boston is a registered trademark of Danfoss. All other trademarks are property of their respective owners.

Danfoss can accept no responsibility for possible errors in catalogs, brochures and other printed material. Danfoss reserves the right to alter its products without notice. This also applies to products already on order provided that such alterations can be made without sub sequential changes being necessary in specifications already agreed. All trademarks in this material are property of the respective companies. Danfoss and the Danfoss logotype are trademarks of Danfoss A/S. All rights reserved.