

Fact Sheet

VLT® OneGearDrive®

VLT® OneGearDrive® comprises a high-efficiency permanent magnet (PM) motor coupled to an optimized bevel gearbox. As part of the Danfoss VLT® FlexConcept® the VLT® OneGearDrive® is an energy-efficient drive system that helps to optimize plant productivity and reduce energy costs.

With only one motor type and three available gear ratios, the motor concept covers all typical versions of conveyor drives commonly used in the food and beverage industry. Furthermore, the restricted range of physical configurations of the VLT® OneGearDrive® simplifies spares holding and makes it more cost efficient, easing engineering and installation thanks to uniform mechanical dimensions.

Flexible plant design

In combination with the VLT® AutomationDrive FC 302 or the VLT® Decentral Drive FCD 302 the VLT® OneGearDrive® is equally suited to central and decentral installations, giving the plant designer complete flexibility from the outset. As a whole, the system can reach energy savings of up to 40% compared with conventional systems.


Two versions

The VLT® OneGearDrive® comes in two versions, the VLT® OneGearDrive® Standard for use in dry and wet production areas and the

VLT® OneGearDrive® Hygienic for use in wet areas, areas with high cleaning intensity and aseptic and clean room production areas.



VLT® OneGearDrive® Hygienic



VLT® OneGearDrive® Standard with brake

Feature	Benefit
High system efficiency including drive	– Save money and energy – up to 40% energy savings compared to conventional systems
High-efficiency permanent-magnet three-phase synchronous 10-pole motor with bevel gear drive	– Better than Super Premium Efficiency class IE4 (comparing to induction motor only). Will comply to highest IES2 class with FC 302
Available hollow shaft diameters: 30, 35, 40 mm and 3 imperial shaft sizes	– Flexible adaption to customer standards
Completely smooth enclosure leaves no crevices or dirt traps	– Easy to clean – Safe production
Motor connection with Danfoss CleanConnect® stainless steel circular connector	– Safe connection in wet areas – Fast installation and replacement – High cleanability
Motor and brake connections via terminal box with CageClamp® technology	– Fast, reliable connection – Lower installation cost
Aseptic coating	– Resistant to detergents and disinfectants (pH 2..14)
Gearbox without breather vents and use of food grade lubricants compliant with FDA and NSF requirements	– Up to 35,000 operating hours in partial load between oil change
High degrees of protection: – IP67 and IP69K (OGD- H) – IP67 (OGD-S)	– Unrestricted use in wash down areas – High protection in wash down areas
Fan-free operation	– Less noise emission – No airborne germs and dirt particles are drawn into the motor and then expelled back into the surrounding air
Only 3 gearbox ratios in one common design	– Up to 70% reduction in variants reduces spare part stock
Compatible with all Danfoss drives, FC 302 and FCD 302 from 0.75 to 3 kW	– Free choice of central or decentral installation

Achieve up to

70%

variant reduction with VLT® OneGearDrive® together with VLT® AutomationDrive FC 302 or VLT® Decentral Drive FCD 302.

In both versions, the completely smooth, easy-to-clean surface free of cooling fins, prevents pockets of dirt from forming and allows detergents to drain off freely. The fan-free motor avoids the risk of airborne germs and dirt particles being drawn in and then expelled back into the surrounding air.

Hygienic design

The VLT® OneGearDrive® Hygienic complies with the requirements for best cleaning and hygienic design. It is certified as usable for clean rooms and aseptic filling by IPA (Fraunhofer institute) according to the dedicated "Air Cleanliness Classification" DIN EN ISO 14644-1.






Specifications


Power rating0.75-2.2 kW
 Speed max.....3000 rpm
 Frequency max.....250 Hz
 Nominal current5.5 A
 Torque.....2.35 Nm/A
 Voltage155 V/1000 rpm
 Weight.....Approx. 22 kg

Speed/ torque characteristics

Gear ratios 5.92; $i = 14.13$ and $i = 31.13$



Dimensions



Dimensions of Danfoss VLT® OneGearDrive® Hygienic in mm

Danfoss Drives Salg Danmark, Jægstrupvej 3, 8361 Hasselager. Tlf. +45 6991 8080, drives.danfoss.dk, E-mail: kundeservice.dk@danfoss.com

Danfoss can accept no responsibility for possible errors in catalogues, brochures and other printed material. Danfoss reserves the right to alter its products without notice. This also applies to products already on order provided that such alterations can be made without consequential changes being necessary in specifications already agreed. All trademarks in this material are property of the respective companies. Danfoss and the Danfoss logotype are trademarks of Danfoss A/S. All rights reserved.