ENGINEERING TOMORROW



Data Sheet

Hermetic bi-flow filter drier Type **DMB** and **DCB**

DMB and DCB are for use in liquid lines on heat pumps.



Hermetic bi-flow filter driers, types DMB and DCB are for use in liquid lines on heat pumps.

Hermetic bi-flow filter driers have built-in check valves which ensure that refrigerant liquid always flows through the filter driers from the outer side of the filter core towards the center. Thus all dirt particles are retained irrespective of flow direction.

DMB and DCB filter driers ensure fast and effective adsorption of moisture as well as organic and inorganic acids.

When building heat pump systems, the use of bi-flow filters can, depending on the type of system, save up to ten solder connections. This reduces production costs and the number of potential leakage points.

Available with flare and solder (Copper and cuplated steel) connections.

For other connections please contact your Danfoss Sales Representative.



Features

The Core type DMB

- 100% 3Å Molecular Sieve core
- High drying capacity minimizing the risk of acid formation (hydrolysis)
- Recommended for use with HFO, HC, HFC and HCFC refrigerants
- · Will not deplete oil additives

The Core type DCB

- 80% 3Å Molecular Sieve with 20% activated alumina
- · Perfect core blend for systems that operate at high condensing temperatures and require high drying capacity
- Recommended for use with HFO, HC, HFC and HCFC refrigerants

The Shell


- PED approved for PS 46 bar
- Available with flare and solder (Copper and cu-plated steel) connections
- Optimum flow characteristics and dirt retention
- The check valves are not sensitive to dirt and give minimum restriction, irrespective of flow direction

The Filter

- Particles above 25 µm are retained
- No dirt released by reversing the flow direction
- Available in sizes 05 30 cubic inches

Construction

Figure 1: Flow direction






Product specification

Technical data

Figure 2: Flare connection








Table 1: Surface and volume

Filter	Solid core surface	Solid core volume	Filter drier volume (shell volume)	Filter drier volume (net volume)
	[cm²]	[cm³]	[1]	[1]
DMB/DCB 05	57	23	0.122	0.085
DMB/DCB 08	90	44	0.173	0.115
DMB/DCB 16	129	80	0.354	0.248
DMB/DCB 30	275	204	0.730	0.501

Table 2: Acid capacity DCB

Filter	Acid capacity ⁽¹⁾
riitei	[g]
DCB 05	0.52
DCB 08	0.99
DCB 16	1.86
DCB 30	4.51

 $^{^{(1)}}$ Adsorption capacity of oleic acid at 0.05 TAN (Total Acid Number).

Temperature range:

-40 - 70 °C

Dirt retention Particles $> 25 \ \mu m$

Identification

Table 3: Type codes

Туре	Codes	Description	
Filter drier	D	Drier	
Solid core	C	80% Molecular Sieve / 20% activated alumina	
Solid Core	M	100% Molecular Sieve core	
Application	В	Bi-flow	
	08	8 in. ³	
Filter housing volume (approx.)	16	16 in. ³	
	30	30 in. ³	

Hermetic bi-flow filter drier, Type DMB and DCB

Туре	Codes	Description
	2	1/4 in. / 6 mm
	3	3/8 in. / 10 mm
Connection (filter connection in 1/8 of an inch incre-	4	½ in. / 12 mm
ments)	5	5/8 in. / 16 mm
	7	⁷ ⁄ ₈ in. / 22 mm
	9	1½ in.
Connection type	(blank)	Flare connection
	S	Solder connection (cu-plated steel connector)

Example for type codes

11	 Itar	\sim	r	n
D	 lter			-

М Solid core

В Application

16 Size (volume)

Connection (filter connection in 1/8 of an inch increments)

Connection type

Selection

Table 4: Type selection is made considering the application

Refrigerant and oil types		DCB	DMB
Refrigerant	HFO	Recommended	Recommended
	HC (1)	Recommended	Recommended
	HFC	Recommended	Recommended
	HCFC	Recommended	Recommended
	Mineral or AB	Recommended	Recommended
Oil	POE or PAG, pure	Recommended	Recommended
	POE or PAG, with additives	Not recommended (2)	Recommended

 $^{^{(1)}}$ Only solder versions (cu-plated / pure copper) and connection sizes below 25 mm are approved for flammable refrigerants now

Dimensions and weights

Figure 5: Flare connection (30 cu.in)




Figure 6: Flare connections (08- 16 cu.in)




Table 5: DMB and DCB

Turno	А	L	D ₁	D ₂	Net weight
Туре	[mm]	[mm]	[mm]	[mm]	[Kg]
DMB/DCB 082	101	145	58	54	0.38
DMB/DCB 083	101	158	58	54	0.42
DMB/DCB 084	101	166	58	54	0.45
DMB/DCB 162	110	154	79	75	0.76
DMB/DCB 163	110	167	79	75	0.79
DMB/DCB 164	110	175	79	75	0.83

⁽²⁾ DCB Hermetic filter driers contain activated alumina, which is a polar material used for acid adsorption. Many oil additives are also polar substances and can be adsorbed by the activated alumina, rendering them useless, and reducing the drier's acid capacity, though this is not harmful to the system



Туре	А	L	D ₁	D ₂	Net weight
	[mm]	[mm]	[mm]	[mm]	[Kg]
DMB/DCB 165	110	184	79	75	0.86
DMB/DCB 303	188	245	80	76	1.10
DMB/DCB 304	188	253	80	76	1.20
DMB/DCB 305	188	262	80	76	1.20

Figure 7: Solder connection (cu-plated 30cu.in)




Figure 8: Solder connection (cu-plated 08-16 cu.in)




Table 6: DMB and DCB

Type	А	В	L	D ₁	D ₂	Net weight
Туре	[mm]	[mm]	[mm]	[mm]	[mm]	[Kg]
DMB/DCB 082s	101	119	133	58	54	0.37
DMB/DCB 083s	101	121	139	58	54	0.38
DMB/DCB 084s	101	123	143	58	54	0.40
DMB/DCB 163s	110	130	148	79	75	0.75
DMB/DCB 164s	110	132	152	79	75	0.77
DMB/DCB 165s	110	136	160	79	75	0.78
DMB/DCB 304s	188	209	230	80	76	1.00
DMB/DCB 305s	188	212	236	80	76	1.10
DMB/DCB 307s	188	214	250	80	76	1.10
DMB 309s	188	198	252	80	76	1.44

Figure 9: Solder connection (pure copper 30cu.in)




Figure 10: Solder connection (pure copper 05cu.in)





Figure 11: Solder connection (pure copper 08-16cu.in)



Hermetic bi-flow filter drier, Type DMB and DCB

Table 7: DMB/DCB solder connection

Туре	Solder connec- tion	A	В	L	D1	D2	Net weight
	[in] [mm]	[mm]	[mm]	[mm]	[mm]	[mm]	kg
DMB/DCB 054s	1/2	75	96	117	58	54	0.31
DMB/DCB 055s	5/8	75	99	123	58	54	0.35
DMB/DCB 082s	1/4(6)	101	117	133	58	54	0.36
DMB/DCB 083s	3/8(10)	101	120	139	58	54	0.37
DMB/DCB 084s	1/2(12)	101	122	143	58	54	0.38
DMB/DCB 163s	3/8(10)	110	129	148	79	75	0.74
DMB/DCB 164s	1/2(12)	110	131	152	79	75	0.76
DMB/DCB 165s	5/8(16)	110	134	158	79	75	0.77
DMB/DCB 304s	1/2(12)	188	209	230	80	76	1.00
DMB/DCB 305s	5/8(16)	188	212	236	80	76	1.10
DMB/DCB 307s	7/8(22)	188	214	250	80	76	1.10



Ordering

Figure 12: Flare connection



Table 8: Type DMB flare

Туре	Co	nn.	Multi	i pack
	[in.]	[mm]	Qty.	Code no.
DMB 082	1/4	6	24	023Z1078
DMB 083	3/8	10	24	023Z1076
DMB 084	1/2	12	24	023Z1074
DMB 163	3/8	10	12	023Z1083
DMB 164	1/2	12	12	023Z1081
DMB 165	5/8	16	12	023Z1080
DMB 303	3/8	10	8	023Z1419
DMB 304	1/2	12	8	023Z1418
DMB 305	5/8	16	8	023Z1417

Table 9: Type DCB flare

Туре	Co	nn.	Multi	Multi pack	
	[in.]	[mm]	Qty.	Code no.	
DCB 082	1/4	6	24	023Z1068	
DCB 083	3/8	10	24	023Z1067	
DCB 084	1/2	12	24	023Z1066	
DCB 162	1/4	6	12	023Z1073	
DCB 163	3/8	10	12	023Z1072	
DCB 164	1/2	12	12	023Z1071	
DCB 165	5/8	16	12	023Z1069	
DCB 303	3/8	10	8	023Z1409	
DCB 304	1/2	12	8	023Z1408	
DCB 305	5/8	16	8	023Z1407	

Figure 13: Solder (cu-plated steel connectors)




Table 10: Type DMB Solder (cu-plated steel connectors)

Table 10. Type Divid Solder (cu-plated steel conflectors)									
Туре	Conn.	Multi pack		Industrial pack		Conn.	Multi pack		
	[in.]	Qty.	Code no.	Qty.	Code no.	[mm]	Qty.	Code no.	
DMB 082s	1/4	24	023Z2079	-	-	6	24	023Z1996	
DMB 083s	3/8	24	023Z2078	16	023Z2091	10	24	023Z1995	
DMB 084s	1/2	24	023Z2077	16	023Z2090	12	24	023Z1993	
DMB 163s	3/8	12	023Z2082	12	023Z2094	10	12	023Z1992	
DMB 164s	1/2	12	023Z2081	12	023Z2093	12	12	023Z1991	
DMB 165s	5/8	12	023Z2080	12	023Z2092	-	-	-	
DMB 303s	3/8	8	023Z1481	-	-	-	-	-	
DMB 304s	1/2	8	023Z1479	-	-	12	8	023Z1451	
DMB 305s	5/8	8	023Z1478	8	023Z1487	-	-	-	
DMB 307s	7/8	8	023Z1477	8	023Z1498	-	-	-	
DMB 309s	11/8	-	-	8	023Z1493	-	-	-	



Table 11: Type DCB Solder (cu-plated steel connectors)

······································								
Туре	Conn.	Multi pack		Industrial pack		Conn.	Conn. Multi pac	
	[in.]	Qty.	Code no.	Qty.	Code no.	[mm]	Qty.	Code no.
DCB 082s	1/4	24	023Z1999	-	-	-	-	-
DCB 083s	3/8	24	023Z1998	-	-	10	24	023Z1994
DCB 084s	1/2	24	023Z1997	-	-	-	-	-
DCB 163s	3/8	12	023Z2076	-	-	-	-	-
DCB 164s	1/2	12	023Z2075	-	-	12	12	023Z1099
DCB 165s	5/8	12	023Z2074	12	023Z2089	-	-	-
DCB 304s	1/2	8	023Z1470	-	-	-	-	-
DCB 305s	5/8	8	023Z1469	-	-	-	-	-
DCB 307s	7/8	8	023Z1468	-	-	-	-	-

Figure 14: Solder (pure copper)




Table 12: DMB solder (copper connectors)

Туре	Conn.	n. Multipack		Industrial pack		Conn.	Multipack	
	in.	qty.	Code no.	qty.	Code no.	mm	qty.	Code no.
DMB054s	1/2	24	023Z2088	-	-	-	-	-
DMB055s	5/8	24	023Z2098	-	-	-	-	-
DMB 082s	1/4	24	023Z1093	-	-	-	-	-
DMB 083s	3/8	24	023Z1091	16	023Z2085	-	-	-
DMB 084s	1/2	24	023Z1090	-	-	-	-	-
DMB 163s	3/8	12	023Z1098	12	023Z2087	10	24	023Z1091
DMB 164s	1/2	12	023Z1096	-	-	12	-	
DMB 165s	5/8	12	023Z1094	12	023Z2086	16	12	023Z1094
DMB 304s	1/2	8	023Z1449	-	-	12	-	-
DMB 305s	5/8	8	023Z1448	-	-	16	8	023Z1448
DMB 307s	7/8	8	023Z1447	-	-	22	8	023Z1447

Table 13: DCB solder (copper connectors)

Туре	Conn.	Multipack		Industrial pack		Conn.	Multipack	
	in.	qty.	Code no.	qty.	Code no.	mm	qty.	Code no.
DCB 083s	3/8	24	023Z1086	-	-	-	-	-
DCB 163s	3/8	12	023Z2097	-	-	-	-	-
DCB 164s	1/2	12	023Z1089	-	-	-	-	-
DCB 165s	5/8	12	023Z1088	-	-	16	12	023Z1088
DCB 304s	1/2	8	023Z1440	-	-	-	-	-
DCB 305s	5/8	8	023Z1439	-	-	16	8	023Z1439
DCB 307s	7/8	8	023Z1438	-	-	22	8	023Z1438



Certificates, declarations, and approvals

The list contains all certificates, declarations, and approvals for this product type. Individual code number may have some or all of these approvals, and certain local approvals may not appear on the list.

Some approvals may change over time. You can check the most current status at danfoss.com or contact your local Danfoss representative if you have any questions.

Table 14: Certificates, declarations, and approvals

Document name	Document type	Document topic	Approval authority
SA 6398	UL Certificate	Mechanical Safety Certificate	UL
023Z9601.AF	Manufacturer's Declaration	ATEX/PED/RoHS	Danfoss
023Z9610.AA	Manufacturer's Declaration	China RoHS	Danfoss
RU Д-DK.AИ08.B.00828_19	EAC Declaration	Machinery & Equipment	EAC



Online support

Danfoss offers a wide range of support along with our products, including digital product information, software, mobile apps, and expert guidance. See the possibilities below.

The Danfoss Product Store



The Danfoss Product Store is your one-stop shop for everything product related—no matter where you are in the world or what area of the cooling industry you work in. Get quick access to essential information like product specs, code numbers, technical documentation, certifications, accessories,

Start browsing at store.danfoss.com.

Find technical documentation



Find the technical documentation you need to get your project up and running. Get direct access to our official collection of data sheets, certificates and declarations, manuals and guides, 3D models and drawings, case stories, brochures, and much more.

Start searching now at www.danfoss.com/en/service-and-support/documentation.

Danfoss Learning



Danfoss Learning is a free online learning platform. It features courses and materials specifically designed to help engineers, installers, service technicians, and wholesalers better understand the products, applications, industry topics, and trends that will help you do your job better.

Create your Danfoss Learning account for free at www.danfoss.com/en/service-and-support/learning.

Get local information and support



Local Danfoss websites are the main sources for help and information about our company and products. Find product availability, get the latest regional news, or connect with a nearby expert—all in your own language.

Find your local Danfoss website here: www.danfoss.com/en/choose-region.

Coolselector®2 - find the best components for you HVAC/R system



Coolselector®2 makes it easy for engineers, consultants, and designers to find and order the best components for refrigeration and air conditioning systems. Run calculations based on your operating conditions and then choose the best setup for your system design.

Download Coolselector®2 for free at coolselector.danfoss.com.

Danfoss A/S

Climate Solutions • danfoss.com • +45 7488 2222

Any information, including, but not limited to information on selection of product, its application or use, product design, weight, dimensions, capacity or any other technical data in product manuals, catalogues descriptions, advertisements, etc. and whether made available in writing, orally, electronically, online or via download, shall be considered informative, and is only binding if and to the extent, explicit reference is made in a quotation or order confirmation. Danfoss cannot accept any responsibility for possible errors in catalogues, brochures, videos and other material. Danfoss reserves the right to alter its products without notice. This also applies to products ordered but not delivered provided that such alterations can be made without changes to form, fit or further that the sending Danfoss reserves the right to after its produce miniocities and the product.

All trademarks in this material are property of Danfoss A/S or Danfoss group companies. Danfoss and the Danfoss logo are trademarks of Danfoss A/S. All rights reserved.