



Demand Signal Generator Module for DIN Rail Mounting

EHD-DSG-201-A-10



Front Panel



General Description

This unit is one of a range of "snap-on" control modules designed for cabinet mounting on rails to DIN EN 50022 or DIN EN 50035. The range is ideally suited for use in control systems using Vickers by Danfoss "KA" or "KB" series proportional valves with integral amplifiers or Vickers by Danfoss "UNIPLUG" series, where external signal, deadband compensation and ramp generation may be required.

The Demand Signal Generator module has a built-in microprocessor which controls all of the facilities offered by the unit. Setting up the various control parameters is done via four input keys

mounted on the front panel. All settings are stored in an on-board EEPROM and once entered are retained, until reset, even when the power is switched off. Visual indication of all settings is provided by four 7-segment LED displays mounted on the front panel.

Up to 16 separate setpoints can be externally selected using four input connections in binary code. Setpoints 1 and 2 are scalable using 0-10 volt analog inputs. Unit operating status is indicated by seven separate LEDs. The unit also accepts a ± 10 volt feedback signal which is compared internally to the command signal and an "in range" signal is generated when they coincide.

Features and Benefits

- Snap-on mounting to DIN rails
- 24V DC power supply with wide tolerance
- Standard ± 10 V DC output signal
- Screw terminals simplify installation
- 16 selectable output levels
- Keypad on front panel
- 4 x 7-segment LED display
- 4-quadrant ramps
- Ramp times up to 99.99 seconds
- Can replace previous design




This product has been designed and tested to meet specific standards outlined in the European Electromagnetic Compatibility Directive (EMC) 89/336/EEC, amended by 91/263/EEC, 92/31/EEC and 93/68/EEC, article 5. For instructions on installation requirements to achieve effective protection levels, see this leaflet and the Installation Wiring Practices for Vickers by Danfoss Electronic Products leaflet 2468. Wiring practices relevant to this Directive are indicated by  Electromagnetic Compatibility (EMC).

Operating Data

Power supply:		
Power supply (input)	[2]	24V DC nominal x 6W
Range		18-36V DC (including $\pm 10\%$ pk-to-pk ripple)
Power ground	[1]	
Control supply (output)	[18]	+10V DC x 10 mA Temperature drift < 1 mV/°C thru 0-50°C (< 0.5 mV/°F thru 32-122°F)
Switched input signals (monitored by green LEDs):		
Enable module	[3]	} 16 possible setpoints in binary mode (4 in DSG mode) Range of outputs -99.99 to +99.99%
Setpoint enable	[4]	
Setpoint 1/Bit 0	[5]	
Setpoint 2/Bit 1	[6]	
Setpoint 3/Bit 2	[7]	
Setpoint 4/Bit 3	[8]	
Enable voltage		17 to 40V
Disable voltage		0 to 3.5V
Input impedance		2.7 k Ω
Analog input signals:		
Control voltage for setpoint 1	[19]	0 to +10V
Ground	[20]	
Control voltage for setpoint 2	[21]	0 to +10V
Ground	[22]	
Feedback voltage from valve	[16]	$\pm 10V$
Input impedance		1 M Ω
Switched output:		
Valve OK signal	[10]	Valve is following input signal correctly (Valve output polarity = command polarity or Valve within set deadband = command at null) V supply -2V < 3V
Valve has reached setpoint		
Valve has not reached setpoint		
Ground	[11]	
Not used	[12]	
Ground	[13]	
Maximum load current (short circuit protected)		< 100 mA
Analog output:		
Drive voltage to valve	[14]	$\pm 10V$ x 5 mA
Ground	[15]	Temperature drift < 1 mV/°C thru 0-50°C (< 0.5 mV/°F thru 32-122°F)
Set-up adjustments (using four keys and 7-segment display on front panel):		
Setpoints		-99.9 to +99.9 % (represents -10V to +10V output voltage)
4-quadrant ramps		10 ms to 99.99s
2 deadbands		0 to 100%
Operating modes:		
16 binary inputs for normal operation		BIN
4 inputs simulating previous design		DSG
Setpoint 1 scalable		ON/OFF
Setpoint 2 scalable		ON/OFF
Ramp enable		ON/OFF
Module enable		ON/OFF
Feedback		ON/OFF


Displayed parameters:		
Power supply voltage	[2]	V
Output voltage	[14]	V
Control voltage for setpoint 1	[19]	%
Control voltage for setpoint 2	[21]	%
Number of active setpoint		1-16
Setpoint value		%
Feedback voltage	[16]	%
Positive deadband		%
Negative deadband		%
Ramp times (4)		Seconds
Connections		Screw clamping terminals
Wiring recommendations, all connections		0.5 to 2.5 mm ² (22 to 12 AWG)
Protection class		IEC 529 IP 20
Vibration:		
Vickers by Danfoss environmental specification (Class 1 level 2)		IEC 68-2-6
Electromagnetic compatibility(EMC):		
Emission		EN-50081-2
Immunity		EN-50082-2
Ambient temperature ranges:		
Operating		0°C to 50°C (32°F to 122°F)
Storage		-25°C to 85°C (-13°F to 180°F)
Mounting		Rails to DIN EN 50022 or DIN EN 50035
Housing material		Polyamid 6.6
Mass		0.3 kg (0.45 lb)

Electrical Block Diagram



Typical Connection Arrangement

Customer-generated logic signals select demand levels for valve with integral amplifier



⏏ Customer's protective ground connection.





Warning: Electromagnetic Compatibility(EMC)

It is necessary to ensure that the unit is wired up in accordance with the Typical Connection Arrangement shown in this leaflet. For effective protection, the user's electrical cabinet, the valve subplate or manifold and the cable screens should be connected to efficient ground points. The metal 7-pin connector partno. 934939 should be used for the integral amplifier.

In all cases, both valve and cable should be kept as far away as possible from any source of electromagnetic radiationsuch as cables carrying heavy current, relays and certain kinds of portable radio transmitters, etc. Difficult environments could mean that extra screening may be necessary to avoid the interference.

Installation Dimensions in mm (inches)



Type	TS1	TS3	TS4/5
A	64.5 (2.6)	60.0 (2.4)	67.5 (2.7)

Products we offer:

- Cartridge valves
- DCV directional control valves
- Electric converters
- Electric machines
- Electric motors
- Gear motors
- Gear pumps
- Hydraulic integrated circuits (HICs)
- Hydrostatic motors
- Hydrostatic pumps
- Orbital motors
- PLUS+1® controllers
- PLUS+1® displays
- PLUS+1® joysticks and pedals
- PLUS+1® operator interfaces
- PLUS+1® sensors
- PLUS+1® software
- PLUS+1® software services, support and training
- Position controls and sensors
- PVG proportional valves
- Steering components and systems
- Telematics

Danfoss Power Solutions is a global manufacturer and supplier of high-quality hydraulic and electric components. We specialize in providing state-of-the-art technology and solutions that excel in the harsh operating conditions of the mobile off-highway market as well as the marine sector. Building on our extensive applications expertise, we work closely with you to ensure exceptional performance for a broad range of applications. We help you and other customers around the world speed up system development, reduce costs and bring vehicles and vessels to market faster.

Danfoss Power Solutions – your strongest partner in mobile hydraulics and mobile electrification.

Go to www.danfoss.com for further product information.

We offer you expert worldwide support for ensuring the best possible solutions for outstanding performance. And with an extensive network of Global Service Partners, we also provide you with comprehensive global service for all of our components.

Local address:

Hydro-Gear

www.hydro-gear.com

Daikin-Sauer-Danfoss

www.daikin-sauer-danfoss.com

**Danfoss
Power Solutions (US) Company**
2800 East 13th Street
Ames, IA 50010, USA
Phone: +1 515 239 6000

**Danfoss
Power Solutions GmbH & Co. OHG**
Krokamp 35
D-24539 Neumünster, Germany
Phone: +49 4321 871 0

**Danfoss
Power Solutions ApS**
Nordborgvej 81
DK-6430 Nordborg, Denmark
Phone: +45 7488 2222

**Danfoss
Power Solutions Trading
(Shanghai) Co., Ltd.**
Building #22, No. 1000 Jin Hai Rd
Jin Qiao, Pudong New District
Shanghai, China 201206
Phone: +86 21 2080 6201