



**Case story** 

# VLT<sup>®</sup> control of **Rolex Paper Mills**

Because of previous experience with Danfoss VLT<sup>®</sup> frequency converters, Rolex Paper Mills based in Palakollu, Andhra Pradesh, India, did not consider any other company than Danfoss for the line automation when the company planed an expansion of the capacity from 300 tons per day to 700 tons per day by adding another newsprint paper manufacturing line.

Newsprint paper manufacturing requires very precise synchronisation of sectional drives as the paper is made from recycled paper and is very thin (45-50 g per square meter) and runs at very high speed.

Since Rolex assembles the unit with partly recycled machinery, synchronisation became rather challenging.

# A complete solution

Since the drives in the project need close synchronisation, a PLC based solution was chosen. Danfoss and Danfoss partner ESPL chose VIPA, a PLC manufacturer, to provide the complete solution.

Danfoss VLT<sup>®</sup> AutomationDrives along with dynamic braking and DC bus sharing were chosen because of the accurate control solution and the ability to run in constant torque mode. Encoder feedback and Profibus options were also considered to make the paper machine run precisely with set speeds.

The rating of drives range from 11 kW to 75 kW and their application details are as follows:

Application	kW rating	Qty
Couch	75	1
Press	37	2
Dryer	22	4
Calendar	22	1
Pope Reel	15	1



ENGINEERING TOMORROW

Danfoss

The VIPA Speed7 range of PLC, model 315-2AJ10, was selected for smooth operator interface and for its quick response in controlling the speed and torque. This has Profibus DP interface, the required number of I/O's and two touch panels.

# **VIPA Speed7**

The CPUs are programmable with Step7 from Siemens and the scanning cycle of the selected CPU is 15 ns for bit operation and 90 ns for floating point operation.

VIPA CPUs also have flexible memory options and a built-in Ethernet interface that makes them ideal for remote trouble shooting if required. Having the Ethernet port available on the PLC also helped to trouble-shoot when one of the bits latched in the PLC program. The programming engineer could reset the bit online.

## System control philosophy

The operator starts the machine in crawl mode to confirm the machine reliability and operation. At this stage the machine runs at low, fixed speed.

Later, the operator will switch the system to synchronization/run mode. Initially it will run at low speeds and all the draw sets for all the sections are adjusted to make sure the paper is drawn smoothly from Couch to Calendar from the machine.

This stage having been achieved, the operator will run the machine at higher speeds. Because the Pope reel



The VIPA Speed7 range of PLC model 315-2AJ10 was selected for its smooth operator interface and for quick response controlling the speed and torque. This has Profibus DP interface, the required number of I/O's and two touch panels.

requires variable torque, the operator switches the calendar and Pope reel from VVC+ mode to torque mode. The torque limits are set based on the VVC mode torque and adjusted further based on the required tightness of the paper roll.

After initial hiccups, the plant has been running smoothly for more than a year and in terms of output production and fewer breakages, is reputed to be the best of the plants in the local area. More than 12 paper mills in the area are controlled by competitor's automation systems.

Contact:

## Oza Paresh

Head of Product Management & Application Danfoss Industries Pvt. Ltd 296 Old Mahabalipuram Road Sholinganallur 600119 Chennai paresh\_oza@danfoss.com

Danfoss can accept no responsibility for possible errors in catalogues, brochures and other printed material. Danfoss reserves the right to alter its products without notice. This also applies to products already on order provided that such alterations can be made without subsequential changes being necessary in specifications already agreed. All trademarks in this material are property of the respective companies. Danfoss and the Danfoss logotype are trademarks of Danfoss A/S. All rights reserved.