

ENGINEERING
TOMORROW

Danfoss

Factory Service Program

Keep it **running**

Proportional Valve Service and Repair Program North America

VICKERS
by Danfoss

Danfoss Factory: **Searcy, AR**

Quick Turnaround

Standard: Five-day service

Valves ship five days from receipt of valve at the Searcy Plant.

Express: Next-day service

Valves ship next business day after receipt in the Searcy Plant.

- Expedited Freight (FedEx, UPS, etc.) available
- 50% premium applies



For assistance

Reach out to your local distributor or Danfoss customer service representative today to request an RMA and return the product for evaluation and service.

Three Service Levels

Your Choice

Select service levels from simple evaluation and testing to a complete rebuild with original Danfoss parts, and now a Danfoss Factory Warranty.



Service Level 1

- Inspect and test
- Flush
- Calibrate
- Test stand report



Service Level 2

Rebuild to "Factory New" New Warranty

- Disassemble
- Inspect and test
- Clean
- New seals
- Flush
- Calibrate
- Test stand report



Service Level 3


















Rebuild to "Factory New" New Danfoss parts New Warranty

- Disassemble
- Inspect and test
- Clean
- New seals
- New parts (as needed)
- Flush
- Calibrate
- Test stand report













Note: Repairs exceeding 60% of new unit price are considered uneconomical and the Searcy team will recommend a new replacement valve. The service inspection fee will be waived in cases where a new replacement valve is ordered, otherwise Level 1 price will be charged for units scrapped or returned "un-repaired."

Restore Performance of these **Vickers®** by Danfoss Proportional Valves

Proportional Directional Valve with On-board Electronics (OBE)







	Single Stage DO3/NG6	DO5/NG10	Two Stage DO5/NG10	DO7/NG16	DO8/NG25	D10/NG32
Servo Performance Valve with Dual Spool Feedback	KBSDG4V-3 		KBHDG5V-5 	KBHDG5V-7 	KBHDG5V-8 	KBHDG5V-10 
High Performance Valve with Single Spool Feedback	KBFDG4V-3 	KBFDG4V-5 	KBFDG5V-5 	KBFDG5V-7 	KBFDG5V-8 	KBFDG5V-10 
Standard Performance Valve without Spool Feedback	KBDG4V-3 	KBDG4V-5 	KBDG5V-5 	KBDG5V-7 	KBDG5V-8 	KBDG5V-10 

Proportional Directional Valve without On-board Electronics (Non-OBE)





	Single Stage DO3/NG6	DO5/NG10	Two Stage DO5/NG10	DO7/NG16	DO8/NG25	D10/NG32
Servo Performance Valve with Dual Spool Feedback	KSDG4V-3 		KHDG5V-5 	KHDG5V-7 	KHDG5V-8 	KHDG5V-10 
High Performance Valve with Single Spool Feedback	KFDG4V-3 					
Standard Performance Valve without Spool Feedback	KDG4V-3 	KDG4V-5 	KDG5V-5 	KDG5V-7 	KDG5V-8 	KDG5V-10 

* Substitute with KHDG5V-10 in place of KFDG5V-10

Proportional Pressure Relief Valve Family

	Single Stage	Two Stage	
OBE	KBCG-3 	KBCG-6 	KBCG-8 
Non-OBE	KCG-3 	KCG-6 	KCG-8 

Proportional Pressure Reducing Valve Family

	Two Stage	
OBE	KBX(C)G-6 	KBX(C)G-8 
Non-OBE	KX(C)G-6 	KX(C)G-8 

Why **Danfoss Factory Service?**

Keep your plant running with Danfoss Factory Service. Experienced factory technicians inspect and test your valve and repair as needed ... and give you a factory test stand report. Original Danfoss parts will give serviced valves “like new” performance **and renewed warranty coverage.**

Do not settle for less. Contact your Danfoss distributor for quick factory service of your Vickers® by Danfoss EH valves.

- **Renewed warranty coverage**
- **Quick turnaround**
- **Three service levels**
- **Local contacts**
- **Factory tested**
- **Genuine Danfoss parts**

Global **Factory Service**

With a strong commitment to serving our customers, we continue investing in equipment and processes that will allow us to improve service levels and meet the demand associated with securing new business and future market growth.

North America

Searcy, AR Plant
United States

Prop Valve Service
Danfoss
400 E. Lincoln Avenue
Searcy, AR 72143

Europe

Havant Plant
United Kingdom

Service Centre of Excellence
Danfoss
46 New Lane
Havant, Hampshire
PO9 2NB
England

Asia

Shanghai Plant
China

Danfoss Power Solutions
(Shanghai) Co., Ltd.
No. 388 Aidu Road
WaiGaoQiao, F.T.Z.
200131, China




Danfoss Power Solutions, Nordborgvej 81, 6430 Nordborg, Denmark, Tel. +45 74 88 22 22, Fax +45 74 65 25 80
www.danfoss.com, E-mail: info@danfoss.com

Any information, including, but not limited to information on selection of product, its application or use, product design, weight, dimensions, capacity or any other technical data in product manuals, catalogues descriptions, advertisements, etc. and whether made available in writing, orally, electronically, online or via download, shall be considered informative, and is only binding if and to the extent, explicit reference is made in a quotation or order confirmation. Danfoss cannot accept any responsibility for possible errors in catalogues, brochures, videos and other material. Danfoss reserves the right to alter its products without notice. This also applies to products ordered but not delivered provided that such alterations can be made without changes to form, fit or function of the product. All trademarks in this material are property of Danfoss A/S or Danfoss group companies. Danfoss and the Danfoss logo are trademarks of Danfoss A/S. All rights reserved.


Typical Proportional Valve Applications



Wind Energy



Injection Molding



Metal Forming



Primary Metals