

Data Sheet

Pressure transmitter CANopen

DST P10B

The DST 10B OEM pressure transmitter is designed for use in industrial applications like Booster Pumps and Air Compressors.

Danfoss DST P10B is developed to comply with CANopen.

It is a cost effective way to control complex machines and make also replacements cost-efficient while offering additional benefits such as diagnostic and communication.

The DST P10B is available in the pressure range 4 to 40 bar. The measuring element is made of stainless steel and covers a media temperature range of -40 to 100 °C.

Features:

- Designed for use in Booster Pumps and Air Compressors
- For ambient temperature up to 100 °C
- Pressure range 0-4 bar to 0 - 40 bar
- Integrated CANopen interface per DS-301
 - Device profile DS-404
- Wetted parts made of stainless steel
- Fully welded design and, therefore, no use of gasket in combination with wetted parts

Product specification

Technical data

Table 1: Performance

Accuracy @ 20 °C	≤ ±0.5% FS
Total error band	0 - 100 °C: 2% -40 - 0 °C: 3%
Response time	< 2.5 ms
Overload pressure	4 × FS
Burst pressure	5 × FS
Durability, P: 10-90% FS	>10 mil. cycles

Table 2: Electrical specifications

Nom. output signal (short-circuit protected)	CANopen
Supply voltage [UB], polarity protected	8 - 32 Vdc
Termination resistor between CAN_H and CAN_L	120 Ohm (recommended)

Table 3: Environmental conditions

Media temperature range			-40 - 100 °C
Ambient temperature range			-40 - 100 °C
Storage temperature range			-40 -150 °C
EMC - Emission			EN 61000-6-3
EMC Immunity up to 6 GHz			EN 61000-6-2
Insulation resistance			> 100 MΩ at 500 V
Vibration resistance	Random	10 grms, 5 Hz - 2 kHz	IEC 60068-2-64
Shock resistance	Shock	500 g / 1 ms	IEC 60068 - 2 - 27
Enclosure with mating connector			IP67

Table 4: Mechanical characteristics


Wetted parts	AISI 304L
	AISI 316L (diaphragm)
Housing	AISI 304L
Electrical connections	Color: Black, Material: PBT-GF30%
Weight (depending on pressure connection)	< 100 g

Table 5: CANopen

CANopen	Sample rate	1953 samples/s (max.)
	Digital filter	configurable moving average filter
	Output protocol	CANopen DS301/DS404 (according to CiA)
	Electrical connection	M12x1,0 according to EN60947-5-2 (2008), 5 pins

Electrical connections

Table 6: Electrical connections

	
Pin-plating	Au plated pins
Pin configuration	Pin 1: PE, Housing Pin 2: VCC Pin 3: GND Pin 4: CAN_H Pin 5: CAN_L

Dimensions / combinations

Figure 1: M12 and G1/4A - ISO 1179-2





Figure 2: M12 and 1/4-18NPT (8mm ø)



Ordering

Table 7: DST P10B - Standard code numbers

Type	Pressure range	Pressure reference	Electrical connector	Elec. connector standard	Pressure connection	Pres. connection standard	Output signal	Code no. (Industry Pack)	Code no. (Multi Pack)
DST P10B	0 - 4 bar	Gauge	M12 x 1.0 (5 pins, Au plated)	EN60947-5-2 (2008)	G1/4-A	DIN EN ISO1179-2 (formerly: DIN 3852 E), incl. O-ring , DIN 3869	CANopen, DS301/DS404 (according to CiA)	075G4149	075G1190
	0 - 6 bar							075G4150	075G1191
	0 - 10 bar							075G4151	075G1192
	0 - 16 bar							075G4152	075G1193
	0 - 25 bar	Sealed Gauge			1/4-18 NPT (8mm Ø)	ANSI/ASME B1.20.1		075G4153	075G1194
	0 - 40 bar							075G4154	075G1195
	0 - 100 psi	Gauge						075G4157	075G1198
	0 - 150 psi							075G4158	075G1199
	0 - 200 psi							075G4159	075G1200
	0 - 300 psi							075G4160	075G1201

Certificates, declarations and approvals

The list contains all certificates, declarations, and approvals for this product type. Individual code number may have some or all of these approvals, and certain local approvals may not appear on the list.

Some approvals may change over time. You can check the most current status at danfoss.com or contact your local Danfoss representative if you have any questions.

Conformity

- CE
- CiA certified (in progress)
-  (in progress)
- UKCA

NOTE:

In respect to Customer Change Notification, only changes in relation to Form Fit and Function can be informed upon!

Online support

Danfoss offers a wide range of support along with our products, including digital product information, software, mobile apps, and expert guidance. See the possibilities below.

The Danfoss Product Store



The Danfoss Product Store is your one-stop shop for everything product related—no matter where you are in the world or what area of the cooling industry you work in. Get quick access to essential information like product specs, code numbers, technical documentation, certifications, accessories, and more.

Start browsing at store.danfoss.com.

Find technical documentation



Find the technical documentation you need to get your project up and running. Get direct access to our official collection of data sheets, certificates and declarations, manuals and guides, 3D models and drawings, case stories, brochures, and much more.

Start searching now at www.danfoss.com/en/service-and-support/documentation.

Danfoss Learning



Danfoss Learning is a free online learning platform. It features courses and materials specifically designed to help engineers, installers, service technicians, and wholesalers better understand the products, applications, industry topics, and trends that will help you do your job better.

Create your Danfoss Learning account for free at www.danfoss.com/en/service-and-support/learning.

Get local information and support



Local Danfoss websites are the main sources for help and information about our company and products. Find product availability, get the latest regional news, or connect with a nearby expert—all in your own language.

Find your local Danfoss website here: www.danfoss.com/en/choose-region.

Danfoss A/S

Climate Solutions • danfoss.com • +45 7488 2222

Any information, including, but not limited to information on selection of product, its application or use, product design, weight, dimensions, capacity or any other technical data in product manuals, catalogues descriptions, advertisements, etc. and whether made available in writing, orally, electronically, online or via download, shall be considered informative, and is only binding if and to the extent, explicit reference is made in a quotation or order confirmation. Danfoss cannot accept any responsibility for possible errors in catalogues, brochures, videos and other material. Danfoss reserves the right to alter its products without notice. This also applies to products ordered but not delivered provided that such alterations can be made without changes to form, fit or function of the product.

All trademarks in this material are property of Danfoss A/S or Danfoss group companies. Danfoss and the Danfoss logo are trademarks of Danfoss A/S. All rights reserved.