

ENGINEERING  
TOMORROW

*Danfoss*

Product Brochure

# Vickers® by Danfoss PVM series open-circuit piston pump

**More guts. More glory.** (Less noise.)

**VICKERS**  
by Danfoss



## Downsize your pumps. Upsize your expectations.

**Requirements are changing in industries everywhere. Government regulators are mandating quieter, more energy-efficient machinery. And design engineers are looking for equipment and components that can generate more power from smaller footprints.**

**These increased expectations require a new generation of hydraulic pumps that are compact, quiet and energy efficient, yet can handle some of your most demanding applications.**

**With their variable-speed-ready range, enhanced 315-bar nominal pressure ratings, quiet operation and “Power Control” option, Vickers by Danfoss PVM Series open circuit piston pumps can help you design machinery that conforms to a new era of performance demands.**



### **The quiet pumps that are making a big noise**

The noisy workplace environments of the past are rapidly going out of fashion. Government regulators and workers alike are demanding job conditions that are quieter and safer. Danfoss PVM Series open circuit piston pumps can help you address these concerns. With the lowest operating noise of any pumps in their class—a full **50 percent quieter** than our previous generation of pumps—Vickers by Danfoss PVM Series pumps can help you build quieter functioning machinery.

### **Power control: flexibility at your fingertips**

Flexibility is the name of the game with Vickers by Danfoss’ optional Power Control for PVM Series pumps. By reducing the displacement as pressure increases, Power Control allows you to limit the power rating at a given speed so the set power is not exceeded. The result? Now you can cut your costs by operating larger pumps with the same size motors. In addition, you can adjust the power setting in the field without changing components or springs, allowing you to quickly and easily fine tune machine performance.



## Save energy, reduce noise and cut costs with variable speed drive technology



- Proven rotating group can produce up to 315 bar of continuous pressure
- Displacement range from 18ccm up to 141ccm
- High load bearings are rated at 14,000 hours at corner horsepower
- Saddle-type swash plate features a steel-backed polymer bearing to extend life
- Unique, tapered design reduces vibration
- Robust shaft and bearings help maximize reliability

Variable speed drive pump solution generates power far more efficiently than conventional, fixed-speed pump systems. They also allow quieter operation, require less cooling and help extend the life of seals and hydraulic oil. Danfoss PVM Series pumps are ready to work with variable speed drive technology across the full speed spectrum.\* Now you can immediately begin transforming your machinery to next-generation standards of energy efficiency and noise.

\*Full speed operation performance data, across full speed range, is available for variable speed applications.

**Reliable and durable: what you expect from Vickers by Danfoss technology**

Reliability and long life are simply expected in your pump requirements. Featuring a robust, noise cancelling three-piece design, high load bearings and other high-quality design considerations, Vickers by Danfoss PVM Series pumps are built to function dependably for years.

**Engineered for a world of demanding applications**

Tap the quiet, compact power of Vickers by Danfoss PVM Series open circuit piston pumps anywhere you need greater hydraulic power and energy efficiency from a smaller displacement pump.

- Discrete manufacturing, including press, machine tools, test and simulation machinery
- Primary metal, food and wood processing applications
- Energy generation, such as wind, steam and hydroelectric turbines
- Oil and gas and marine applications
- General industrial applications of all kinds



Experience the quiet, compact power of Vickers by Danfoss PVM Series open circuit piston pumps.


**Danfoss | PVM**



# Vickers by Danfoss PVM Series

## Open circuit piston pumps


**PVM System Pressure vs. Shaft Speed**



Test condition: Mineral oil SAE 10W, oil temperature 49° C (120° F), 1 bar absolute inlet pressure.

Vickers by Danfoss PVM Series open circuit piston pumps have been tested and qualified for improved pressure ratings as shown in the chart above.

**Flow vs Pressure - 74cc**



The Power Control option for Vickers by Danfoss PVM Series open circuit piston pumps provides precise control characteristics for optimal power utilization.



Danfoss Power Solutions, Nordborgvej 81, 6430 Nordborg, Denmark, Tel. +45 74 88 22 22, Fax +45 74 65 25 80  
www.danfoss.com, E-mail: info@danfoss.com

Any information, including, but not limited to information on selection of product, its application or use, product design, weight, dimensions, capacity or any other technical data in product manuals, catalogues descriptions, advertisements, etc. and whether made available in writing, orally, electronically, online or via download, shall be considered informative, and is only binding if and to the extent, explicit reference is made in a quotation or order confirmation. Danfoss cannot accept any responsibility for possible errors in catalogues, brochures, videos and other material. Danfoss reserves the right to alter its products without notice. This also applies to products ordered but not delivered provided that such alterations can be made without changes to form, fit or function of the product. All trademarks in this material are property of Danfoss A/S or Danfoss group companies. Danfoss and the Danfoss logo are trademarks of Danfoss A/S. All rights reserved.