


Data sheet

Slimline nozzles

General data sheet

For specific information on this product, please contact Danfoss A/S.

Identification



As an example nozzles housing engraved with the following:

- 1 Danfoss
- 2 Finished Product Code (030L6618)
- 3 Batch Code (MR4)

Application

This type of nozzle has been widely used within the humidification industry for years. It is tailored for fine water atomization in applications like comfort humidity control, open space humidification, adiabatic cooling etc. The nozzle generates billions of very small droplets, depending on pressure and water quality. The finer and more uniform the water mist, the greater the potential for adhesion between water and the surrounding particles.

With our technology we can achieve humidification and cooling without wetting. The nozzle has a long-life expectancy due to the Tin/Nickel (SnNi) coated design. The droplet size and spraying pattern will not rapidly deteriorate. Lifetime of the nozzles are depending on the application, environment, pressure, temperature, and filtration (contamination) of the fluid.

Application and features


- Adiabatic cooling
- Humidification
- Disinfection
- Dust control
- Cleaning
- Green houses
- Field proven performance for over 75 years
- Accurate, flow rate and spray angle
- Produces a finely atomized mist

Availability

- Standard flow rate: 1,3 – 17,2 L/h
- Spray angle: 60° & 80°
- Spray pattern: Hollow
- Connection thread 10/24 & 12/24

Further specifications on request

Design



All nozzles come with a built-in valve as standard. With the slimline anti-drip nozzles, operators can achieve fluid cut-off near the orifice while maintaining pressure within the nozzle supply system.


Components:

- 1. Housing
- 2. Orifice disc
- 3. Cone
- 4. Spring
- 5. Guide
- 6. O-ring Ø6,0
- 7. Rubber ball
- 8. Screw
- 9. O-ring Ø4,0


Data sheet

Slimline nozzles

Spray angle and spray pattern



60° & 80° spray angle



Hollow spray

Technical data

Material and construction

The nozzle housing, guide and screw are Tin/ Nickel (SnNi) plated brass. This coating is tight and extremely hard which gives a valuable corrosion resistance.

Disc and cone are available in:

- AISI 303 (Stainless Steel)
- Nickel Silver (copper nickel alloy)


Spring is made of Stainless Steel AISI 303. Material for ball & O-ring's is FPM.

Tightening torque

Recommended tightening torque	Tighten by hand
Maximum tightening torque	3 Nm

Flow rates

Standard flow rates are available in the region between the curves.



Performance

Minimum recommended operation pressure is 14 bar.

Maximum recommended operation pressure is 80 bar.

Cut off valve


The cut off valve has a closing pressure between 4,5 to 6 bar.

Further specifications on request

Nozzle types

Nozzles are available with 2 different spray angles 60° & 80° with hollow spray pattern.

Dimensions



Danfoss A/S

Climate Solutions • danfoss.com • +45 7488 2222

Any information, including, but not limited to information on selection of product, its application or use, product design, weight, dimensions, capacity or any other technical data in product manuals, catalogues descriptions, advertisements, etc. and whether made available in writing, orally, electronically, online or via download, shall be considered informative, and is only binding if and to the extent, explicit reference is made in a quotation or order confirmation. Danfoss cannot accept any responsibility for possible errors in catalogues, brochures, videos and other material. Danfoss reserves the right to alter its products without notice. This also applies to products ordered but not delivered provided that such alterations can be made without changes to form, fit or function of the product.

All trademarks in this material are property of Danfoss A/S or Danfoss group companies. Danfoss and the Danfoss logo are trademarks of Danfoss A/S. All rights reserved.