


Installation Guide


Service kits – Catalogue



A	PN	DN	Δp (bar)							Code No.
			$0.05 \div 0.5$ $0.1 \div 0.5$	$0.2 \div 1.0$	$0.3 \div 2.0$	$0.8 \div 1.6$	0.2	0.3	0.5	
	16	15 ÷ 32	-	×		-	×	-	-	003H1330
			-	-		-	-	×	-	003H1326
			-	-		-	-	-	×	003H1331
			-	-		×	-	-	-	003H1332
	25	15 ÷ 50		-	-		×		-	88835920
		15 ÷ 25		-	-		-		×	88835930
		32 ÷ 50		-	-		-		×	88835940













B	PN	DN	Δp_b (bar)							Code No.
			$0.1 \div 0.5$	$0.2 \div 1.0$	$0.3 \div 2.0$	$0.8 \div 1.6$	0.2	0.3	0.5	
	16	15 ÷ 32					×			003H1330
	25	15 ÷ 25					×			88835920
		32 ÷ 50					-			-

M1	CuSn5ZnPb (Rg5)
M2	EN-GJS-400-18-LT (GGG 40.3)













Page	PN		
2	16	AVP, AVP-F, AVPB, AVPB-F, AVD, AVQ, AVQM	M1
2	16	AVPQ, AVPQ-F	M1
3	16	AVPQ 4, AVPQ 4-F	M1
3	16	AVPA	M1
4	25	AVP, AVP-F, AVPB, AVPB-F, AVPBT-F, AVD, AVQ, AVQT, AVQM, AVQMT	M1
			M2
5	25	AVPQ, AVPQ-F	M1
			M2
6	25	AVPQ 4, AVPQ 4-F	M1
			M2
7	25	AVPA	M1
			M2
8	25	AVA	M1
			M2
9	25	AVDS	M1











Page	PN		
10	25	SAVA	M1
			M2
11	25	SAVD	M1
			M2
12	25	AVPBT	M1
13	25	AVPBT	M2
15	25	AVPQT	M1
16	25	AVPQT	M2
18	25	VG	M1
18	25	VG, VGF	M2
18	25	VGS	M1
19	16	Control valve insert	M1
20	25	Control valve insert	M1
21			M2
22	25	STL	M1, M2















PN 16 AVP, AVP-F, AVPB, AVPB-F, AVD AVQ, AVQM	A B M1	PN 16 AVPQ, AVPQ-F	A, B M1
1 	2 	1 	2 
3 	3 	3 	3 
5 	4 	5 	4 













Service kits – Catalogue

PN 16		AVPQ 4, AVPQ 4-F		A	B	M1	PN 16		AVPA		A	M1	
1		2						1		2			
													
3								3					
													
5		4						5		4			
													











Service kits – Catalogue











PN 25	AVP, AVP-F, AVPB, AVPB-F, AVPBT-F, AVD AVQ, AVQT, AVQM, AVQMT	A B	M1	PN 25	AVP, AVP-F, AVPB, AVPB-F, AVPBT-F, AVD AVQ, AVQT, AVQM, AVQMT	M2			
1 	2 	3  AVD →	4  88835920 003H6758 AVQM DN 50 - flange 003H6782 AVQMT DN 50 - flange	1 	2 	5 	4 	7 	5 

PN 25		AVPQ, AVPQ-F		B	M1	PN 25		AVPQ, AVPQ-F		M2
1		2				1		2		
										
3						4				
										
5		4				7		5		
										

PN 25		AVPQ 4, AVPQ 4-F		B	M1	PN 25		AVPQ 4, AVPQ 4-F		M2	
1 		2 				1 		2 			
3 		4 				4 		5 			
5 		4 				7 		6 			


Service kits – Catalogue

PN 25	AVPA	M1	PN 25	AVPA	M2
1  PAM082.101	2  PAM083.101		1  PAM085.101	2  PAM086.101	
3  PAM084.101			3  PAM087.101		
5  PAM082.101	4  PAM083.101		5  PAM085.101	4  PAM086.101	


PN 25	AVA	M1	PN 25	AVA	M2
1  P.M.108.1/01	2  P.M.108.1/01	1  P.M.111.1/01	2  P.M.112.1/01		
3  P.M.110.1/01		3  P.M.113.1/01			
5  P.M.108.1/01	4  P.M.108.1/01	5  P.M.111.1/01	4  P.M.112.1/01		

PN 25	AVDS	M1
-------	------	----


1













2












3



Service kits – Catalogue


PN 25	SAVA	M1	PN 25	SAVA	M2
1 	2 	1 	2 		
3 	3 				
5 	4 	5 	4 		

PN 25	SAVD	M1	PN 25	SAVD	M2
1 	2 	1 	2 		
3    NEW  NEW 	4    NEW  NEW 	7 	5  6 		


PN 25 AVPBT

M1


1




2




3



4




5




PN 25 AVPBT

M2


1




2




3



5




4




PN 25 AVPBT


M2

7








6






PN 25	AVPQT	M2
-------	-------	----













PN 25	AVPQT	M2
-------	-------	----

7





6



PN 16	VG	M1	PN 25	VG, VGF	M2	PN 16	VGS	M1
1 			1 			1 		
2 			2 			2 		
3 			3 			3 		


Service kits – Catalogue

PN 16 / PN 25		M1	PN 25	M2						
					<table border="1"><tr><td>M1</td><td>CuSn5ZnPb (Rg5)</td></tr><tr><td>M2</td><td>EN-GJS-400-18-LT (GGG 40.3)</td></tr></table>	M1	CuSn5ZnPb (Rg5)	M2	EN-GJS-400-18-LT (GGG 40.3)	
M1	CuSn5ZnPb (Rg5)									
M2	EN-GJS-400-18-LT (GGG 40.3)									
 45 Nm			 45 Nm		 AMV(E)	 25 Nm				
PN 16						M1				




PN 25		M1
-------	--	----


1




2





3






5



4









PN 25 STL

M1, M2


1




2




3





5








4





PN 25 STL

M1, M2



Service kits – Catalogue
