

Installation guide

Shut-off ball valve

Type GBC (90bar)




009R9666

009R9666


Refrigerants: R 744 (CO₂)
 Max. working pressure(PS/MWP): 90 bar / 1305 psig
 Media temperature range: -40 °C - 100°C /-40 °F - 212°F

Warning
 Only authorized persons are allowed to operate this valve, as closing can cause build-up of excessive pressure in the system. For the application use with R744 as part of a secondary loop or cascade system should refer to the datasheet for more attentions.

Remove cap and access cap (if present)





Opening valve



Valve size	Max. torque	
	Nm	ft-lbs
6s - 22s	7	5.2
25s - 28s	26	19.2
35s	27	19.9
42s	48	35.4

OPEN Position

CLOSED Position



Імпортер:ТОВ з іі "Данфосс ТОВ" 04080, Київ 80, п/с 168, Україна

Info for UK customers only: Danfoss Ltd., 22 Wycombe End, HP9 1NB, GB

1

6s-12s: Max. 10 sec.
16s: Max. 20 sec.

2

6s-12s: Max. 5 sec.
16s: Max. 10 sec.

No need for wet cloth during brazing

3 N₂ gas from opposite side of soldering point.

Min. 5% Ag

Max. 100 °C
(212 °F)

Max. 150 °C
(300 °F)

Max. 850 °C
(1562 °F)

Install Schrader valve (if present) and cap

Danfoss
9680113

Install Schrader valve with approx. torque 0.3 Nm / 0.2 ft-lbs

Tighten cap

Danfoss
967722.10

Tighten the cap with approx. torque

Valve size	Max. Torque	
	Nm	ft-lbs
6s - 12s	10	7.4
16s - 22s	15	11.0
25s - 35s	20	14.8
42s	32	23.6

Danfoss
9680116

	Fully closed	Fully open

Danfoss A/S
Climate Solutions • danfoss.com • +45 7488 2222

Any information, including, but not limited to information on selection of product, its application or use, product design, weight, dimensions, capacity or any other technical data in product manuals, catalogues descriptions, advertisements, etc. and whether made available in writing, orally, electronically, online or via download, shall be considered informative, and is only binding if and to the extent, explicit reference is made in a quotation or order confirmation. Danfoss cannot accept any responsibility for possible errors in catalogues, brochures, videos and other material. Danfoss reserves the right to alter its products without notice. This also applies to products ordered but not delivered provided that such alterations can be made without changes to form, fit or function of the product.
All trademarks in this material are property of Danfoss A/S or Danfoss group companies. Danfoss and the Danfoss logo are trademarks of Danfoss A/S. All rights reserved.